

N Male to SMA Female Adapter



PE910113

Configuration

- N Male Connector 1
- SMA Female Connector 2
- 50 Ohms Impedance
- Straight Body Geometry

Features

- Max VSWR of 1.2:1 up to 11 GHz

Applications

- Allows Connection Between Series
- General Purpose Test

Description

Pasternack's PE910113 type N male to SMA female adapter is part of our full line of RF components available for same-day shipping. Our type N to SMA adapter has a male to female gender configuration. PE910113 type N male to SMA female adapter operates to 11 GHz. The Pasternack RF adapter provides excellent VSWR of 1.2:1 maximum.

RF adapters are often used to enable connections between two connector types that would otherwise not mate. Certain adapter configurations can also be used to protect connectors on expensive equipment where the number of connect/disconnect cycles is high. An RF, microwave or millimeter wave adapter is connected to the equipment, and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Pasternack also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		11	GHz
Impedance		50		Ohms
VSWR			1.2:1	
Insertion Loss			0.132	dB
Operating Voltage (AC)			500	Vrms
Dielectric Withstanding Voltage (AC)			1,500	Vrms
Insulation Resistance	5,000			MOhms

Mechanical Specifications

Size

Length	1.09 in [27.61 mm]
Width	0.83 in [21.01 mm]
Height	1.09 in [27.61 mm]
Weight	0.10 lbs [45.36 g]

Description	Connector 1	Connector 2
Polarity	Standard	Standard
Mating Cycles, Min	500	100

N Male to SMA Female Adapter



PE910113

Description	Connector 1	Connector 2
Mating Torque	6 to 10 in-lbs 0.68 to 1.13 Nm	4 in-lbs 0.45 Nm min
Contact Captivation Axial Force, Min	6.3 lbs [2.86 kg]	6.1 lbs [2.77 kg]
Coupling Proof Torque	15 in-lbs [1.7 Nm]	5.3 in-lbs [0.6 Nm]
Coupling Retention, Min	101.2 lbs [45.9 kg]	

Material Specifications

Description	Connector 1		Connector 2	
	Material	Plating	Material	Plating
Type	N Male		SMA Female	
Contact			Beryllium Copper	Gold over Nickel over Copper
Insulation	PTFE		PTFE	
Outer Conductor			Brass	Copper-Tin-Zinc Alloy
Body	Brass	Gold over Nickel over Copper	Brass	Copper-Tin-Zinc Alloy

Environmental Specifications

Temperature

Operating Range

-65 to +165 °C

Humidity

MIL-STD-202, Method 206

Thermal Shock

MIL-STD-202, Method 107, Condition B

Salt Spray

MIL-STD-202, Method 101, Condition B

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

N Male to SMA Female Adapter from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [N Male to SMA Female Adapter PE910113](#)

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

