

## MCX Plug Connector Solder Attachment Surface Mount PCB, 0.036 inch Hole Diameter



**PE517802**

## Configuration

- MCX Plug Connector
- 50 Ohms
- Straight Body Geometry
- Surface Mount

## Features

- Max. Operating Frequency 6 GHz
- Excellent VSWR of 1.2:1
- Gold over Nickel over Copper Plated Brass Contact

## Applications

- General Purpose Test
- PCB Applications

## Description

Pasternack's PE517802 MCX Plug Connector Solder Attachment is part of our full line of RF components available for same-day shipping. Our MCX plug connector operates up to a maximum frequency of 6 GHz and offers excellent VSWR of 1.2:1.

Our MCX plug surface mount connector PE517802 datasheet specifications and drawing with dimensions are shown below in this PDF. Pasternack's broad catalog of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. Whether the need is to provide an I/O for a board design, or simply create a custom cable assembly configuration, Pasternack has the right connector for the job. Pasternack can also expertly build your custom cable assemblies for you and ship same-day.

## Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		6	GHz
VSWR			1.2:1	
Operating Voltage (AC)			250	Vrms
Dielectric Withstanding Voltage (AC)			750	Vrms
Inner Conductor DC Resistance			5	mOhms
Outer Conductor DC Resistance			2.5	mOhms
Insulation Resistance	10,000			MOhms
Impedance		50		Ohms

## Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency Range	DC to 1	1 to 3				GHz
Insertion Loss, Max	0.1	0.15				dB

## Mechanical Specifications

<b>Size</b>	
Length	0.232 in [5.89 mm]
Width	0.236 in [5.99 mm]
Height	0.236 in [5.99 mm]

## MCX Plug Connector Solder Attachment Surface Mount PCB, 0.036 inch Hole Diameter



### PE517802

Weight	0.1 lbs [45.36 g]
Mating Cycles	500 Cycles
Engagement Force	5.6lbs [2.54kg]
Disengagement Force	1.8lbs [816.47g]

#### Material Specifications

Description	Material	Plating
Contact	Brass	Gold over Nickel over Copper
Insulation	PTFE	
Body	Phosphor Bronze	Gold over Nickel over Copper

#### Environmental Specifications

##### Temperature

Operating Range

Humidity

Thermal Shock

Salt Spray

-55 to +155 deg C

MIL-STD-202, Method 106

MIL-STD-202, Method 107, Condition F

MIL-STD-202, Method 101, Condition B

#### Compliance Certifications (see product page for current document)

#### Plotted and Other Data

Notes:

MCX Plug Connector Solder Attachment Surface Mount PCB, 0.036 inch Hole Diameter from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [MCX Plug Connector Solder Attachment Surface Mount PCB, 0.036 inch Hole Diameter PE517802](#)

URL: <https://www.pasternack.com/mcx-plug-pcb-connector-pe517802.html>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

# PE517802 CAD Drawing

MCX Plug Connector Solder Attachment Surface Mount PCB, 0.036 inch Hole Diameter



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

PE DS Rev-D4 Aze