

RP SMA Female Bulkhead Connector Crimp Attachment For LMR-240-75, LMR-240-75-DB, LMR-240-75-FR, .268 inch D Hole, IP67 Mated



**PE517832**

**Configuration**

- SMA Female Reverse Polarity Connector
- MIL-STD-348B
- 50 Ohms
- Straight Body Geometry
- Connector Interface Types: LMR-240-75, LMR-240-75-DB, LMR-240-75-FR
- Bulkhead

**Features**

- Max. Operating Frequency 6 GHz
- Gold over Nickel over Copper Plated Brass Contact
- Reverse Polarity
- IP67 Mated

**Applications**

- General Purpose Test
- Rack and Panel Mount Applications
- Custom Cable Assemblies

**Description**

Pasternack's PE517832 RP SMA Female Bulkhead Mount Connector Crimp Attachment for LMR-240-75, LMR-240-75-DB and LMR-240-75-FR Cable IP67 Mated Mated is part of our full line of RF components available for same-day shipping. The female reverse polarity configuration uses a female connector body with a male inner contact pin. Our SMA female connector operates up to a maximum frequency of 6 GHz. This SMA bulkhead connector allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications. The connector has an IP67 rating to protect against dust and temporary moisture protection under immersion conditions.

Our reverse polarity SMA female bulkhead connector PE517832 datasheet specifications and drawing with dimensions are shown below in this PDF. Pasternack's broad catalog of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. Whether the need is to provide an I/O for a board design, or simply create a custom cable assembly configuration, Pasternack has the right connector for the job. Pasternack can also expertly build your custom cable assemblies for you and ship same-day.

**Electrical Specifications**

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		6	GHz
VSWR		1.2:1		
Dielectric Withstanding Voltage (AC)			1,000	Vrms
High Potential Voltage			335	Vrms
Inner Conductor DC Resistance			3	mOhms
Outer Conductor DC Resistance			2	mOhms
Insulation Resistance	5,000			MOhms
Impedance		50		Ohms

Electrical Specification Notes:  
Insertion loss is equal to 0.04 x SQRT F(GHz) dB

**Mechanical Specifications**

**Size**  
Length 0.843 in [21.41 mm]

RP SMA Female Bulkhead Connector Crimp Attachment For LMR-240-75, LMR-240-75-DB, LMR-240-75-FR, .268 inch D Hole, IP67 Mated



**PE517832**

Width	0.433 in [11 mm]
Height	0.433 in [11 mm]
Weight	0.011 lbs [4.99 g]
Mating Cycles	100 Cycles
Mating Torque	4 to 5.3 in-lbs [[0.45 to 0.60 Nm]]
Cable Retention Force	6.1 lbs [2.77 kg]

**Material Specifications**

Description	Material	Plating
Contact	Brass	Gold over Nickel over Copper
Insulation	PTFE	
Outer Conductor	Brass	Gold over Nickel over Copper
Body	Brass	Gold over Nickel over Copper
Gasket	Silicone	
Crimp Sleeve	Copper	Gold over Nickel over Copper

**Environmental Specifications**

<b>Temperature</b>	
Operating Range	-65 to +165 deg C
Ingress Protection (IP) Rating	IP67 Mated
Humidity	MIL-STD-202, Method 106
Thermal Shock	MIL-STD-202, Method 107, Condition B

**Compliance Certifications** (see [product page](#) for current document)

**Plotted and Other Data**

Notes:

RP SMA Female Bulkhead Connector Crimp Attachment For LMR-240-75, LMR-240-75-DB, LMR-240-75-FR, .268 inch D Hole, IP67 Mated from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [RP SMA Female Bulkhead Connector Crimp Attachment For LMR-240-75, LMR-240-75-DB, LMR-240-75-FR, .268 inch D Hole, IP67 Mated PE517832](#)

URL: <https://www.pasternack.com/sma-female-reverse-polarity-lmr-240-75-lmr-240-75-db-connector-pe517832.html>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

# PE517832 CAD Drawing

RP SMA Female Bulkhead Connector Crimp Attachment For LMR-240-75, LMR-240-75-DB, LMR-240-75-FR, .268 inch D Hole, IP67 Mated

