



## BNC SOL VNA Calibration Kit Operating from DC to 10 GHz, Including Short Circuit, Open Circuit, and Load

### TECHNICAL DATA SHEET

PE5CK1024

Pasternack's BNC 18 GHz Vector Network Analyzer (VNA) calibration kit is used to calibrate VNA and associated test setup, thus allowing Vector Error Correction to compensate for systematic errors inherent in the measurement of the device under test (DUT) allowing for precise and accurate characterization of the DUT's performance. The PE5CK1024 SOL cal kit includes precisely defined male and female coaxial Short Circuits, Open Circuits, and Fixed Loads for use during a standard multi-port calibration process. The electrical behavior of the calibration standards is defined in the cal kit definition files for Keysight, Rohde & Schwarz, and Anritsu instruments, and are also provided in this manual. These files may be obtained by contacting Tech Support or downloaded from the PE5CK1024 product page on Pasternack's web site. It is necessary to follow the VNA manufacturer's instructions to import the cal kit definitions into the instrument.

A properly performed n-port SOL calibration characterizes the performance of the VNA hardware and any other cables or components out to the plane of the calibration. These affects are then removed from subsequent measurements. Calibrations performed using high quality VNA test cables effectively extends the VNA test ports to the end of the Test cables and this allows for greater flexibility when characterizing a product under test. High quality VNA test port cables are designed to optimize the stability of their phase and magnitude response – this allows the calibration to remain valid over flexure, time, and temperature, and over many mate/de-mate cycles.

Available in Stock, ship same day!

#### Features

- Cal kit definition files for Keysight, Rohde & Schwarz, and Anritsu VNAs
- Works with all major VNAs
- Protective wooden case for safe storage of components

#### Applications

- Calibration of Vector Network Analyzers
- Research and development
- Aerospace and defense
- Production test environments

#### Configuration

Connector	BNC
Frequency Range	DC to 10 GHz

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [BNC SOL VNA Calibration Kit Operating from DC to 10 GHz, Including Short Circuit, Open Circuit, and Load PE5CK1024](#)



BNC SOL VNA Calibration Kit Operating from DC to 10 GHz, Including Short Circuit, Open Circuit, and Load

TECHNICAL DATA SHEET

PE5CK1024

Electrical Specifications for PE5CK1024 BNC Devices

Item	Part Number	Specifications	Frequency (GHz)
Female Termination Male Termination	PE5TR1015 PE5TR1016	1.04 Max VSWR 1.1 Max VSWR 1.2 Max VSWR	DC to 2 2 to 4 4 to 10
Female Short Male Short	PE5SC3019 PE5SC3020	±5.0° deviation from nominal	DC to 10
Female Open Male Open	PE5SC3034 PE5SC3035	±5.0° deviation from nominal	DC to 10

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [BNC SOL VNA Calibration Kit Operating from DC to 10 GHz, Including Short Circuit, Open Circuit, and Load PE5CK1024](#)




BNC SOL VNA Calibration Kit Operating from DC to 10 GHz, Including Short Circuit, Open Circuit, and Load

TECHNICAL DATA SHEET

PE5CK1024

PE5SC3019 BNC Female Short Specifications



ELECTRICAL		UNIT
Frequency Range	DC to 10	GHz
Phase	DC to 10GHz   ±5.0°	Max
Offset Impedance	50	Ω
Offset Loss	1.5	GΩ/s
Electrical Delay	60.21	nS
Inductance	L0 x 10 <sup>-12</sup> = 0.0	H
	L1 x 10 <sup>-24</sup> = 0.0	H/Hz
	L2 x 10 <sup>-33</sup> = 0.0	H/Hz <sup>2</sup>
	L3 x 10 <sup>-42</sup> = 0.0	H/Hz <sup>3</sup>
MECHANICAL		
Housing	Brass (Nickel Plate Finish)	
Connector	BNC Female	
Screw Thread	N/A	
Dimensions	0.56 [1.42]Ø, 1.2 [30.5] Length	
Pin Depth	0.208 + 0/ -0.005	

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [BNC SOL VNA Calibration Kit Operating from DC to 10 GHz, Including Short Circuit, Open Circuit, and Load PE5CK1024](#)



BNC SOL VNA Calibration Kit Operating from DC to 10 GHz, Including Short Circuit, Open Circuit, and Load

TECHNICAL DATA SHEET

PE5CK1024

PE5SC3020 BNC Male Short Specifications



ELECTRICAL			UNIT
Frequency Range	DC to 10		GHz
Phase	DC to 10GHz	±5.0°	Max
Offset Impedance	50		Ω
Offset Loss	1.5		GΩ/s
Electrical Delay	84.29		nS
Inductance	L0 x 10 <sup>-12</sup> = 0.0		H
	L1 x 10 <sup>-24</sup> = 0.0		H/Hz
	L2 x 10 <sup>-33</sup> = 0.0		H/Hz <sup>2</sup>
	L3 x 10 <sup>-42</sup> = 0.0		H/Hz <sup>3</sup>
MECHANICAL			
Housing	Beryllium Copper (Nickel Plate Finish)		
Connector	BNC Male		
Screw Thread	N/A		
Dimensions	0.545 [13.7]Ø, 1.14 [28.9] Length		
Pin Depth	0.209 + 0.005/ - 0		

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [BNC SOL VNA Calibration Kit Operating from DC to 10 GHz, Including Short Circuit, Open Circuit, and Load PE5CK1024](#)



BNC SOL VNA Calibration Kit Operating from DC to 10 GHz, Including Short Circuit, Open Circuit, and Load

TECHNICAL DATA SHEET

PE5CK1024

PE5SC3034 BNC Female Open Specifications



ELECTRICAL		UNIT
Frequency Range	DC to 10	GHz
Phase	DC to 10GHz   ±5.0°	Max
Offset Impedance	50	Ω
Offset Loss	1.5	GΩ/s
Electrical Delay	56.24	pS
Capacitance	$C0 \times 10^{-15} = 57$	F
	$C1 \times 10^{-27} = 1350$	F/Hz
	$C2 \times 10^{-36} = 275$	F/Hz <sup>2</sup>
	$L3 \times 10^{-45} = -35$	F/Hz <sup>3</sup>

MECHANICAL	
Housing	Brass (Nickel Plate Finish)
Connector	BNC Female
Screw Thread	N/A
Dimensions	0.56 [14.22]∅, 1.22 [30.99] Length
Pin Depth	0.208 + 0/ -0.005

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [BNC SOL VNA Calibration Kit Operating from DC to 10 GHz, Including Short Circuit, Open Circuit, and Load PE5CK1024](#)



BNC SOL VNA Calibration Kit Operating from DC to 10 GHz, Including Short Circuit, Open Circuit, and Load

TECHNICAL DATA SHEET

PE5CK1024

PE5SC3035 BNC Male Open Specifications



ELECTRICAL		UNIT
Frequency Range	DC to 10	GHz
Phase	DC to 10GHz ±5.0°	Max
Offset Impedance	50	Ω
Offset Loss	1.5	GΩ/s
Electrical Delay	80.16	pS
Capacitance	$C0 \times 10^{-15} = 62$	F
	$C1 \times 10^{-27} = 450$	F/Hz
	$C2 \times 10^{-36} = 235$	F/Hz <sup>2</sup>
	$L3 \times 10^{-45} = -10$	F/Hz <sup>3</sup>
MECHANICAL		
Housing	Beryllium Copper (Nickel Plate Finish)	
Connector	BNC Male	
Screw Thread	N/A	
Dimensions	0.545 [13.71]Ø, 1.14 [28.95] Length	
Pin Depth	0.209 + 0.005/0	

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [BNC SOL VNA Calibration Kit Operating from DC to 10 GHz, Including Short Circuit, Open Circuit, and Load PE5CK1024](#)





BNC SOL VNA Calibration Kit Operating from DC to 10 GHz, Including Short Circuit, Open Circuit, and Load

TECHNICAL DATA SHEET

PE5CK1024

PE5TR1015 BNC Female Termination



ELETRICAL			UNIT
Frequency Range	DC to 10		GHz
VSWR at Frequency Range	DC to 2 GHz	1.04	Max
	2 to 4 GHz	1.1	Max
	4 to 10 GHz	1.2	Max
Impedance	50		$\Omega$
Power Rating	1 watt CW		
	1kW Peak		

MECHANICAL	
Housing	Brass (Nickel Plate Finish)
Connector	BNC Female
Screw Thread	N/A
Dimensions	0.56 [14.22] $\varnothing$ , 1.51 [38.4] Length
Pin Depth	0.208 + 0/ - 0.005

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [BNC SOL VNA Calibration Kit Operating from DC to 10 GHz, Including Short Circuit, Open Circuit, and Load PE5CK1024](#)



BNC SOL VNA Calibration Kit Operating from DC to 10 GHz, Including Short Circuit, Open Circuit, and Load

TECHNICAL DATA SHEET

PE5CK1024

PE5TR1016 BNC Male Termination



ELETRICAL			UNIT
Frequency Range	DC to 10		GHz
VSWR at Frequency Range	DC to 2 GHz	1.04	Max
	2 to 4 GHz	1.1	Max
	4 to 10 GHz	1.2	Max
Impedance	50		$\Omega$
Power Rating	1 watt CW		
	1kW Peak		

MECHANICAL	
Housing	Brass (Nickel Plate Finish)
Connector	BNC Male
Screw Thread	N/A
Dimensions	0.54 [13.7] $\varnothing$ , 1.43 [36.4] Length
Pin Depth	0.209 + 0.005/ - 0

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [BNC SOL VNA Calibration Kit Operating from DC to 10 GHz, Including Short Circuit, Open Circuit, and Load PE5CK1024](#)





BNC SOL VNA Calibration Kit Operating from DC to 10 GHz, Including Short Circuit, Open Circuit, and Load

## General Instructions and Usage Notes

#	Notes
1	Keep provided protective blue caps installed when not in use.
2	Store in climate controlled environment.
3	Always keep connectors clean.
4	Avoid touching the connector interface.
5	Use caution when handling.
6	For female components, do not insert male pin greater than 0.037" [.94 mm]. <b>Failure to comply will result in damage to the female connector.</b>
7	When mating, always ensure that the components to be interconnected remain in a fixed position while rotating <b>only the coupling nut</b> slowly to mate the connectors.
8	When de-mating, always ensure that the interconnected components remain in a fixed position while rotating <b>only the coupling nut</b> slowly to de-mate the connectors.
9	Visually inspect the connector threads prior to use. If needed, clean the center conductor pin and outer conductor with alcohol to remove any debris that may be present. <b>Be sure to apply the alcohol in a circular motion with a lint-free cloth or applicator.</b>
10	Use at room temperature.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [BNC SOL VNA Calibration Kit Operating from DC to 10 GHz, Including Short Circuit, Open Circuit, and Load PE5CK1024](#)



## BNC SOL VNA Calibration Kit Operating from DC to 10 GHz, Including Short Circuit, Open Circuit, and Load

### TECHNICAL DATA SHEET

PE5CK1024

**Compliance Certifications** (see [product page](#) for current document)

#### Plotted and Other Data

Notes:

- Values at +25 °C, sea level

BNC SOL VNA Calibration Kit Operating from DC to 10 GHz, Including Short Circuit, Open Circuit, and Load from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [BNC SOL VNA Calibration Kit Operating from DC to 10 GHz, Including Short Circuit, Open Circuit, and Load PE5CK1024](#)

URL: <https://www.pasternack.com/bnc-short-open-load-sol-vna-calibration-kit-10ghz-pe5ck1024-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.