



## 7/16 DIN Male to 7/16 DIN Female Adapter IP67 UnMated

### TECHNICAL DATA SHEET

PE91228

#### Configuration

Connector 1	7/16 DIN Male
Impedance 1	50 Ohms
Connector Specification 1	IEC 169-4
Connector 2	7/16 DIN Female
Impedance 2	50 Ohms
Connector Specification 2	IEC 169-4
Adapter Design	Standard
Body Style	Straight

#### Electrical Specifications

Frequency Range	DC to 6 GHz
Maximum VSWR	1.25:1

#### Mechanical Specifications

<b>Size</b>	
Length, in [mm]	1.673 [42.49]

#### Connector 1

Type	7/16 DIN Male
Inner Conductor Material and Plating	Beryllium Copper, Silver
Coupling Nut Material and Plating	Brass, Tri-Metal
Hex Size, mm	32
Torque, ft-lbs [Nm]	18.333 [24.86]
Body Material and Plating	Brass, Tri-Metal
Dielectric Type	PTFE

#### Connector 2

Type	7/16 DIN Female
Inner Conductor Material and Plating	Beryllium Copper, Silver
Body Material and Plating	Brass, Tri-Metal
Dielectric Type	PTFE

#### Environmental Specifications

<b>Temperature</b>	
Operating Range	-45 to +120 deg C
Ingress Protection	IP67 UnMated

#### Compliance Certifications (visit [www.Pasternack.com](http://www.Pasternack.com) for current document)

RoHS Compliant	
REACH Compliant	06/16/2014

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [7/16 DIN Male to 7/16 DIN Female Adapter IP67 UnMated PE91228](#)



## 7/16 DIN Male to 7/16 DIN Female Adapter IP67 UnMated

### TECHNICAL DATA SHEET

PE91228

#### Plotted and Other Data

Notes:

- Values at +25 °C, sea level

7/16 DIN Male to 7/16 DIN Female Adapter IP67 UnMated from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [7/16 DIN Male to 7/16 DIN Female Adapter IP67 UnMated PE91228](http://www.pasternack.com/7-16-male-7-16-female-straight-adapter-pe91228-p.aspx)

URL: <http://www.pasternack.com/7-16-male-7-16-female-straight-adapter-pe91228-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

# PE91228 CAD Drawing

7/16 DIN Male to 7/16 DIN Female Adapter IP67 UnMated



DWG TITLE

**PE91228**

NOTES:  
 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.  
 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.  
 3. DIMENSIONS ARE IN INCHES [mm].

FSCM NO. 53919

CAD FILE 061114

SCALE N/A

SIZE A

2233

**PE PASTERNAK**  
 THE ENGINEER'S RF SOURCE

Pasternack Enterprises, Inc.  
 P.O. Box 16759 | Irvine | CA | 92623  
 Phone: (949) 261-1920 | Fax: (949) 261-7451  
 Website: www.pasternack.com | E-Mail: sales@pasternack.com