



50 Ohm N Male to 75 Ohm N Female Matching Pad Operating from DC to 3 GHz RoHS Compliant

Matching Pads Technical Data Sheet

PE7070

Features

- DC to 3 GHz Frequency Range
- VSWR < 1.35:1
- 1W Max CW Power

Applications

- CATV / Cable Networks
- Communication Systems
- Test and Measurement
- Wireless Systems

Description

Pasternack's PE7070 is a 50 ohm type N male to 75 ohm type N female matching pad that operates from DC to 3 GHz. This type N to type N impedance matching pad offers a VSWR of 1.35:1 max and an attenuation accuracy of ± 0.5 dB. PE7070 50 ohm to 75 ohm minimum loss pad has a maximum CW power rating of 1 Watt.

Matching pads are used to match the different impedance between two devices, maximizing power transfer between the two impedances. Pasternack's minimum loss impedance matching pads are available in various connector combinations to fit your needs, all of which ship the same day.

Configuration

Connector 1	50 Ohms N Male
Connector Specification 1	MIL-STD-348
Connector 2	75 Ohms N Female
Connector Specification 2	MIL-STD-348

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		3	GHz
VSWR			1.35:1	
Attenuation		5.7 \pm 0.5		dB
Input Power (CW) rated at +25°C, derated linearly to 0.25W at +125°C			1	Watt
Input Power (Peak) 5 μ s pulse, 0.05% duty cycle			250	Watts

Electrical Specification Notes:

Impedance Matching Pads are resistive devices and are not designed as DC Pass or DC Block circuits

Values at +25°C, sea level

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [50 Ohm N Male to 75 Ohm N Female Matching Pad Operating from DC to 3 GHz RoHS Compliant PE7070](#)



50 Ohm N Male to 75 Ohm N Female Matching Pad
Operating from DC to 3 GHz RoHS Compliant

Matching Pads Technical Data Sheet

PE7070

Mechanical Specifications

Size

Length	1.91 in [48.51 mm]
Width	0.8 in [20.32 mm]
Weight	0.13 lbs [58.97 g]
Housing Material and Plating	Passivated Stainless Steel

Connectors

Description	Connector 1	Connector 2
Type	N Male	N Female
Impedance	50 Ohms	75 Ohms
Inner Conductor Material and Plating	Beryllium Copper, Gold	Beryllium Copper, Gold
Body Material and Plating	Passivated Stainless Steel	Passivated Stainless Steel

Environmental Specifications

Temperature

Operating Range	-20 to +85 deg C
-----------------	------------------

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

50 Ohm N Male to 75 Ohm N Female Matching Pad Operating from DC to 3 GHz RoHS Compliant from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [50 Ohm N Male to 75 Ohm N Female Matching Pad Operating from DC to 3 GHz RoHS Compliant PE7070](#)

URL: <https://www.pasternack.com/50-ohm-n-male-75-ohm-n-female-matching-pad-pe7070-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE7070 CAD Drawing

50 Ohm N Male to 75 Ohm N Female Matching Pad
 Operating from DC to 3 GHz RoHS Compliant



NOTES:
 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
 3. DIMENSIONS ARE IN INCHES [mm].

DWG TITLE
PE7070

FSCM NO. 53919

2233

SIZE A

SCALE N/A

CAD FILE 112712-B

PE PASTERNAK®
 Pasternack Enterprises, Inc.
 P.O. Box 16759 | Irvine | CA | 92623
Phone: (949) 261-1920 | **Fax:** (949) 261-7451
Website: www.pasternack.com | **E-Mail:** sales@pasternack.com