

SMA Female to TNC Female Adapter



RF Adapters Technical Data Sheet

PE9442

Configuration

- SMA Female Connector 1
- TNC Female Connector 2

Features

- Max VSWR of 1.25:1 up to 18 GHz
- SMA interface compliant with MIL-C-39012
- TNC interface compliant with MIL-C-39012
- Gold Plated Beryllium Copper Contact

- 50 Ohm
- Straight Body Geometry
- Max VSWR of 1.25:1 up to 18 GHz
- SMA Interface compliant with MIL-C-39012
- TNC Interface compliant with MIL-C-39012
- Gold Plated Beryllium Copper Contact

Applications

- Allows Connection Between Series
- General Purpose Test
- Allows Connection Between Series
- General Purpose Test

Description

Pasternack's PE9442 SMA female to TNC female adapter is part of our full line of RF components available for same-day shipping. The SMA connector mates mechanically with commercially available 3.5mm and 2.92mm (K) connectors. Our SMA to TNC adapter has a female to female gender configuration. PE9442 SMA female to TNC female adapter operates to 18 GHz. The Pasternack RF adapter provides excellent VSWR of 1.25:1 maximum.

RF adapters are often used to enable connections between two connector types that would otherwise not mate. Certain adapter configurations can also be used to protect connectors on expensive equipment where the number of connect/disconnect cycles is high. An RF, microwave or millimeter wave adapter is connected to the equipment, and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Pasternack also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

Electrical Specifications

Frequency Range	DC	18	GHz
VSWR		1.25:1	

Mechanical Specifications

Size

 Length
 1.62 in [41.15 mm]

 Width
 0.56 in [14.22 mm]

 Weight
 0.0602 lbs [27.31 g]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SMA Female to TNC Female Adapter PE9442

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com



SMA Female to TNC Female Adapter



RF Adapters Technical Data Sheet

PE9442

Description	Connector 1	Connector 2	
Туре	SMA Female	TNC Female	
Polarity	Standard	Standard	
Interface Specification	MIL-C-39012	MIL-C-39012	

Mechanical Specification Notes: TNC connector is mode free up to 18 GHz.

Material Specifications

laterial	Plating	Material	Plating
IA Female		TNC Female	
lium Copper	Gold	Beryllium Copper	Gold
d Stainless Steel		Passivated Stainless Steel	
1	A Female lium Copper	IA Female lium Copper Gold	A Female TNC Female lium Copper Gold Beryllium Copper

Environmental Specifications

Temperature

Operating Range -65 to +125 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SMA Female to TNC Female Adapter PE9442

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451



SMA Female to TNC Female Adapter



RF Adapters Technical Data Sheet

PE9442

SMA Female to TNC Female Adapter from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SMA Female to TNC Female Adapter PE9442

URL: https://www.pasternack.com/sma-female-tnc-female-straight-adapter-pe9442-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

PE9442 CAD DrawingSMA Female to TNC Female Adapter

