



D-Sub Receptacle to D-Sub Receptacle Adapter

TECHNICAL DATA SHEET

PE9689

D-Sub Receptacle to D-Sub Receptacle Adapter

Configuration

Connector 1	D-Sub Receptacle
Impedance 1	50 Ohms
Connector 2	D-Sub Receptacle
Impedance 2	50 Ohms
Adapter Design	Standard
Body Style	Straight

Mechanical Specifications

Size

Length, in [mm]	1.225 [31.12]
Width/Dia., in [mm]	0.223 [5.66]

Connector 1

Type	D-Sub Receptacle
Inner Conductor Material and Plating	Gold
Body Material and Plating	Brass, Gold
Dielectric Type	PTFE

Connector 2

Type	D-Sub Receptacle
Inner Conductor Material and Plating	Gold
Body Material and Plating	Brass, Gold
Dielectric Type	PTFE

Compliance Certifications (visit www.Pasternack.com for current document)

RoHS Compliant	Yes
----------------	-----

Plotted and Other Data

Notes:	Values at 25 °C, sea level
--------	----------------------------

D-Sub Receptacle to D-Sub Receptacle Adapter from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [D-Sub Receptacle to D-Sub Receptacle Adapter PE9689](http://www.pasternack.com/d-sub-receptacle-d-sub-receptacle-straight-adapter-pe9689-p.aspx)

URL: <http://www.pasternack.com/d-sub-receptacle-d-sub-receptacle-straight-adapter-pe9689-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.

PE9689 CAD Drawing

D-Sub Receptacle to D-Sub Receptacle Adapter



NOTES:
 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
 3. DIMENSIONS ARE IN INCHES [mm].

DWG TITLE		FSCM NO. 53919		CAD FILE	111402	SCALE	N/A	SIZE	A	127
PE9689		REV. -								

PASTERNAK ENTERPRISES, INC.
 P O BOX 16759, IRVINE, CA 92623
 PHONE (949) 261-1920 FAX (949) 261-7451
 WEB ADDRESS: www.pasternack.com
 E-MAIL ADDRESS: sales@pasternack.com
COAXIAL & FIBER OPTICS

