

WR-137 Waveguide Standard Gain Horn Antenna

Operating from 5.85 GHz to 8.2 GHz with a Nominal
10 dB Gain N Female Input, Pro Line

Technical Data Sheet

PE9859B/NF-10

Features

- WR-137 Rectangular Waveguide Interface
- 5.85 GHz to 8.2 GHz
- 10 dBi Nominal Gain
- Type N Female Connector

Applications

- Antenna Measurements
- Laboratory Use
- Wireless Communication
- Microwave Radio Systems

Description

The Proline series PE9859B/NF-10 standard gain horn antenna (also known as waveguide horn) from Pasternack is part of our huge selection of waveguide antennas. This Pasternack standard gain horn antenna is manufactured with a WR-137 input and a waveguide to coaxial transition adapter. Our WR-137 standard gain horn antenna has a nominal gain of 10 dBi. This WR-137 standard gain horn has a Type N waveguide to coax transition adapter that is female gender. The Pasternack 10 dBi WR-137 horn antenna operates from 5.85 GHz to 8.2 GHz. The WR-137 PE9859B/NF-10 waveguide horn is US made and TAA compliant. It is part of over 40,000 RF, microwave and millimeter wave components available from Pasternack. Waveguide standard gain horn antennas, such as the PE9859B/NF-10, are used in a wide variety of applications due to their high power handling capability, low loss, high directivity, and near constant electrical performance. Pasternack's Type N female WR-137 standard gain horns are available in 10, 15 and 20 dBi models with pyramidal shape and rectangular input. Our WR-137 standard gain horn Proline antennas with Type N female interface can ship worldwide the same day as it is purchased as with our other available RF parts.


Configuration

Design	WR-137 Standard Gain Horn
Pattern	Directional
Polarization	Linear
Coaxial Interface	N Female

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	5.85		8.2	GHz
Impedance		50		Ohms
Waveguide Standard Gain Horn				
Gain		10		dB
Waveguide to Coaxial Adapter				
Input VSWR			1.3:1	

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [WR-137 Waveguide Standard Gain Horn Antenna Operating from 5.85 GHz to 8.2 GHz with a Nominal 10 dB Gain N Female Input, Pro Line PE9859B/NF-10](#)



WR-137 Waveguide Standard Gain Horn Antenna
Operating from 5.85 GHz to 8.2 GHz with a Nominal
10 dB Gain N Female Input, Pro Line

Technical Data Sheet

PE9859B/NF-10

Mechanical Specifications

Size

Length	4.38 in [111.25 mm]
Width	2.02 in [51.31 mm]
Height	1.48 in [37.59 mm]
Weight	0.42 lbs [190.51 g]

RF Connector

Type	N Female
------	----------

Waveguide Interface

Waveguide Size	WR-137
Flange Type	CMR-137

Environmental Specifications

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

2 Dimensional OML Drawing	PE9859B/NF-10
Notes:	

WR-137 Waveguide Standard Gain Horn Antenna Operating from 5.85 GHz to 8.2 GHz with a Nominal 10 dB Gain N Female Input, Pro Line from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [WR-137 Waveguide Standard Gain Horn Antenna Operating from 5.85 GHz to 8.2 GHz with a Nominal 10 dB Gain N Female Input, Pro Line PE9859B/NF-10](#)




URL: <https://www.pasternack.com/wr-137-waveguide-standard-gain-horn-antenna-10-db-n-pe9859b-nf-10-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE9859B/NF-10 CAD Drawing

WR-137 Waveguide Standard Gain Horn Antenna Operating from 5.85 GHz to 8.2 GHz with a Nominal 10 dB Gain N Female Input, Pro Line

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
B	PCR PE9859B-10 20210526	06/02/2021	KHIETPAS



<p>THIRD-ANGLE PROJECTION</p> <p>THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF PASTERNAK CORPORATION ALL RIGHTS RESERVED.</p>		<p>SHEET 1 OF 1</p>																			
<p>SCALE N/A</p>		<p>REV B</p>																			
<p>PE PASTERNAK an INFINITE brand</p> <p>Pasternack Enterprises, Inc. P.O. Box 16759, Irvine, CA 92623. Phone: 1.949.261.1920 1.866.727.8376 Fax: 1.949.261.7451 Website: www.pasternack.com E-mail: sales@pasternack.com</p>		<p>ITEM NO. PE9859B/NF-10</p>																			
<p>UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS</p> <p>TOLERANCES:</p> <table border="1"> <tr> <th>XX</th> <th>FRACTIONS</th> <th>ANGLES</th> </tr> <tr> <td>.XX = ±.02 [.51]</td> <td>± 1/32</td> <td>ANGLES ± 1°</td> </tr> <tr> <td>.XXX = ±.005 [.13]</td> <td></td> <td></td> </tr> </table> <p>CABLE LENGTH (L) TOLERANCES:</p> <table border="1"> <tr> <td>L ≤ 12 [305]</td> <td>± 1 [25] / -0</td> </tr> <tr> <td>12 [305] < L ≤ 60 [1524]</td> <td>± 2 [51] / -0</td> </tr> <tr> <td>60 [1524] < L ≤ 120 [3048]</td> <td>± 4 [102] / -0</td> </tr> <tr> <td>120 [3048] < L ≤ 300 [7620]</td> <td>± 6 [152] / -0</td> </tr> <tr> <td>300 [7620] < L</td> <td>± 5% / -0</td> </tr> </table>	XX	FRACTIONS	ANGLES	.XX = ±.02 [.51]	± 1/32	ANGLES ± 1°	.XXX = ±.005 [.13]			L ≤ 12 [305]	± 1 [25] / -0	12 [305] < L ≤ 60 [1524]	± 2 [51] / -0	60 [1524] < L ≤ 120 [3048]	± 4 [102] / -0	120 [3048] < L ≤ 300 [7620]	± 6 [152] / -0	300 [7620] < L	± 5% / -0	<p>SIZE A</p> <p>CAGE CODE 53919</p> <p>DRAWN BY BPUCHASKI</p>	<p>ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.</p>
XX	FRACTIONS	ANGLES																			
.XX = ±.02 [.51]	± 1/32	ANGLES ± 1°																			
.XXX = ±.005 [.13]																					
L ≤ 12 [305]	± 1 [25] / -0																				
12 [305] < L ≤ 60 [1524]	± 2 [51] / -0																				
60 [1524] < L ≤ 120 [3048]	± 4 [102] / -0																				
120 [3048] < L ≤ 300 [7620]	± 6 [152] / -0																				
300 [7620] < L	± 5% / -0																				

NOTES:
1. LABEL PER ILS-100-03 (FOR INTERNAL REFERENCE ONLY)
LABEL LOCATION FOR REFERENCE ONLY

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.