

2 Way WR-75 Waveguide Power Divider UG Square Cover Flange From 13.75 GHz to 14.5 GHz, Aluminum



PEW75DV001

Features

- 2-Way Waveguide Power Divider
- WR-75 Waveguide Interface
- 13.75 to 14.5 GHz Frequency Range
- Max Power 20 Watts (CW)
- Insertion Loss 0.3 dB max
- Isolation 17 dB min

Applications

- Test Benches
- Radar
- Satellite
- Microwave Radio
- Attenuation Measurements
- Power Measurements

Description

Pasternack carries a wide selection of waveguide power dividers to fit your needs. These components are essential in many systems, allowing the combination of multiple signals or splitting of a single signal into multiple signals with equal magnitude and phase. The PEW75DV001 is a 2-way waveguide power divider that operates from 13.75 to 14.5 GHz and can handle up to 20 Watts (CW) with 0.3 dB max insertion loss and 17 dB min isolation. The package uses WR-75 waveguide interface.

Electrical Specifications

Number of Output Ports

2

Description	Min	Typ	Max	Units
Frequency Range	13.75		14.5	GHz
Input VSWR			1.25:1	
Output VSWR			1.25:1	
Insertion Loss			0.3	dB
Isolation	17			dB
Amplitude Balance			± 0.2	dB
Phase Balance			± 2	Degrees
Input Power (CW)			20	Watts
Input Power (Peak)			20	kWatts

Mechanical Specifications

Size

Length	2.76 in [70.1 mm]
Width	2.13 in [54.1 mm]
Height	2.32 in [58.93 mm]
Weight	0.21 lbs [95.25 g]
Finish	Gray
Housing Material and Plating	Aluminum, Chromate Conversion

Configuration

Input Waveguide Size	WR-75
Input Flange Designation	UG
Input Flange Type	Square Cover

2 Way WR-75 Waveguide Power Divider UG Square Cover Flange From 13.75 GHz to 14.5 GHz, Aluminum



PEW75DV001

Input Body Material	Aluminum, Chromate Conversion
Output Waveguide Size	WR-75
Output Flange Designation	UG
Output Flange Type	Square Cover
Output Body Material	Aluminum, Chromate Conversion

Environmental Specifications

Temperature	
Operating Range	-40 to +70 deg C
Storage Range	-55 to +85 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Typical Performance Data

2 Way WR-75 Waveguide Power Divider UG Square Cover Flange From 13.75 GHz to 14.5 GHz, Aluminum from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2 Way WR-75 Waveguide Power Divider UG Square Cover Flange From 13.75 GHz to 14.5 GHz, Aluminum PEW75DV001](#)

URL: <https://www.pasternack.com/2-way-wr-75-waveguide-power-divider-ug-square-cover-flange-from-13.75-ghz-to-14.5-ghz-aluminum-pew75dv001-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PEW75DV001 CAD Drawing

2 Way WR-75 Waveguide Power Divider UG Square Cover Flange From 13.75 GHz to 14.5 GHz, Aluminum

