

PEPASTESNACK PEWCA1085 1810

WR-159 CPR-159G Grooved Flange to N Female Waveguide to Coax Adapter Operating from 4.9 GHz to 7.05 GHz

Waveguide to Coax Adapters Technical Data Sheet

PEWCA1055

Features

- D Band
- 4.9 to 7.05 GHz Frequency Range
- WR-159 Waveguide Interface

- CPR-159G Flange
- N Female RF Interface
- Right Angle

Applications

- Test Benches
- Radar

- Satellite
- Microwave Radio Systems
- Military and Space
- Communication Systems

Description

The PEWCA1055 is a waveguide to coaxial adapter operating in the D Band with a 4.9 to 7.05 GHz frequency range. This adapter offers a WR-159 waveguide interface size using a standard CPR-159G Flange. The PEWCA1055 is constructed of Aluminum Alloy and painted to ensure durability. The coaxial connector offered by this adapter uses a N Female Connector. All waveguide components available for same day shipping.

Configuration

Waveguide Size Flange RF Connector Impedance Body Geometry WR-159 CPR-159G N Female 50 Ohms Right Angle

Electrical Specifications

| Description | Minimum | Typical | Maximum | Units |
|-----------------|---------|---------|---------|-------|
| Frequency Range | 4.9 | | 7.05 | GHz |
| VSWR | | 1.25:1 | | |
| | | | | |

Mechanical Specifications

RF Connector

Connector Type N Female

Waveguide Interface

Waveguide Type WR-159
Flange Type CPR-159G
Body Material and Plating Aluminum, Paint

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: WR-159 CPR-159G Grooved Flange to N Female Waveguide to Coax Adapter Operating from 4.9 GHz to 7.05 GHz PEWCA1055

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com



WR-159 CPR-159G Grooved Flange to N Female Waveguide to Coax Adapter Operating from 4.9 GHz to 7.05 GHz



Waveguide to Coax Adapters Technical Data Sheet

PEWCA1055

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

• Values at +25 °C, sea level unless stated otherwise

Typical Performance Data



WR-159 CPR-159G Grooved Flange to N Female Waveguide to Coax Adapter Operating from 4.9 GHz to 7.05 GHz from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: WR-159 CPR-159G Grooved Flange to N Female Waveguide to Coax Adapter Operating from 4.9 GHz to 7.05 GHz PEWCA1055

URL: https://www.pasternack.com/wr159-cpr-159g-grooved-flange-to-type-n-female-waveguide-coax-adapter-pewca1055-p. aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

PEWCA1055 CAD Drawing

WR-159 CPR-159G Grooved Flange to N Female Waveguide to Coax Adapter Operating from 4.9 GHz to 7.05 GHz

