



SP4T PIN Diode Switch Operating From 500 MHz to 18 GHz
Up to 0.1 Watts (+20 dBm) and Field Replaceable SMA

PIN Diode Switches Technical Data Sheet

PE71S6223

Features

- SP4T Reflective Switch
- 0.5 GHz to 18.0 GHz
- Insertion Loss 3.2 dB typ
- Isolation 55 dB min
- Power Input 20 dBm CW max
- Switching Speed 100 nsec max

Applications

- Test & Measurement
- Military Communication
- Commercial Communication
- Wireless Communications
- SATCOM
- Military Electronic Systems
- RF Test Stations

Description

The PE71S6223 is a Single Pole Four Throw (SP4T) Reflective PIN Diode Switch that operates from 0.5 to 18 GHz. Performance includes 3.2 dB typ insertion loss, 55 dB min Isolation, and 100 nsec max switching speed. The design incorporates TTL-compatible driver circuitry for accurate logic control. Operational temperature range is -40°C to +85°C and dual voltage controls of +5 VDC and -15 VDC are required. The rugged package design is compact, features field replaceable female SMA connectors, and is designed to meet MIL-STD 202F environmental test conditions which include humidity, shock, vibration, altitude, and temperature cycle.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	0.5		18	GHz
Impedance		50		Ohms
VSWR			2:1	
Insertion Loss		3.2		dB
Isolation	55			dB
Switching Time			100	ns
Input Power (CW)			0.1	Watts
Survival Power			1	Watts
Positive Operating Voltage		5		Vdc
Negative Operating Voltage		-15		Vdc
Current @ 5 Vdc		160		mA
Current @ -15 Vdc		50		mA
Operating Temperature	-40		+85	deg C

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SP4T PIN Diode Switch Operating From 500 MHz to 18 GHz Up to 0.1 Watts \(+20 dBm\) and Field Replaceable SMA PE71S6223](#)



SP4T PIN Diode Switch Operating From 500 MHz to 18 GHz
Up to 0.1 Watts (+20 dBm) and Field Replaceable SMA

PIN Diode Switches Technical Data Sheet

PE71S6223

Mechanical Specifications

Size

Length	1.5 in [38.1 mm]
Width	1.5 in [38.1 mm]
Height	0.6 in [15.24 mm]
Weight	0.137 lbs [62.14 g]
Finish	Blue Paint

Configuration

Design	Reflective, SP4T
RF Connector	SMA Female
RF Connector Option	Field Replaceable
TTL Control Connector	Solder Pin

Environmental Specifications

Temperature

Operating Range	-40 to +85 deg C
Storage Range	-55 to +125 deg C

Humidity

MIL-STD-202F, Method 103B, Condition B

MIL-STD-202F, Method 213B, Condition B

MIL-STD-202F, Method 204D, Condition B

MIL-STD-202F, Method 105C, Condition B

MIL-STD-202F, Method 107D, Condition A

ESD Sensitive Material, Transport material in Approved ESD bags. Handle only in ESD Workstation.



Compliance Certifications (visit www.Pasternack.com for current document)

Not RoHS Compliant

REACH Compliant

12/17/2015

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SP4T PIN Diode Switch Operating From 500 MHz to 18 GHz Up to 0.1 Watts \(+20 dBm\) and Field Replaceable SMA PE71S6223](#)





SP4T PIN Diode Switch Operating From 500 MHz to 18 GHz
Up to 0.1 Watts (+20 dBm) and Field Replaceable SMA

PIN Diode Switches Technical Data Sheet

PE71S6223

Typical Performance Data



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SP4T PIN Diode Switch Operating From 500 MHz to 18 GHz Up to 0.1 Watts \(+20 dBm\) and Field Replaceable SMA PE71S6223](#)




SP4T PIN Diode Switch Operating From 500 MHz to 18 GHz
Up to 0.1 Watts (+20 dBm) and Field Replaceable SMA


PIN Diode Switches Technical Data Sheet

PE71S6223

(J1 – J3) Insertion Loss and Return Loss



(J1 – J3) Isolation



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SP4T PIN Diode Switch Operating From 500 MHz to 18 GHz Up to 0.1 Watts \(+20 dBm\) and Field Replaceable SMA PE71S6223](#)




SP4T PIN Diode Switch Operating From 500 MHz to 18 GHz
Up to 0.1 Watts (+20 dBm) and Field Replaceable SMA

PIN Diode Switches Technical Data Sheet

PE71S6223

(J1 – J4) Insertion Loss and Return Loss



(J1 – J4) Isolation





Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SP4T PIN Diode Switch Operating From 500 MHz to 18 GHz Up to 0.1 Watts \(+20 dBm\) and Field Replaceable SMA PE71S6223](#)



SP4T PIN Diode Switch Operating From 500 MHz to 18 GHz
Up to 0.1 Watts (+20 dBm) and Field Replaceable SMA

PIN Diode Switches Technical Data Sheet

PE71S6223



SP4T PIN Diode Switch Operating From 500 MHz to 18 GHz Up to 0.1 Watts (+20 dBm) and Field Replaceable SMA from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SP4T PIN Diode Switch Operating From 500 MHz to 18 GHz Up to 0.1 Watts \(+20 dBm\) and Field Replaceable SMA PE71S6223](#)



SP4T PIN Diode Switch Operating From 500 MHz to 18 GHz
Up to 0.1 Watts (+20 dBm) and Field Replaceable SMA

PIN Diode Switches Technical Data Sheet

PE71S6223


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SP4T PIN Diode Switch Operating From 500 MHz to 18 GHz Up to 0.1 Watts \(+20 dBm\) and Field Replaceable SMA PE71S6223](https://www.pasternack.com/sp4t-pin-diode-switch-18-ghz-20-dbm-sma-pe71s6223-p.aspx)

URL: <https://www.pasternack.com/sp4t-pin-diode-switch-18-ghz-20-dbm-sma-pe71s6223-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE71S6223 CAD Drawing

SP4T PIN Diode Switch Operating From 500 MHz to 18 GHz Up
to 0.1 Watts (+20 dBm) and Field Replaceable SMA



DWG TITLE

PE71S6223

NOTES:
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES [mm].

FSCM NO. 53919

CAD FILE 041916

SCALE N/A

SIZE A

2233

PASTERNAK
THE ENGINEER'S RF SOURCE

Pasternack Enterprises, Inc.
P.O. Box 16759 | Irvine | CA | 92623
Phone: (949) 261-1920 | Fax: (949) 261-7451
Website: www.pasternack.com | E-Mail: sales@pasternack.com