



Waveguide Couplers Assemblies Technical Data

PEWCT1078

The PEWCT1078 is a 40 dB WR-90 four port crossguide coupler with one coupled port terminated (making it a three port coupler) and a coax adapter on the opposite coupled port. This coupler can be mounted directly into the waveguide signal path, connected via coax to allow signal sampling /monitoring. The coupler has a typical VSWR of 1.05:1 and are made of bronze with brass UG-39/U Square Cover flanges. The PEWCT1078 is part of a family of cross guide couplers offered by Pasternack with coupling values ranging from 20 to 50 dB. There is also a full family of top wall (broad wall) couplers. For the three port version of this coupler (terminated but no coax adapter) please see the PEWCT1022. For the four port version of this coupler (no termination, no coax adapter) please see the PEWCP1057.

Features

- Three Port
- Crossguide Waveguide Coupler
- Terminated
- 40 dB Nominal Coupling Level
- Applications
 - Test Benches
 - Radar
 - Satellite

Microwave Radio

Attenuation Measurements Power Measurements Source Leveling

Waveguide Body made of Bronze with Brass Flanges

N Female Coax Adapter

Low VSWR

8.2 GHz to 12.4 GHz Frequency Range

Electrical Specifications

Description	Minimum	Typical	Maximum	Units	
Frequency Range	8.2		12.4	GHz	
Impedance		50		Ohms	
Coupler					
Nominal Coupling Level		40		dB	
Directivity		10		dB	
Insertion Loss		0.1		dB	
Main Line VSWR		1.05:1			
Termination					
Input Power (CW)			4	Watts	
Waveguide to Coax Adapters					
VSWR		1.25:1			

Mechanical Specifications

Interface Waveguide Size

WR-90

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: WR-90 Waveguide 40 dB Crossguide Coupler, UG-39/U Square Cover Flange, N Female Coupled Port, 8.2 GHz to 12.4 GHz, Bronze PEWCT1078

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com





PEWCT1078

Waveguide Couplers Assemblies Technical Data

Flange Type Flange Designation Flange Material and Plating RF Connector Type

Coupler Body Material and Plating Termination Body Material and Plating Square Cover UG-39/U Brass N Female

Bronze Bronze

Environmental Specifications

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Typical Performance Data

				VSW	/R			
5								
			/					
:								
)								
,								
8.2 GHz	8.7	9.3	9.8	10	.3 10).8 1	11.4 1	.1.9 12

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: WR-90 Waveguide 40 dB Crossguide Coupler, UG-39/U Square Cover Flange, N Female Coupled Port, 8.2 GHz to 12.4 GHz, Bronze PEWCT1078

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com





PEWCT1078

Waveguide Couplers Assemblies Technical Data

Coupling Value 0 dB -10 -20 -30 -40 -50 -60 8.20 GHz 8.8 9.4 10.0 10.6 11.2 11.8 12.4 Directivity 0 dB -5 Jum May monthly mmm many -10 -15 -20 -25 -30 -35 -40 8.20 GHz 9.4 10.0 88 10.6 11.2 11.8 12.4

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: WR-90 Waveguide 40 dB Crossguide Coupler, UG-39/U Square Cover Flange, N Female Coupled Port, 8.2 GHz to 12.4 GHz, Bronze PEWCT1078

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com





Waveguide Couplers Assemblies Technical Data

PEWCT1078

WR-90 Waveguide 40 dB Crossguide Coupler, UG-39/U Square Cover Flange, N Female Coupled Port, 8.2 GHz to 12.4 GHz, Bronze from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: WR-90 Waveguide 40 dB Crossguide Coupler, UG-39/U Square Cover Flange, N Female Coupled Port, 8.2 GHz to 12.4 GHz, Bronze PEWCT1078

URL: https://www.pasternack.com/wr90-waveguide-40db-crossguide-coupler-ug-39-square-n-12.4-ghz-pewct1078-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451 Sales@Pasternack.com • Techsupport@Pasternack.com

PEWCT1078 CAD Drawing

WR-90 Waveguide 40 dB Crossguide Coupler, UG-39/U Square Cover Flange, N Female Coupled Port, 8.2 GHz to 12.4 GHz, Bronze

