



SP3T PIN Diode Switch Operating From 2 GHz to 4 GHz
Up to 0.1 Watts (+20 dBm) and Field Replaceable SMA

PIN Diode Switches Technical Data Sheet

PE71S6272

Features

- SP3T Reflective Switch
- 2.0 GHz to 4.0 GHz
- High Speed Switching
- Insertion Loss 1.2 dB typ
- Isolation 75 dB typ
- Power Input 20 dBm CW max
- Field Replaceable Connectors

Applications

- Test & Measurement
- Military Communication
- Commercial Communication
- Wireless Communications
- SATCOM
- Military Electronic Systems
- RF Test Stations

Description

The PE71S6272 is a Single Pole Triple Throw (SP3T) Reflective PIN Diode Switch that operates from 2 GHz to 4 GHz. Performance includes 1.2 dB typ insertion loss, 75 dB typ isolation, and 100 nsec max switching speed. The design incorporates TTL compatible driver circuitry for accurate logic control. Operational temperature range is -55°C to +85°C and dual voltage controls of +5 DC and -15 DC are required. The rugged package is designed to meet a series of MIL-STD-202F environmental conditions including humidity, shock, vibration, and temperature cycle. Package interfaces include solder terminals and female SMA connectors.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	2		4	GHz
Impedance		50		Ohms
Insertion Loss		1.2		dB
Isolation		75		dB
Rise Time			75	ns
Switching Time			100	ns
Input Power (CW)			0.1	Watts
Survival Power			1	Watts
Positive Operating Voltage		5		Vdc
Negative Operating Voltage		-15		Vdc
Current @ 5 Vdc		150		mA
Current @ -15 Vdc		75		mA
Operating Temperature	-55		+85	deg C

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SP3T PIN Diode Switch Operating From 2 GHz to 4 GHz Up to 0.1 Watts \(+20 dBm\) and Field Replaceable SMA PE71S6272](#)



SP3T PIN Diode Switch Operating From 2 GHz to 4 GHz
Up to 0.1 Watts (+20 dBm) and Field Replaceable SMA

PIN Diode Switches Technical Data Sheet

PE71S6272

Mechanical Specifications

Size

Length	1.5 in [38.1 mm]
Width	1.5 in [38.1 mm]
Height	0.4 in [10.16 mm]
Weight	0.093 lbs [42.18 g]
Finish	Blue Paint

Configuration

Design	Reflective, SP3T
RF Connector	SMA Female
RF Connector Option	Field Replaceable
TTL Control Connector	Solder Pin

Environmental Specifications

Temperature

Operating Range	-55 to +85 deg C
Storage Range	-65 to +125 deg C

Humidity

Shock

Vibration

Altitude

Temperature Cycling

ESD Sensitivity

MIL-STD-202F, Method 103B, Condition B
MIL-STD-202F, Method 213B, Condition B
MIL-STD-202F, Method 204D, Condition B
MIL-STD-202F, Method 105C, Condition B
MIL-STD-202F, Method 107D, Condition A
ESD Sensitive Material, Transport material in Approved
ESD bags. Handle only in ESD Workstation.



Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SP3T PIN Diode Switch Operating From 2 GHz to 4 GHz Up to 0.1 Watts \(+20 dBm\) and Field Replaceable SMA PE71S6272](#)




SP3T PIN Diode Switch Operating From 2 GHz to 4 GHz
Up to 0.1 Watts (+20 dBm) and Field Replaceable SMA

PIN Diode Switches Technical Data Sheet

PE71S6272

Typical Performance Data

(J1 – J2) Insertion Loss and Return Loss



(J1 – J2) Isolation



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SP3T PIN Diode Switch Operating From 2 GHz to 4 GHz Up to 0.1 Watts \(+20 dBm\) and Field Replaceable SMA PE71S6272](#)




SP3T PIN Diode Switch Operating From 2 GHz to 4 GHz
Up to 0.1 Watts (+20 dBm) and Field Replaceable SMA


PIN Diode Switches Technical Data Sheet

PE71S6272

(J1 – J3) Insertion Loss and Return Loss



(J1 – J3) Isolation



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SP3T PIN Diode Switch Operating From 2 GHz to 4 GHz Up to 0.1 Watts \(+20 dBm\) and Field Replaceable SMA PE71S6272](#)




SP3T PIN Diode Switch Operating From 2 GHz to 4 GHz
Up to 0.1 Watts (+20 dBm) and Field Replaceable SMA


PIN Diode Switches Technical Data Sheet

PE71S6272

(J1 – J4) Insertion Loss and Return Loss



(J1 – J4) Isolation



SP3T PIN Diode Switch Operating From 2 GHz to 4 GHz Up to 0.1 Watts (+20 dBm) and Field Replaceable SMA from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SP3T PIN Diode Switch Operating From 2 GHz to 4 GHz Up to 0.1 Watts \(+20 dBm\) and Field Replaceable SMA PE71S6272](#)



SP3T PIN Diode Switch Operating From 2 GHz to 4 GHz
Up to 0.1 Watts (+20 dBm) and Field Replaceable SMA

PIN Diode Switches Technical Data Sheet

PE71S6272


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SP3T PIN Diode Switch Operating From 2 GHz to 4 GHz Up to 0.1 Watts \(+20 dBm\) and Field Replaceable SMA PE71S6272](https://www.pasternack.com/sp3t-pin-diode-switch-4-ghz-20-dbm-sma-pe71s6272-p.aspx)

URL: <https://www.pasternack.com/sp3t-pin-diode-switch-4-ghz-20-dbm-sma-pe71s6272-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE71S6272 CAD Drawing

SP3T PIN Diode Switch Operating From 2 GHz to 4 GHz Up
to 0.1 Watts (+20 dBm) and Field Replaceable SMA



Pasternack Enterprises, Inc.
P.O. Box 16759 | Irvine | CA | 92623

Phone: (949) 261-1920 | Fax: (949) 261-7451

Website: www.pasternack.com | E-Mail: sales@pasternack.com

DWG TITLE

PE71S6272

CAGE CODE 53919

NOTES:
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES [mm].

CAD FILE 04/03/18

SCALE N/A

SIZE A

7361