

## SPDT Electromechanical Relay Latching Switch, DC to 67 GHz, Up to 80W, 28V, 2M Lifecycles, Solder Terminal, 1.85mm

### PE71S9020



#### Features

- Single Pole Double Throw
- DC to 67 GHz Frequency Range
- Isolation greater than 50 dB minimum
- 2M Cycle Min Operating Life
- +28 Volt DC
- 80 Watt average Power
- Latching Actuator
- -25 to +70°C Operating Temperature
- Insertion Loss as low as 1.1 dB Max
- VSWR as low as 1.9:1 max
- 1.85mm Female RF connectors
- Solder Terminals for DC Control

#### Applications

- Aerospace & Defense
- Test & Measurement
- Microwave Radio Systems
- Military Commercial Communication Systems
- Research & Development
- SATCOM
- Wireless Communications
- Enterprise
- IOT

#### Description

The PE71S9020 is a Single Pole Double Throw (SPDT) electromechanical relay switch that operates across a wide frequency range of DC to 67 GHz and can handle up to 80 Watts of CW input power in a break before make condition. The 50 Ohm design is rated for 2M life cycles for high reliability operation and features a Latching actuator, which maintains its position without continuous power, reducing power consumption and ensuring stable operation even during power loss. Impressive performance includes insertion loss less than 1.1 dB maximum and isolation greater than 50 dB minimum. The Latching actuator requires +28 Vdc bias voltage, and operates over a temperature range of -25°C to +70°C. The rugged and compact package assembly supports 1.85mm Female connectors and terminal solder pins for DC Control.

#### Electrical Specifications (TA = +25°C, DC Voltage = 28 Vdc)

Switch Type	SPDT
Actuator Type	Latching
Switching Sequence	Make Before Break
Polarity	Negative Common

Description	Min	Typ	Max	Units
Frequency Range	DC		67	GHz
Impedance		50		Ohms
Operating Voltage	24	28	30	Volts
Actuating Current @ 28 Volts		80		mA
VSWR			1.9:1	
Insertion Loss			1.1	dB
Isolation	50			dB
Input Power (CW)			80	Watts
Switching Time			10	ms

SPDT Electromechanical Relay Latching  
Switch, DC to 67 GHz, Up to 80W, 28V, 2M  
Lifecycles, Solder Terminal, 1.85mm



## PE71S9020

### Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency Range	DC to 6	6 to 18	18 to 26.5	26.5 to 40	40 to 67	GHz
VSWR, Max	1.3:1	1.5:1	1.7:1	1.9:1	1.9:1	
Insertion Loss, Max	0.3	0.5	0.7	0.8	1.1	dB
Isolation, Min	70	60	55	50	50	dB
Power In, Max (CW)	80	50	20	10	3	Watts

Electrical Specification Notes:

Average Power at 25°C per RF Path

SPDT Electromechanical Relay Latching Switch, DC to 67 GHz, Up to 80W, 28V, 2M Lifecycles, Solder Terminal, 1.85mm



## PE71S9020

### Mechanical Specifications

#### Size

Length	1.53 in [38.86 mm]
Width/Diameter	1.5 in [38.1 mm]
Height	0.51 in [12.95 mm]
Weight	0.05 lbs [22.68 g]
Package Type	Connectorized
Operating Life	2,000,000 Cycles

#### Connectors

RF Connector Type	1.85mm Female
RF Connector Specification	IEEE STD 287
Control Connector	Solder Pin

Mechanical Specification Notes:  
Solder Pins: 250°C max/30sec.

### Environmental Specifications

#### Temperature

Operating Range	-25 to +70 deg C
Storage Range	-40 to +85 deg C
Construction	Splashproof

### Compliance Certifications

(see product page for current document)

### Plotted and Other Data

#### Notes:

Values shown are typical at 25°C.

SPDT Electromechanical Relay Latching Switch, DC to 67 GHz, Up to 80W, 28V, 2M Lifecycles, Solder Terminal, 1.85mm from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SPDT Electromechanical Relay Latching Switch, DC to 67 GHz, Up to 80W, 28V, 2M Lifecycles, Solder Terminal, 1.85mm PE71S9020](#)

URL: <https://www.pasternack.com/spdt-electromechanical-relay-latching-switch-67-mhz-80w-28v-1.85mm-pe71s9020-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE71S9020 CAD Drawing

SPDT Electromechanical Relay Latching Switch, DC to 67 GHz, Up to 80W, 28V, 2M Lifecycles, Solder Terminal, 1.85mm

