




## Low Loss SPO-375 Rated Corrugated Coax Cable with Black PE Jacket Superflexible Outdoor Rated

## RF Cables Technical Data Sheet



### **Applications**

 Distributed Antenna Systems (DAS)

- Antenna Installations
- Small Cell

- Outdoor Applications
- Commination Tower Install

#### Description

SPO-375 low loss outdoor rated coax cable by Times Microwave is part of our full line of RF components available for same-day shipping. The SPO-375 coaxial cable features a low loss dielectric with an 83% velocity of propagation (VoP), BCCAL center conductor and a helically corrugated, copper outer conductor. These features combine to make the Times Microwave SPO-375 a superflexible, low PIM coax cable that is well suited for use as an antenna jumper cable, Distributed Antenna Systems (DAS), small cell, and other outdoor applications. The tough, black polyethylene jacket provides moisture and UV protection and is suitable for outdoor use.

Our datasheet specifications and drawing with dimensions for Times Microwave SPO-375 coax cable are shown below in this PDF. Whether the need is to provide a low PIM jumper connection, low PIM feeder cable or simply create a custom cable assembly configuration, Pasternack has the right SPO-375 cable assembly for the job. See our web site to find the right connector cable combination for your application.

### **Electrical Specifications**

| Description             | Minimum | Typical    | Maximum | Units        |
|-------------------------|---------|------------|---------|--------------|
| Frequency Range         | DC      |            | 6       | GHz          |
| Impedance               |         | 50         |         | Ohms         |
| Velocity of Propagation |         | 83         |         | %            |
| Passive Intermodulation |         |            | -158    | dBc          |
| Nominal Capacitance     |         | 24 [78.74] |         | pF/ft [pF/m] |
|                         |         |            |         |              |

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Low Loss SPO-375 Rated Corrugated Coax Cable with Black PE Jacket Superflexible Outdoor Rated SPO-375

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451 Sales@Pasternack.com • Techsupport@Pasternack.com

© 2019 Pasternack Enterprises All Rights Reserved





# Low Loss SPO-375 Rated Corrugated Coax Cable with Black PE Jacket Superflexible Outdoor Rated

# RF Cables Technical Data Sheet



| Description                    | F1     | F2  | <b>F3</b> | F4              | F5               | Units    |  |  |  |
|--------------------------------|--------|---|-----------|-----------------|------------------|----------|--|--|--|
| Frequency                      | 0.5    | 1   | 2         | 6               |                  | GHz      |  |  |  |
| Attenuation, Typ               | 2.96   | 4.33  | 6.23      | 11.62           |                  | dB/100ft |  |  |  |
|                                | 9.71   | 14.21   | 20.44     | 38.12           |                  | dB/100m  |  |  |  |
| nput Power (CW), Max           | 970    | 740   | 510       | 220             |                  | Watts    |  |  |  |
|                                |        |   |           |                 |                  |          |  |  |  |
| hanical Specification          | S      |   | 0         | 12 in [10.02 i  |                  |          |  |  |  |
| Weight                         |        | 0.43 in [10.92 mm]<br>0.132 lbs/ft [0.2 Kg/m] |           |                 |                  |          |  |  |  |
| Min. Bend Radius (Instal       | ation) |   |           |                 |                  |          |  |  |  |
| Construction Specificat        | tions  |   |           |                 |                  |          |  |  |  |
| Description                    |        | Material and Platin                           |           |                 | Diame            | ter      |  |  |  |
| Inner Conductor                | Cop    | per Clad Alumir                               | num1      | 0.11 in 2.79 mm |                  |          |  |  |  |
| Conductor Type                 | Solic  | 1   |           |                 |                  |          |  |  |  |
| Dielectric                     | Foar   | Foam PE                                       |           |                 | 0.27 in 6.86 mm  |          |  |  |  |
| Outer Conductor                | Cop    | per   |           | 0               | .38 in 9.65 mm   |          |  |  |  |
|                                | Corr   | ugated  |           |                 |                  |          |  |  |  |
| Jacket                         | PE, I  | Black   |           | 0               | .43 in [10.92 mm | ו]       |  |  |  |
|                                |        |   |           |                 |                  |          |  |  |  |
| ironmental Specifica           | tions  |   |           |                 |                  |          |  |  |  |
| Temperature<br>Operating Range |        |   | -/        | 0 to +85 deg    | C                |          |  |  |  |
|                                |        |   | _         |                 | 0                |          |  |  |  |
|                                |        |   |           |                 |                  |          |  |  |  |
|                                |        |   |           |                 |                  |          |  |  |  |
|                                |        |   |           |                 |                  |          |  |  |  |
|                                |        |   |           |                 |                  |          |  |  |  |
|                                |        |   |           |                 |                  |          |  |  |  |

Outdoor Rated SPO-375

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451 Sales@Pasternack.com • Techsupport@Pasternack.com

© 2019 Pasternack Enterprises All Rights Reserved





# Low Loss SPO-375 Rated Corrugated Coax Cable with Black PE Jacket Superflexible Outdoor Rated

## RF Cables Technical Data Sheet



Compliance Certifications (see product page for current document)

#### Plotted and Other Data Notes:

Low Loss SPO-375 Rated Corrugated Coax Cable with Black PE Jacket Superflexible Outdoor Rated from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Low Loss SPO-375 Rated Corrugated Coax Cable with Black PE Jacket Superflexible Outdoor Rated SPO-375

URL: https://www.pasternack.com/low-loss-corrugated-spo375-pe-jacket-spo-375-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

Low Loss SPO-375 Rated Corrugated Coax Cable with

Black PE Jacket Superflexible Outdoor Rated



4