



Mixers Technical Data Sheet

PE86X1031

Features

- Double Balanced Mixer Design
- LO & RF Frequency Range: 24 GHz to 32 GHz
- IF Frequency Range: DC to 8 GHz
- LO Drive Level +13 dBm
- Advanced MMIC Technology
- Conversion Loss: 10.5 dB typ
- · Port Isolations up to 40 dB typ

- Input IP3 Level: +18 dBm
- RF Input for P1dB: +13 dBm
- RF/LO Connectors: Female 2.92mm
- IF Connector: Female SMA
- Operating Temperature Range: -40°C to +85°C
- Designed to Meet MIL-STD-202 Environmental Test Conditions

Applications

- Electronic Warfare
- Point-to-Point Radios
- Point-to-Multipoint Radios
- VSAT

- Radar
- Space Systems
- · Test Instrumentation
- Sensors

- Tlecom Infrastructure
- Military End-Use

Description

The PE86X1031 is a broadband Double Balanced Mixer that operates across an RF and LO frequency range from 24 GHz to 32 GHz with an IF frequency range of DC to 8 GHz and supports an LO drive level of +13 dBm nominal. The design advanced MMIC technology and exhibits exceptional typical performance that includes Conversion Loss of 10.5 dB, RF to LO and LO to IF isolation levels up to 40 dB, and an input IP3 level of +18 dBm. The 50 ohm hybrid module does not require any external components or matching circuitry. The rugged compact package assembly supports female 2.92mm connectors on the RF and LO ports and a female SMA connector on the IF port, operates over a temperature range of -40°C to +85°C, and is designed to meet MIL-STD-202 environmental test conditions for Humidity, Shock, Vibration, and Altitude for high reliability.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
RF Frequency Range	24		32	GHz
LO Frequency Range	24		32	GHz
IF Frequency Range	DC		8	GHz
Impedance		50		Ohms
Conversion Loss		10.5	12.5	dB
LO to RF Isolation	32	38		dB
LO to IF Isolation	20	40		dB
RF to IF Isolation	20	30		dB
Input at 1dB Compression Point		+13		dBm
Input at 2nd Order Intercept Point		+40		dBm
Input at 3rd Order Intercept Point		+18		dBm
LO Input Power		+13		dBm

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Double Balanced Mixer Operating from 24 GHz to 32 GHz with an IF Range from DC to 8 GHz and LO Power of +13 dBm, 2.92mm PE86X1031

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (868) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Sales@Pastemack.com • Techsupport@Pastemack.com





Mixers Technical Data Sheet

PE86X1031

Absolute Maximum Rating

Parameter	Rating	Units
RF/IF Power	+13	dBm
LO Driver	+27	dBm
Operating Temperature	-40 to +85	°C
Storage Temperature	-65 to +150	°C



ESD Sensitive Material, Transport material in Approved ESD bags. Handle only in approved ESD Workstation.

Mechanical Specifications

Configuration

DesignDouble BalancedPackage TypeConnectorizedRF Connector2.92mm FemaleLO Connector2.92mm FemaleIF ConnectorSMA Female

Environmental Specifications

Humidity MIL-STD-202F, Method 103B, Condition B
Shock MIL-STD-202F, Method 213B, Condition B
Vibration MIL-STD-202F, Method 204D, Condition B
Altitude MIL-STD-202F, Method 105C, Condition B

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Double Balanced Mixer Operating from 24 GHz to 32 GHz with an IF Range from DC to 8 GHz and LO Power of +13 dBm, 2.92mm PE86X1031

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (868) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com






Mixers Technical Data Sheet

PE86X1031

Typical Performance Data





Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Double Balanced Mixer Operating from 24 GHz to 32 GHz with an IF Range from DC to 8 GHz and LO Power of +13 dBm, 2.92mm PE86X1031

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (868) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451


Sales@Pasternack.com • Techsupport@Pasternack.com





Mixers Technical Data Sheet

PE86X1031



Double Balanced Mixer Operating from 24 GHz to 32 GHz with an IF Range from DC to 8 GHz and LO Power of +13 dBm, 2.92mm from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Double Balanced Mixer Operating from 24 GHz to 32 GHz with an IF Range from DC to 8 GHz and LO Power of +13 dBm, 2.92mm PE86X1031

URL: https://www.pasternack.com/2.92mm-mixer-24-32-ghz-if-dc-8-ghz-pe86x1031-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE86X1031 CAD Drawing

Double Balanced Mixer Operating from 24 GHz to 32 GHz with an IF Range from DC to 8 GHz and LO Power of +13 dBm, 2.92mm

