

SMA Jack to BMA Plug 4 Hole Flange Mount Adapter

PE910025



Configuration

- SMA Jack Connector 1
- BMA Plug Connector 2
- 50 Ohms Impedance
- 4 Hole Flange Mount Method

Features

- Max VSWR of 1.25:1 up to 18 GHz
- SMA interface compliant with MIL-STD-348B
- BMA interface compliant with MIL-STD-348B

Applications

- Allows Connection Between Series
- General Purpose Test
- Rack Mounted Equipment

Description

Pasternack's PE910025 SMA jack to BMA plug 4 hole flange adapter is part of our full line of RF components available for same-day shipping. The SMA connector mates mechanically with commercially available 3.5mm and 2.92mm (K) connectors. Our SMA to BMA adapter has a jack to plug gender configuration built of durable stainless steel. PE910025 SMA jack to BMA plug adapter operates to 18 GHz. The Pasternack RF adapter provides excellent VSWR of 1.25:1 maximum. This SMA to BMA adapter allows for easier connections in tight spaces. This RF SMA to BMA 4 hole flange adapter allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

RF adapters are often used to enable connections between two connector types that would otherwise not mate. Certain adapter configurations can also be used to protect connectors on expensive equipment where the number of connect/disconnect cycles is high. An RF, microwave or millimeter wave adapter is connected to the equipment, and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Pasternack also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		18	GHz
Impedance	50			Ohms
VSWR	1.25:1			
Insertion Loss	0.212			dB
Operating Voltage (AC)	1,000			Vrms
Dielectric Withstanding Voltage (AC)	1,500			Vrms
Insulation Resistance	5,000			MOhms

Mechanical Specifications

Size

Length	0.80 in [20.19 mm]
Width	0.50 in [12.70 mm]
Height	0.50 in [12.70 mm]
Weight	0.01 lbs [3.58 g]

SMA Jack to BMA Plug 4 Hole Flange Mount Adapter



PE910025

Description	Connector 1	Connector 2
Polarity	Standard	Standard
Interface Specification	MIL-STD-348B	MIL-STD-348B
Mating Cycles, Min	500	1,000
Mating Torque	7 to 9.5 in-lbs 0.79 to 1.07 Nm	
Contact Captivation Axial Force, Min	6.1 lbs [2.77 kg]	6.1 lbs [2.77 kg]
Coupling Proof Torque	15 in-lbs [1.7 Nm]	

Material Specifications

Description	Connector 1		Connector 2	
	Material	Plating	Material	Plating
Type	SMA Jack		BMA Plug	
Insulation	PTFE		PTFE	
Outer Conductor	Beryllium Copper	Gold over Nickel over Copper	Beryllium Copper	Gold over Nickel over Copper
Body	Stainless Steel	Passivated	Stainless Steel	Passivated
Gasket	Silicone		Silicone	

Environmental Specifications

Temperature

Operating Range	-65 to +165 °C
Humidity	MIL-STD-202, Method 206
Thermal Shock	MIL-STD-202, Method 107, Condition B
Salt Spray	MIL-STD-202, Method 101, Condition B

Compliance Certifications (see product page for current document)

Plotted and Other Data

SMA Jack to BMA Plug 4 Hole Flange Mount Adapter from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Jack to BMA Plug 4 Hole Flange Mount Adapter PE910025](#)

URL: <https://www.pasternack.com/sma-jack-to-bma-plug-4-hole-flange-mount-adapter-pe910025.html>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE910025 CAD Drawing

SMA Jack to BMA Plug 4 Hole Flange Mount Adapter

