


## 2.92mm Female to 3.5mm Female Miter Right Angle Adapter



### PE91521

#### Configuration

- 2.92mm Female Connector 1
- 3.5mm Female Connector 2

- 50 Ohm
- Miter Right Angle Body Geometry

#### Features

- Max VSWR of 1.25:1 up to 34.5 GHz
- 4  $\mu$ m. Minimum contact plating
- Gold over Nickel Plated Beryllium Copper Contact

- The design of the 3.5mm adapters enables operation to an extended frequency range of 34.5GHz

#### Applications

- Allows Connection Between Series
- General Purpose Test

#### Description

Pasternack's PE91521 2.92mm female to 3.5mm female miter right angle adapter is part of our full line of RF components available for same-day shipping. The 2.92mm connector mates mechanically with commercially available SMA and 3.5mm connectors. Our 2.92mm to 3.5mm adapter has a female to female gender configuration built of durable stainless steel. PE91521 2.92mm female to 3.5mm female adapter operates to 34.5 GHz. The Pasternack RF adapter provides excellent VSWR of 1.25:1 maximum. This miter right angle 2.92mm to 3.5mm adapter allows for easier connections in tight spaces.

RF adapters are often used to enable connections between two connector types that would otherwise not mate. Certain adapter configurations can also be used to protect connectors on expensive equipment where the number of connect/disconnect cycles is high. An RF, microwave or millimeter wave adapter is connected to the equipment, and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Pasternack also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

#### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		34.5	GHz
Impedance		50 Ohm		
VSWR			1.25:1	

#### Mechanical Specifications

##### Size

Length	0.62 in [15.80 mm]
Width	0.22 in [5.49 mm]
Height	0.63 in [15.90 mm]
Weight	0.30 lbs [136.08 g]

Description	Connector 1	Connector 2
Type	2.92mm Female	3.5mm Female
Polarity	Standard	Standard

## 2.92mm Female to 3.5mm Female Miter Right Angle Adapter



**PE91521**

### Material Specifications

Description	Connector 1		Connector 2	
	Material	Plating	Material	Plating
Type	2.92mm Female		3.5mm Female	
Contact	Beryllium Copper	Gold over Nickel 4 μin. Minimum	Beryllium Copper	Gold over Nickel 4 μin. Minimum
Insulation	Oxide-Noryl		Oxide-Noryl	
Outer Conductor	Passivated Stainless Steel		Passivated Stainless Steel	
Body	Passivated Stainless Steel		Passivated Stainless Steel	

### Compliance Certifications (see [product page](#) for current document)

2.92mm Female to 3.5mm Female Miter Right Angle Adapter from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.92mm Female to 3.5mm Female Miter Right Angle Adapter PE91521](#)

URL: <https://www.pasternack.com/2.92mm-female-3.5mm-female-miter-right-angle-adapter-pe91521-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

# PE91521 CAD Drawing

## 2.92mm Female to 3.5mm Female Miter Right Angle Adapter



ZONE		REV	B
DESCRIPTION		ECO-12455	
DATE		09/27/2023	
CHANGED BY		DZINN	
APPROVED		SELLIS	

<b>PASTERNAK</b> an INFINITB brand		INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5 SCALE: NONE SHEET: 1 OF 1
Website: <a href="http://www.Pasternack.com">www.Pasternack.com</a> Phone: 1.866.727.8376   1.949.261.1920		DESCRIPTION: 2.92mm FEMALE TO 3.5mm FEMALE RIGHT ANGLE ADAPTER
UNLESS OTHERWISE SPECIFIED, LEADING DIMENSIONS ARE IN INCHES. DIMENSIONS IN [ ] ARE MILLIMETERS.	<b>TOLERANCES:</b> .X = ±.2 [5] .XX = ±.02 [0.5] .XXX = ±.005 [0.13]	<b>FRACTIONS</b> ± 1/32 <b>ANGLES ± 1°</b>
ALL DIMENSIONS ARE FOR REFERENCE ONLY. UNDIMENSIONED NON-CRITICAL FEATURES MAY VARY IN SIZE AND LOCATION. COLORS MAY VARY.	CABLE LENGTH TOLERANCES: <12 [305] ±.60 [15.24] = ±.2 [5] / -0 >12 [305] ±.60 [15.24] = ±.2 [5] / -0 >40 [1024] ±.120 [3048] = ±.4 [102] / -0 >120 [3048] ±.300 [7620] = ±.93 [23] / -0	SIZE: A CAGE CODE: 53919 DRAWN BY: DZINN ITEM NO.: PE91521

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

PE DS Rev-D4-A4326