

75 Ohm SMC Jack to SMC Jack Adapter



TECHNICAL DATA SHEET

PE9227

75 Ohm SMC Jack to SMC Jack Adapter

Co	nfia	uration

Connector 1SMC JackImpedance 175 OhmsConnector 2SMC JackImpedance 275 OhmsAdapter DesignStandardBody StyleStraight

Mechanical Specifications

Temperature

Operating Range,deg C -65 to +165

Size

 Length, in [mm]
 0.688 [17.48]

 Width/Dia., in [mm]
 0.344 [8.74]

Connector 1

Type SMC Jack
Inner Conductor Material and Plating Gold
Inner Conductor Plating Specification MIL-G-45204
Body Material and Plating Brass, Nickel
Dielectric Type Teflon

Connector 2

Type SMC Jack
Inner Conductor Material and Plating Gold
Inner Conductor Plating Specification MIL-G-45204
Body Material and Plating Brass, Nickel
Dielectric Type Teflon

Compliance Certifications (visit www.Pasternack.com for current document)

RoHS Compliant Yes

Plotted and Other Data

Notes: Values at 25 °C, sea level

URL: http://www.pasternack.com/smc-jack-smc-jack-straight-adapter-pe9227-p.aspx

75 Ohm SMC Jack to SMC Jack Adapter from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451 Sales@Pasternack.com • Techsupport@Pasternack.com

PE9227 CAD Drawing 75 Ohm SMC Jack to SMC Jack Adapter

