



SMA Female to SMA Female Cable 24 Inch Length Using RG223 Coax

RF Cable Assemblies Technical Data Sheet

PE33254-24

Configuration

- Connector 1: SMA Female
- Connector 2: SMA Female
- Cable Type: RG223

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		12.4	GHz
VSWR			1.4:1	
Velocity of Propagation		66		%
Capacitance		30.8 [101.05]		pF/ft [pF/m]
Operating Voltage (AC)			500	Vrms

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.5	1	2.5	5	12.4	GHz
Insertion Loss (Max.)	0.38	0.47	0.64	0.87		dB
VSWR (Max.)	1.4:1	1.4:1	1.4:1	1.4:1	1.4:1	
Return Loss (Max.)	15.56	15.563	15.563	15.563	15.563	dB

Mechanical Specifications

Cable Assembly

Length	24 in [609.6 mm]
Diameter	0.25 in [6.35 mm]
Weight	0.092 lbs [41.73 g]

Cable

Cable Type	RG223
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper, Silver
Dielectric Type	PE
Number of Shields	2
Shield Layer 1	Silver Plated Copper Braid

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Female to SMA Female Cable 24 Inch Length Using RG223 Coax PE33254-24](#)



SMA Female to SMA Female Cable 24 Inch Length Using RG223 Coax

RF Cable Assemblies Technical Data Sheet

PE33254-24

Shield Layer 2
 Jacket Material
 Jacket Diameter

Silver Plated Copper Braid
 PVC, Black
 0.21 in [5.33 mm]

One Time Minimum Bend Radius

1 in [25.4 mm]

Connectors

Description	Connector 1	Connector 2
Type	SMA Female	SMA Female
Impedance	50 Ohms	50 Ohms
Contact Material and Plating	Beryllium Copper, Gold	Beryllium Copper, Gold
Contact Plating Specification	50 μ in. minimum.	50 μ in. minimum.
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification	100 μ in. minimum.	100 μ in. minimum.

Compliance Certifications

(visit www.Pasternack.com for current document)

For RoHS Compliant version, use PE33254LF-24. Contact Pasternack if product cannot be found.
 REACH Compliant

12/19/2011

Plotted and Other Data

Notes:

- Values at 25°C, sea level.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Female to SMA Female Cable 24 Inch Length Using RG223 Coax PE33254-24](#)




SMA Female to SMA Female Cable 24 Inch Length Using RG223 Coax

RF Cable Assemblies Technical Data Sheet

PE33254-24

How to Order

Part Number Configuration:



Example: PE33254-12 = 12 inches long cable
PE33254-100cm = 100 cm long cable

SMA Female to SMA Female Cable 24 Inch Length Using RG223 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Female to SMA Female Cable 24 Inch Length Using RG223 Coax PE33254-24](#)

URL: <http://www.pasternack.com/sma-female-sma-female-rg223u-cable-assembly-pe33254-24-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE33254-24 CAD Drawing

SMA Female to SMA Female Cable 24 Inch Length Using RG223 Coax



NOTES:
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES [mm].
4. LENGTH TOLERANCE IS $\pm 1.5\%$ OR 3/8", WHICHEVER IS GREATER.

DWG TITLE	PE33254
FSCM NO.	53919

PASTERNAK® THE ENGINEER'S RF SOURCE	Pasternack Enterprises, Inc. P.O. Box 16759 Irvine CA 92623 Phone: (949) 261-1920 Fax: (949) 261-7451 Website: www.pasternack.com E-Mail: sales@pasternack.com	CAD FILE	120115	SCALE	N/A	SIZE	A	2233
--	---	----------	--------	-------	-----	------	---	------