

# Exposed Dipole Antenna with 400 to 470 MHz, 3 dBi, N Female, Vertical Polarization, 1 Port, 1.5 VSWR



### **Antennas Technical Data Sheet**

## PEANED1015

#### **Features**

- Frequency coverage for 400 MHz to 470 MHz with Type N Female connector and gain 3 dBi / 0.85 dBd antennas
- Multiple exposed dipoles can be mouted on a mast for best performance
- · Feild adjustable radition patterns with 100W max input

### **Applications**

- Outdoor point-to-point (PtP) or point-to-multipoint (PtMP) applications
- UHF radio applications supported with Trunking for two-way radio communications
- Public Safety / Emergency services / Marine communications / Rail road communications

power per port

- · Easy and quick time to installations with U-Bolt mounts
- Industrially tuned folded dipole allows plug and play
- Weather and corrision free made of high-grade aluminum alloys
- · Vertical Polarization
- · Tetra and P-25 Applications exclusively supported
- Land Mobile Radio (LMR) and Private Mobile Radio (PMR)
- Fixed and mobile services for paging/voice/data in full duplex and half duplex mode

#### Description

Pasternack's PEANED1014 3 dBi Exposed dipole antenna, with N female connector, is an economical yet high-performance antenna designed for high-power applications. The Exposed dipole antenna's beamwidth can be adjusted according to applications by fixing dipoles at certain heights and directions. This high gain 3 dBi antenna transmits high-power signals, increasing the signal strength and thus providing improved coverage, better-broadcast control, and faster speed. This Exposed dipole antenna can output frequencies from 400 to 470 MHz, which is useful for military communications, trunking, public safety, industrial communication, and amateur radio applications.

Pasternack's Exposed dipole antenna uses vertical polarization to transmit signals, thus reducing interference and performing better at lower heights. All components of this 3 dBi antenna are DC grounded for lightning protection, rugged outdoor design, and have a high-power handling capacity. The Exposed dipole antenna has 1 port to connect an external circuit with 100W maximum input power per port.

This Pasternack's 400 to 470 MHz VHF/UHF antenna is one of the simplest and most widely used antenna producing radiation patterns like that of an electric dipole. PEANED1014 Exposed dipole antenna is a dipole stand-alone made of aluminum alloy, and thus packaging, transportation, and installation become easier. It has a 1.5 VSWR that results in the best power transfer and reduced losses. It comes with a threaded and weatherproof N female connector type which ensuring a reliable physical connection and can be fixed on a pole using the U-bolt brackets that come with the antenna.

PEANED1014 antenna with a 3 dBi maximum gain is ideal for LMR, military, airports, construction, mining, commercial applications, and radio users. This PEANED1014 Exposed dipole antenna from Pasternack comes in compact packaging for lower shipping costs. Pasternack's 400 to 470 MHz, 3 dBi Exposed dipole antenna with a N female connector is in stock and ready to ship the same day. Contact Pasternack's knowledgeable and friendly technical support and sales staff for your answers on antennas or other products.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Exposed Dipole Antenna with 400 to 470 MHz, 3 dBi, N Female, Vertical Polarization, 1 Port, 1.5 VSWR PEANED1015

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451



# Exposed Dipole Antenna with 400 to 470 MHz, 3 dBi, N Female, Vertical Polarization, 1 Port, 1.5 VSWR



### **Antennas Technical Data Sheet**

PEANED1015

Configuration

Design Dipole Band Type Single

Radiation Pattern Omni Directional

Polarization Vertical
Connector Type N Female

Number of Ports

Lightning Protection DC Ground

**Electrical Specifications** 

Description	Minimum	Typical	Maximum	Units
Frequency Range	400		470	MHz
Input VSWR			1.5:1	
Impedance		50	Ye. 19	Ohms
Gain			3	dBi
Input Power			100	Watts

**Mechanical Specifications** 

Radome Material Aluminum Alloy

Size

 Overall Length
 12.5 in [317.5 mm]

 Width
 12 in [304.8 mm]

 Height
 2 in [50.8 mm]

 Weight
 10.56 lbs [4.79 kg]

**Environmental Specifications** 

**Temperature** 

Operating Range -40 to +80 deg C

Compliance Certifications (see product page for current document)

**Plotted and Other Data** 

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Exposed Dipole Antenna with 400 to 470 MHz, 3 dBi, N Female, Vertical Polarization, 1 Port, 1.5 VSWR PEANED1015



# Exposed Dipole Antenna with 400 to 470 MHz, 3 dBi, N Female, Vertical Polarization, 1 Port, 1.5 VSWR



### **Antennas Technical Data Sheet**

### PEANED1015

Exposed Dipole Antenna with 400 to 470 MHz, 3 dBi, N Female, Vertical Polarization, 1 Port, 1.5 VSWR from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Exposed Dipole Antenna with 400 to 470 MHz, 3 dBi, N Female, Vertical Polarization, 1 Port, 1.5 VSWR PEANED1015

URL: https://www.pasternack.com/antenna-400-470-mhz-n-type-female-connector-peaned1015-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

# **PEANED1015 CAD Drawing**

Exposed Dipole Antenna with 400 to 470 MHz, 3 dBi, N Female, Vertical Polarization, 1 Port, 1.5 VSWR

