

## M39029 Socket Size 8 D38999 Contact for 0.085 Cable



### PEMACTRF8S10

#### Configuration

- Push-on M39029 Socket Connector
- MIL-STD: M39029/59
- 50 Ohms
- Connector Interface Types: D38999 Series I, D38999 Series III, D38999 Series IV, 0.085 Cable, RG405 Cable, M17/133-RG405 Cable
- Contact Size: 8

#### Features

- Fits any MIL-DTL-38999 size 8 insert
- Superior high frequency performance
- Blindmate connections
- Made from high quality materials giving a robust mechanical design
- Solderless inner connection to reduce assembly cost

#### Applications

- Civilian and Military Aerospace
- High Reliability Installations
- Harsh Environments

#### Description

The PEMACTRF8S10 from Pasternack is a size 8 M39029 socket contact that is designed for D38999 Series I, D38999 Series III, and D38999 Series IV military type connector shells. This RF coaxial contact has a solder/non-solder contact attachment method and is built to offer superior performance in demanding applications that require high-frequency data transmission. The M39029 coax contact comes with an impedance of 50 Ohms and a maximum VSWR of 1.35.

Our RF contact has a maximum frequency of 3 GHz. This M39029 RF contact is made up of beryllium copper material with gold plating. The PEMACTRF8S10 coax contact has a PTFE dielectric type and a dielectric withstanding voltage of 1000 Vrms. Our M39029 socket contact has a maximum insertion loss of 0.191 dB.

Pasternack's RF contact has an inner conductor and outer conductor made of beryllium copper. These RF coax contacts are specifically engineered to minimize signal loss and crosstalk, providing excellent impedance matching and reducing VSWR. Our M39029 socket contact can operate at temperatures ranging from -65 to 125 degrees C.

PEMACTRF8S10 RF contact is part of more than one million RF, microwave, and millimeter wave parts in stock at Pasternack. This PEMACTRF8S10 coax contact is ready to buy and can be shipped worldwide the same business day as ordered from our warehouse in the United States. Pasternack maintains M39029 socket RF contacts in various sizes and configurations, which allows them to be customized to meet the specific requirements of different applications. For further information on similar products, our expert technical support and trained sales team can get you the ideal RF contact as per your requirements.

#### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		3	GHz
VSWR			1.35:1	
Insertion Loss			0.191	dB
Operating Voltage (AC)			250	Vrms
Dielectric Withstanding Voltage (AC)			1,000	Vrms
Insulation Resistance	5,000			MOhms

M39029 Socket Size 8 D38999 Contact for 0.085 Cable



**PEMACTRF8S10**

**Electrical Specifications**

Description	Minimum	Typical	Maximum	Units
Impedance		50		Ohms

**Installation**

Description	Specification
Insertion Tool	No tool required
Extraction Tool	M81969/14-06

**Mechanical Specifications**

Mating Cycles	500 Cycles
<b>Size</b>	
Length	1.187 in [30.15 mm]
Width	0.315 in [8 mm]
Height	0.315 in [8 mm]
Weight	0.01 lbs [4.54 g]

**Material Specifications**

Description	Material	Plating
Contact	Beryllium Copper	Gold
Insulation	PTFE	
Outer Conductor	Beryllium Copper	Gold
Body	Beryllium Copper	Gold

**Environmental Specifications**

<b>Temperature</b>	
Operating Range	-65 to +125 deg C
Shock	MIL-STD-202, Method 213, Condition I
Vibration	MIL-STD-202, Method 204, Condition D
Salt Spray	MIL-STD-202, Method 101, Test Condition B

**Compliance Certifications** (see [product page](#) for current document)

**Plotted and Other Data**

Notes:

## M39029 Socket Size 8 D38999 Contact for 0.085 Cable



### PEMACTRF8S10

M39029 Socket Size 8 D38999 Contact for 0.085 Cable from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [M39029 Socket Size 8 D38999 Contact for 0.085 Cable PEMACTRF8S10](https://www.pasternack.com/m39029-socket-size-8-d38999-contact-for-0.085-cable-pemactrf8s10)

URL: <https://www.pasternack.com/m39029-socket-size-8-d38999-contact-for-0.085-cable-pemactrf8s10-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

# PEMACTRF8S10 CAD Drawing

M39029 Socket Size 8 D38999 Contact for 0.085 Cable

