

WR-15 Waveguide Standard Gain Horn Antenna Operating from 50 GHz to 75 GHz with a Nominal 25 dBi Gain with UG-385/U-Mod Round Cover Flange



Gain Horns Technical Data Sheet

PEWAN1012

Features

- · Rectangular Waveguide Interface
- 50 GHz to 75 GHz

Applications

- · Antenna Measurements
- · Wireless Communication

- 25 dBi Nominal Gain
- UG-385/U-Mod Round Cover Flange
- Laboratory Use
- Microwave Radio Systems

Description

Waveguide standard gain horn antennas are used in a wide variety of applications due to their high power handling capability, low loss, high directivity, and near constant electrical performance across a broad bandwidth. Pasternack's PEWAN1012 WR-15 waveguide standard gain horn antenna operating from 50 GHz to 75 GHz with a nominal 25 dBi gain is part of our full line of RF components available for same-day shipping. This Pasternack pyramidal horn antenna has a gold plated brass body and a precision tolerance UG-385/U-Mod round cover flange. The PEWAN1012 WR-15 waveguide standard gain horn antenna offers low gain variation across its operating frequency range.

Configuration

Design

Pattern Polarization WR-15 Standard Gain Horn

Directional Linear

Electrical Specifications

Minimum	Typical	Maximum	Units
50		75	GHz
	25		dBi
24			dBi
	10		Degrees
	9		Degrees
	1.15:1		
	50	50 25 24 10 9	50 75 25 24 10 9

Mechanical Specifications

Size

 Length
 4.09 in [103.89 mm]

 Width
 1.704 in [43.28 mm]

 Height
 1.419 in [36.04 mm]

 Weight
 0.098 lbs [44.45 g]

Waveguide Interface

Waveguide Size WR-15 Flange Type Round Cover

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: WR-15 Waveguide Standard Gain Horn Antenna Operating from 50 GHz to 75 GHz with a Nominal 25 dBi Gain with UG-385/U-Mod Round Cover Flange PEWAN1012

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com



WR-15 Waveguide Standard Gain Horn Antenna Operating from 50 GHz to 75 GHz with a Nominal 25 dBi Gain with UG-385/U-Mod Round Cover Flange



Gain Horns Technical Data Sheet


PEWAN1012

Flange Designation Body Material and Plating UG-385/U-Mod Brass, Gold

Compliance Certifications (see product page for current document)

Plotted and Other Data

Typical Performance Data



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: WR-15 Waveguide Standard Gain Horn Antenna Operating from 50 GHz to 75 GHz with a Nominal 25 dBi Gain with UG-385/U-Mod Round Cover Flange PEWAN1012

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451




WR-15 Waveguide Standard Gain Horn Antenna Operating from 50 GHz to 75 GHz with a Nominal 25 dBi Gain with UG-385/U-Mod Round Cover Flange



Gain Horns Technical Data Sheet

PEWAN1012



WR-15 Waveguide Standard Gain Horn Antenna Operating from 50 GHz to 75 GHz with a Nominal 25 dBi Gain with UG-385/U-Mod Round Cover Flange from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: WR-15 Waveguide Standard Gain Horn Antenna Operating from 50 GHz to 75 GHz with a Nominal 25 dBi Gain with UG-385/U-Mod Round Cover Flange PEWAN1012

URL: https://www.pasternack.com/wr-15-waveguide-gain-horn-antenna-25dbi-ug-385-mod-round-flange-pewan1012-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PEWAN1012 CAD Drawing

WR-15 Waveguide Standard Gain Horn Antenna Operating from 50 GHz to 75 GHz with a Nominal 25 dBi Gain with UG-385/U-Mod Round Cover Flange

