



Technical Data Sheet

PEWAN187-10NF

Features

- 3.95 GHz to 5.85 GHz
- WR-187 Waveguide Band

- 10 dBi Nominal Gain
- N Female Connector

Applications

- Antenna Measurements
- Wireless Communication
- Laboratory Use

- · Microwave Radio Systems
- · Radome Testing
- Automotive Antenna Test

Solutions

- · Radar Cross Section
- · Satellite Antenna Testing

Description

The PEWAN187-10NF standard gain horn antenna (also known as waveguide horn) from Pasternack is part of our comprehensive selection of waveguide antennas. This standard gain horn is mated with a WR-187 to N Female waveguide to coaxial adapter and operates from 3.95 GHz to 5.85 GHz.

Our PEWAN187-10NF standard gain horn antenna has a nominal gain of 10 dBi with a Horizontal and Vertical HPBW (Half Power Beam Width) of 52.1 and 51.6 degrees respectively. Pasternack's N Female to WR-187 standard gain horns are available in 10, 15 and 20 dBi models with pyramidal shape and connectorized input.

Waveguide antennas, such as the PEWAN187-10NF are used in a wide variety of applications due to the high-power handling capability, low loss, high directivity, and near constant electrical performance. Our WR-187 waveguide antennas with N Female interface is part of over 40,000 RF, microwave and millimeter wave components from Pasternack available worldwide and Ship same day.

Configuration

Design Coaxial Interface WR-187 Standard Gain Horn

N Female

Electrical Specifications

Minimum	Typical	Maximum	Units
3.95		5.85	GHz
	10		dBi
	52.1		Degrees
	51.6		Degrees
		1.3:1	
		3.95 10 52.1	3.95 5.85 10 52.1 51.6

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: WR-187 Standard Gain Horn with 10 dBi gain, N Female connector PEWAN187-10NF

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451





Technical Data Sheet

PEWAN187-10NF

Mechanical Specifications

Size

 Length
 5.266 in [133.76 mm]

 Width
 2.845 in [72.26 mm]

 Height
 2.284 in [58.01 mm]

 Weight
 0.585 lbs [265.35 g]

RF Connector

Type N Female

Waveguide Interface

Waveguide Size WR-187

Environmental Specifications

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:






Technical Data Sheet

PEWAN187-10NF

Typical Performance Data








Technical Data Sheet

PEWAN187-10NF








Technical Data Sheet

PEWAN187-10NF








Technical Data Sheet

PEWAN187-10NF



WR-187 Standard Gain Horn with 10 dBi gain, N Female connector from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: WR-187 Standard Gain Horn with 10 dBi gain, N Female connector PEWAN187-10NF

URL: https://www.pasternack.com/wr-187-waveguide-standard-gain-horn-antenna-10-dbi-n-pewan187-10nf-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PEWAN187-10NF CAD DrawingWR-187 Standard Gain Horn with 10 dBi gain, N Female connector

