



SMA Male to SMA Male Cable 6 Inch Length Using RG174 Coax

RF Cable Assemblies Technical Data Sheet

PE3353-6

Configuration

- Connector 1: SMA Male
- Connector 2: SMA Male
- Cable Type: RG174

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		1,000	MHz
VSWR			1.4:1	
Velocity of Propagation		66		%
Capacitance		30.8 [101.05]		pF/ft [pF/m]

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	50	100	250	500	1,000	MHz
Insertion Loss (Max.)	0.22	0.24	0.27	0.31	0.36	dB
VSWR (Max.)	1.4:1	1.4:1	1.4:1	1.4:1	1.4:1	
Return Loss (Max.)	15.56	15.563	15.563	15.563	15.563	dB

Mechanical Specifications

Cable Assembly

Length	6 in [152.4 mm]
Diameter	0.312 in [7.92 mm]
Weight	0.017 lbs [7.71 g]

Cable

Cable Type	RG174
Impedance	50 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper Clad Steel
Dielectric Type	PE (LD)
Number of Shields	1
Shield Layer 1	Tinned Copper Braid

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male to SMA Male Cable 6 Inch Length Using RG174 Coax PE3353-6](#)



SMA Male to SMA Male Cable 6 Inch Length Using RG174 Coax

RF Cable Assemblies Technical Data Sheet

PE3353-6

 Jacket Material
 Jacket Diameter

 PVC, Black
 0.1 in [2.54 mm]

Connectors

Description	Connector 1	Connector 2
Type	SMA Male	SMA Male
Specification	MIL-STD-348A	MIL-STD-348A
Impedance	50 Ohms	50 Ohms
Contact Material and Plating	Brass, Gold	Brass, Gold
Contact Plating Specification	30 μ in. Minimum	30 μ in. Minimum
Dielectric Type	PTFE	PTFE
Coupling Nut Material and Plating	Brass, Nickel	Brass, Nickel
Coupling Nut Plating Specification	100 μ in. Minimum	100 μ in. Minimum
Hex Size	5/16 in	5/16 in
Torque	5 in-lbs [0.57 Nm]	5 in-lbs [0.57 Nm]
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification	100 μ in. Minimum	100 μ in. Minimum

Environmental Specifications

Temperature

Operating Range

-40 to +80 deg C

Compliance Certifications (visit www.Pasternack.com for current document)

For RoHS Compliant version, use PE3353LF-6. Contact Pasternack if product cannot be found.

REACH Compliant

12/19/2011

Plotted and Other Data

Notes:

- Values at 25°C, sea level.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male to SMA Male Cable 6 Inch Length Using RG174 Coax PE3353-6](#)




SMA Male to SMA Male Cable 6 Inch Length Using RG174 Coax

RF Cable Assemblies Technical Data Sheet

PE3353-6

How to Order

Part Number Configuration:



Example: PE3353-12 = 12 inches long cable
PE3353-100cm = 100 cm long cable

SMA Male to SMA Male Cable 6 Inch Length Using RG174 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male to SMA Male Cable 6 Inch Length Using RG174 Coax PE3353-6](#)


URL: <http://www.pasternack.com/sma-male-sma-male-rg174au-cable-assembly-pe3353-6-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3353-6 CAD Drawing

SMA Male to SMA Male Cable 6 Inch Length Using RG174 Coax

Standard Lengths	
-12	12"
-24	24"
-36	36"
-48	48"
-60	60"
-XXX Custom Length in Inches	



PE PASTERNACK®

Pasternack Enterprises, Inc.
P.O. Box 16759 | Irvine | CA | 92623

Phone: (949) 261-1920 | Fax: (949) 261-7451

Website: www.pasternack.com | E-Mail: sales@pasternack.com

DWG TITLE

PE3353-XX

NOTES:
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES [mm].
4. LENGTH TOLERANCE IS $\pm 1.5\%$ OR $3/8"$, WHICHEVER IS GREATER.

REV. A	FSCM NO.	53919	CAD FILE	021308	SCALE N/A	SIZE A	127
--------	----------	-------	----------	--------	-----------	--------	-----