



Dual Directional 40 dB SMA Coupler From 800 MHz to 2.5 GHz Rated To 200 Watts

TECHNICAL DATA SHEET

PE2CP1014

Configuration

Connector 1	SMA Female
Connector 2	SMA Female
Coupled Connectors	SMA Female
Design	Dual Directional Coupler

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	0.8		2.5	GHz
Directivity	20			dB
Impedance		50		Ohms
Insertion Loss			0.25	dB
Input Power			200	Watts
Input VSWR			1.25:1	
Coupling Value	40			dB
Coupling Tolerance			± 1	dB
Coupling Flatness			±0.5	dB

Mechanical Specifications

Temperature	
Operating Range	+85 to -55 deg C
Size	
Length	2.5 in [63.5 mm]
Width/Dia.	0.57 in [14.48 mm]
Height	1.3 in [33.02 mm]
Housing Material and Plating	Aluminum Alloy, Chem Film

Connectors

Description	Connector 1	Connector 2	Coupled Connectors
Type	SMA Female	SMA Female	SMA Female

Compliance Certifications

 (visit www.Pasternack.com for current document)

RoHS Compliant

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Dual Directional 40 dB SMA Coupler From 800 MHz to 2.5 GHz Rated To 200 Watts PE2CP1014](#)



Dual Directional 40 dB SMA Coupler From 800 MHz to 2.5 GHz Rated To 200 Watts

TECHNICAL DATA SHEET

PE2CP1014

Dual Directional 40 dB SMA Coupler From 800 MHz to 2.5 GHz Rated To 200 Watts from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Dual Directional 40 dB SMA Coupler From 800 MHz to 2.5 GHz Rated To 200 Watts PE2CP1014](#)

URL: <http://www.pasternack.com/dual-directional-40-db-sma-coupler-800-mhz-2.5-ghz-200-watts-pe2cp1014-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE2CP1014 CAD Drawing

Dual Directional 40 dB SMA Coupler From 800 MHz to 2.5 GHz Rated To 200 Watts



INPUT	OUTPUT	FORWARD COUPLING	REFLECTED COUPLING
J1	J2	J3	J4
J2	J1	J4	J3

NOTES:
 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
 3. DIMENSIONS ARE IN INCHES [mm].

PE2CP1014

DWG TITLE

TOLERANCE	.XX	$\pm .02$
	.XX	$\pm .005$
	ANG.	$\pm 1/2$

* THESE DIMENSIONS AND TOLERANCES
 SUPERSEDE NOTE #1 ON TITLE BLOCK.

PASTERNACK
 THE ENGINEER'S RF SOURCE

Pasternack Enterprises, Inc.
 P.O. Box 16759 | Irvine | CA | 92623

Phone: (949) 261-1920 | Fax: (949) 261-7451

Website: www.pasternack.com | E-Mail: sales@pasternack.com

FSCM NO.	CAD FILE	SCALE	SIZE	REV
53919	041015	N/A	A	2233