



## SC Male to SC Male Cable 12 Inch Length Using RG141 Coax

### RF Cable Assemblies Technical Data Sheet

PE34439-12

#### Configuration

- Connector 1: SC Male
- Connector 2: SC Male
- Cable Type: RG141

#### Features

- PTFE (FG) Jacket

#### Applications

- General Purpose
- Laboratory Use

#### Description

Pasternack's PE34439-12 SC male to SC male 12 inch cable using RG141 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack SC to SC cable assembly has a male to male gender configuration with 50 ohm flexible RG141 coax.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

#### Electrical Specifications

| Description  | Minimum | Typical      | Maximum | Units        |
|--------------|---------|--------------|---------|--------------|
| Capacitance  |         | 29.4 [96.46] |         | pF/ft [pF/m] |
| Jacket Spark |         |              | 2,000   | Vrms         |

#### Mechanical Specifications

##### Cable Assembly

|          |                     |
|----------|---------------------|
| Length*  | 12 in [304.8 mm]    |
| Diameter | 0.8 in [20.32 mm]   |
| Weight   | 0.173 lbs [78.47 g] |

##### Cable

|                                      |                           |
|--------------------------------------|---------------------------|
| Cable Type                           | RG141                     |
| Impedance                            | 50 Ohms                   |
| Inner Conductor Type                 | Solid                     |
| Inner Conductor Material and Plating | Copper Clad Steel, Silver |
| Dielectric Type                      | PTFE                      |
| Number of Shields                    | 1                         |

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SC Male to SC Male Cable 12 Inch Length Using RG141 Coax PE34439-12](#)



SC Male to SC Male Cable 12 Inch Length Using RG141 Coax

RF Cable Assemblies Technical Data Sheet

PE34439-12

|                 |                      |
|-----------------|----------------------|
| Shield Layer 1  | Silver Plated Copper |
| Jacket Material | PTFE (FG), Beige     |
| Jacket Diameter | 0.19 in [4.83 mm]    |

**Connectors**

| Description                   | Connector 1   | Connector 2   |
|-------------------------------|---------------|---------------|
| Type                          | SC Male       | SC Male       |
| Specification                 | MIL-C-39012   | MIL-C-39012   |
| Impedance                     | 50 Ohms       | 50 Ohms       |
| Contact Material and Plating  | Silver        | Silver        |
| Contact Plating Specification | QQ-S-365      | QQ-S-365      |
| Dielectric Type               | Teflon        | Teflon        |
| Body Material and Plating     | Brass, Nickel | Brass, Nickel |

Mechanical Specification Notes:

\*All cable assemblies have a length tolerance of 1.5% or  $\pm 3/8$ ", whichever is greater.

**Compliance Certifications** (see [product page](#) for current document)

**Plotted and Other Data**

Notes:

- Values at 25°C, sea level.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SC Male to SC Male Cable 12 Inch Length Using RG141 Coax PE34439-12](#)



## SC Male to SC Male Cable 12 Inch Length Using RG141 Coax

### RF Cable Assemblies Technical Data Sheet

PE34439-12

#### How to Order

Part Number Configuration:

PE34439

- xx

uu

Unit of Measure:

cm = Centimeters

<blank> = Inches

Length

Base Number

Example: PE34439-12 = 12 inches long cable  
PE34439-100cm = 100 cm long cable

SC Male to SC Male Cable 12 Inch Length Using RG141 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SC Male to SC Male Cable 12 Inch Length Using RG141 Coax PE34439-12](https://www.pasternack.com/sc-male-sc-male-rg141au-cable-assembly-pe34439-12-p.aspx)


URL: <https://www.pasternack.com/sc-male-sc-male-rg141au-cable-assembly-pe34439-12-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

# PE34439-12 CAD Drawing

## SC Male to SC Male Cable 12 Inch Length Using RG141 Coax

| REVISIONS |                 |          |          |
|-----------|-----------------|----------|----------|
| REV.      | DESCRIPTION     | DATE     | APPROVED |
| A         | INITIAL RELEASE | 07/23/19 | S. ELLIS |



|  |                                       |             |           |         |       |       |           |       |             |   |   |
|--|---------------------------------------|-------------|-----------|---------|-------|-------|-----------|-------|-------------|---|---|
| <p>UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [ ] ARE MILLIMETERS</p> <p>TOLERANCES:</p> <table border="0"> <tr> <td>X±.2</td> <td>[5.08]</td> <td>FRACTIONS</td> </tr> <tr> <td>.XX±.01</td> <td>[.25]</td> <td>±.132</td> </tr> <tr> <td>.XXX±.005</td> <td>[.13]</td> <td>ANGLES ± 1°</td> </tr> </table> <p>ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.</p> <p>THIRD-ANGLE PROJECTION</p> | X±.2                                  | [5.08]      | FRACTIONS | .XX±.01 | [.25] | ±.132 | .XXX±.005 | [.13] | ANGLES ± 1° | <p><b>PE PASTERNAK</b><br/>an INFINITO brand</p> <p>Pasternack Enterprises, Inc.<br/>P.O. Box 16759, Irvine, CA 92623.<br/>Phone: 1.949.261.1920   1.866.727.8376<br/>Fax: 1.949.261.7451<br/>www.pasternack.com   e-mail: sales@pasternack.com</p> | <p>THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF PASTERNAK CORPORATION. ALL RIGHTS RESERVED.</p> |
|  | X±.2                                  | [5.08]      | FRACTIONS |         |       |       |           |       |             |   |   |
| .XX±.01  | [.25]                                 | ±.132       |           |         |       |       |           |       |             |   |   |
| .XXX±.005  | [.13]                                 | ANGLES ± 1° |           |         |       |       |           |       |             |   |   |
| <p>SIZE: A</p> <p>CAGE: 53919</p> <p>DRAWN BY: K.DANG</p> <p>PART NUMBER: PE34439</p>  | <p>SHEET 1 OF 1</p> <p>SCALE: N/A</p> |             |           |         |       |       |           |       |             |   |   |

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.