



3.5mm Male to 3.5mm Male Cable 200 cm Length Using RG402 Coax, LF Solder, RoHS

RF Cable Assemblies Technical Data Sheet

PE34570LF-200CM

Configuration

- Connector 1: 3.5mm Male
- Connector 2: 3.5mm Male
- Cable Type: RG402

Features

- Max Frequency 34 GHz

Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE34570LF-200CM 3.5mm male to 3.5mm male 199.9 cm cable using RG402 coax is part of our full line of RF components available for same-day shipping. Pasternack's semi-rigid RF cable assemblies are ideal for high performance applications and can be formed, using proper tooling, to the routing pattern required. This Pasternack 3.5mm to 3.5mm cable assembly has a male to male gender configuration with 50 ohm semi-rigid RG402 coax. The PE34570LF-200CM 3.5mm male to 3.5mm male cable assembly operates to 34 GHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		34	GHz
VSWR			1.4:1	
Capacitance		29.9 [98.1]		pF/ft [pF/m]

Mechanical Specifications

Cable Assembly

Length*	78.7 in [199.9 cm]
Diameter	0.32 in [8.13 mm]
Weight	0.24 lbs [108.86 g]

Cable

Cable Type	RG402
Impedance	50 Ohms
Inner Conductor Type	Solid

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [3.5mm Male to 3.5mm Male Cable 200 cm Length Using RG402 Coax, LF Solder, RoHS PE34570LF-200CM](#)



3.5mm Male to 3.5mm Male Cable 200 cm Length
Using RG402 Coax, LF Solder, RoHS

RF Cable Assemblies Technical Data Sheet

PE34570LF-200CM

Inner Conductor Material and Plating	Copper Clad Steel, Silver
Dielectric Type	PTFE
Number of Shields	1
Shield Layer 1	Copper

Connectors

Description	Connector 1	Connector 2
Type	3.5mm Male	3.5mm Male
Impedance	50 Ohms	50 Ohms
Contact Material and Plating	Beryllium Copper, Gold	Beryllium Copper, Gold
Contact Plating Specification	50µ in. minimum	50µ in. minimum
Dielectric Type	PCTFE	PCTFE
Body Material and Plating	Passivated Stainless Steel	Passivated Stainless Steel
Body Plating Specification	SAE-AMS-2700	SAE-AMS-2700
Coupling Nut Material and Plating	Passivated Stainless Steel	Passivated Stainless Steel
Coupling Nut Plating Specification	SAE-AMS-2700	SAE-AMS-2700
Hex Size	5/16 in.	5/16 in.
Torque	8 in-lbs [0.9 Nm]	8 in-lbs [0.9 Nm]

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

- Values at 25°C, sea level.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [3.5mm Male to 3.5mm Male Cable 200 cm Length Using RG402 Coax, LF Solder, RoHS PE34570LF-200CM](#)




3.5mm Male to 3.5mm Male Cable 200 cm Length
Using RG402 Coax, LF Solder, RoHS

RF Cable Assemblies Technical Data Sheet

PE34570LF-200CM

Typical Performance Data



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [3.5mm Male to 3.5mm Male Cable 200 cm Length Using RG402 Coax, LF Solder, RoHS PE34570LF-200CM](#)



3.5mm Male to 3.5mm Male Cable 200 cm Length
Using RG402 Coax, LF Solder, RoHS

RF Cable Assemblies Technical Data Sheet

PE34570LF-200CM

How to Order

Part Number Configuration:

PE34570LF - xx uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE34570LF-12 = 12 inches long cable
PE34570LF-100cm = 100 cm long cable

3.5mm Male to 3.5mm Male Cable 200 cm Length Using RG402 Coax, LF Solder, RoHS from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [3.5mm Male to 3.5mm Male Cable 200 cm Length Using RG402 Coax, LF Solder, RoHS PE34570LF-200CM](#)


URL: <https://www.pasternack.com/3.5mm-male-3.5mm-male-rg402u-cable-assembly-pe34570lf-200cm-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE34570LF-200CM CAD Drawing

3.5mm Male to 3.5mm Male Cable 200 cm Length Using RG402 Coax, LF Solder, RoHS

Standard Lengths	
-12	12"
-24	24"
-36	36"
-48	48"
-60	60"
-XXX	Custom Length in Inches



NOTES:
 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
 3. DIMENSIONS ARE IN INCHES (mm).
 4. LENGTH TOLERANCE IS $\pm 1.5\%$ OR $3/8"$, WHICHEVER IS GREATER.

DWG TITLE
PE34570LF-XX

PASTERNAK®
 Pasternack Enterprises, Inc.
 P.O. Box 16759 | Irvine | CA | 92623
 Phone: (949) 261-1920 | Fax: (949) 261-7451
 Website: www.pasternack.com | E-Mail: sales@pasternack.com

REV. A	FSCM NO. 53919	CAD FILE 020408	SCALE N/A	SIZE A	127
--------	----------------	-----------------	-----------	--------	-----