

## 7/16 DIN Male to HN Male Cable Using RG213 Coax





### PE34809

#### Configuration

- Connector 1: 7/16 DIN Male
- Connector 2: HN Male
- Cable Type: RG213
- Coax Flex Type: Flexible

#### Features

- 66% Phase Velocity
- PVC Jacket



#### Applications

- General Purpose
- Laboratory Use

#### Description

Pasternack's PE34809 7/16 DIN male to HN male cable using RG213 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack 7/16 DIN to HN cable assembly has a male to male gender configuration with 50 ohm flexible RG213 coax.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

#### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Velocity of Propagation		66		%
Capacitance		30.8 [101.05]		pF/ft [pF/m]

#### Mechanical Specifications

##### Cable Assembly

Weight 0.451 lbs [204.57 g]

##### Cable

Cable Type	RG213
Impedance	50 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper
Dielectric Type	PE
Number of Shields	1
Shield Layer 1	Copper Braid

## 7/16 DIN Male to HN Male Cable Using RG213 Coax



### PE34809

Jacket Material	PVC, Black
Jacket Diameter	0.405 in [10.29 mm]

#### Connectors

Description	Connector 1	Connector 2
Type	7/16 DIN Male	HN Male
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Contact Material and Plating		Brass, Gold
Contact Plating Specification		30 $\mu$ in. minimum
Dielectric Type		PTFE
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification		100 $\mu$ in. minimum
Coupling Nut Material and Plating		Brass, Nickel
Coupling Nut Plating Specification		100 $\mu$ in. minimum

#### Environmental Specifications

**Compliance Certifications** (see product page for current document)


#### Plotted and Other Data

Notes:  
Values at 25°C, sea level.

## 7/16 DIN Male to HN Male Cable Using RG213 Coax

**PE34809****Typical Performance Data****How to Order**

Part Number Configuration:



Example: PE34809-12 = 12 inches long cable  
PE34809-100cm = 100 cm long cable

7/16 DIN Male to HN Male Cable Using RG213 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [7/16 DIN Male to HN Male Cable Using RG213 Coax PE34809](#)

URL: <https://www.pasternack.com/7-16-din-male-to-hn-male-cable-using-rg213-pe34809-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

# PE34809 CAD Drawing

7/16 DIN Male to HN Male Cable Using RG213 Coax



SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV
A	53919	HBAKKE	PE34809	A