



N Male to N Female Cable 72 Inch Length Using RG225 Coax , LF Solder

RF Cable Assemblies Technical Data Sheet

PE33728LF-72

Configuration

- Connector 1: N Male
- Connector 2: N Female
- Cable Type: RG225

Features

- Max Frequency 400 MHz
- Double Shielded
- PTFE (FG) Jacket

Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE33728LF-72 type N male to type N female 72 inch cable using RG225 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack type N to type N cable assembly has a male to female gender configuration with 50 ohm flexible RG225 coax. The PE33728LF-72 type N male to type N female cable assembly operates to 400 MHz. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		400	MHz
Capacitance	32.4 [106.3]			pF/ft [pF/m]

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	50	100	250			MHz
Insertion Loss (Typ.)	0.238	0.275	0.388			dB

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [N Male to N Female Cable 72 Inch Length Using RG225 Coax , LF Solder PE33728LF-72](#)



N Male to N Female Cable 72 Inch Length
Using RG225 Coax , LF Solder

RF Cable Assemblies Technical Data Sheet

PE33728LF-72

Mechanical Specifications

Cable Assembly

Weight	1.303 lbs [591.03 g]
Cable	
Cable Type	RG225
Impedance	50 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper, Silver
Dielectric Type	PTFE
Number of Shields	2
Shield Layer 1	Silver Plated Copper Braid
Shield Layer 2	Silver Plated Copper Braid
Jacket Material	PTFE (FG), Brown
Jacket Diameter	0.43 in [10.92 mm]

Connectors

Description	Connector 1	Connector 2
Type	N Male	N Female
Specification	MIL-STD-348A	MIL-STD-348A
Impedance	50 Ohms	50 Ohms
Contact Material and Plating	Brass, Gold	Phosphor Bronze, Gold
Contact Plating Specification	30 μ in. minimum	30 μ in. minimum
Dielectric Type	Teflon	Teflon
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification	100 μ in. minimum	100 μ in. minimum
Coupling Nut Material and Plating	Brass, Nickel	
Coupling Nut Plating Specification	100 μ in. minimum	

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

- Values at 25°C, sea level.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [N Male to N Female Cable 72 Inch Length Using RG225 Coax , LF Solder PE33728LF-72](#)



N Male to N Female Cable 72 Inch Length
Using RG225 Coax , LF Solder

RF Cable Assemblies Technical Data Sheet

PE33728LF-72

How to Order

Part Number Configuration:

PE33728LF - **xx** **uu**

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE33728LF-12 = 12 inches long cable
PE33728LF-100cm = 100 cm long cable

N Male to N Female Cable 72 Inch Length Using RG225 Coax , LF Solder from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [N Male to N Female Cable 72 Inch Length Using RG225 Coax , LF Solder PE33728LF-72](#)

URL: <https://www.pasternack.com/n-male-n-female-rg225u-cable-assembly-pe33728lf-72-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE33728LF-72 CAD Drawing

N Male to N Female Cable 72 Inch Length Using RG225 Coax , LF Solder

