



## UHF Male to UHF Male Cable 24 Inch Length Using RG8 Coax

### RF Cable Assemblies Technical Data Sheet

PE3623-24

#### Configuration

- Connector 1: UHF Male
- Connector 2: UHF Male
- Cable Type: RG8

#### Features

- Max Frequency 300 MHz
- 66% Phase Velocity
- PVC (NC) Jacket

#### Applications

- General Purpose
- Laboratory Use

#### Description

Pasternack's PE3623-24 UHF male to UHF male 24 inch cable using RG8 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack UHF to UHF cable assembly has a male to male gender configuration with 50 ohm flexible RG8 coax. The PE3623-24 UHF male to UHF male cable assembly operates to 300 MHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

#### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		300	MHz
VSWR			1.4:1	
Velocity of Propagation		66		%
Capacitance		30.8 [101.05]		pF/ft [pF/m]

#### Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	50	100	250	300		MHz
Insertion Loss (Typ.)	0.46	0.54	0.78	0.86		dB

Electrical Specification Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [UHF Male to UHF Male Cable 24 Inch Length Using RG8 Coax PE3623-24](#)



## UHF Male to UHF Male Cable 24 Inch Length Using RG8 Coax

### RF Cable Assemblies Technical Data Sheet

PE3623-24

The Insertion Loss data above is based on the performance specifications of the coax and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1 dB per connector.

#### Mechanical Specifications

##### Cable Assembly

Weight 0.313 lbs [141.97 g]

##### Cable

Cable Type RG8  
 Impedance 50 Ohms  
 Inner Conductor Type Stranded  
 Inner Conductor Material and Plating Copper  
 Dielectric Type PE (LD)  
 Number of Shields 1  
 Shield Layer 1 Copper Braid  
 Jacket Material PVC (NC), Black  
 Jacket Diameter 0.405 in [10.29 mm]

##### Connectors

Description	Connector 1	Connector 2
Type	UHF Male	UHF Male
Impedance	50 Ohms	50 Ohms
Contact Material and Plating	Brass, Gold	Brass, Gold
Contact Plating Specification	30µ in. minimum	30µ in. minimum
Dielectric Type	Teflon	Teflon
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification	100µ in. minimum	100µ in. minimum
Coupling Nut Material and Plating	Brass, Nickel	Brass, Nickel
Coupling Nut Plating Specification	100µ in. minimum	100µ in. minimum

**Compliance Certifications** (see [product page](#) for current document)

#### Plotted and Other Data

Notes:

- Values at 25°C, sea level.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [UHF Male to UHF Male Cable 24 Inch Length Using RG8 Coax PE3623-24](#)



## UHF Male to UHF Male Cable 24 Inch Length Using RG8 Coax

### RF Cable Assemblies Technical Data Sheet

PE3623-24

#### How to Order

Part Number Configuration:

PE3623

- xx

uu

Unit of Measure:

cm = Centimeters

<blank> = Inches

Length

Base Number

Example: PE3623-12 = 12 inches long cable  
PE3623-100cm = 100 cm long cable

UHF Male to UHF Male Cable 24 Inch Length Using RG8 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [UHF Male to UHF Male Cable 24 Inch Length Using RG8 Coax PE3623-24](https://www.pasternack.com/uhf-male-uhf-male-rg8au-cable-assembly-pe3623-24-p.aspx)


URL: <https://www.pasternack.com/uhf-male-uhf-male-rg8au-cable-assembly-pe3623-24-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

# PE3623-24 CAD Drawing

UHF Male to UHF Male Cable 24 Inch Length Using RG8 Coax

Standard Lengths	
-12	12"
-24	24"
-36	36"
-48	48"
-60	60"
-XXX	Custom Length in Inches



NOTES:  
 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.  
 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.  
 3. DIMENSIONS ARE IN INCHES (mm).  
 4. LENGTH TOLERANCE IS  $\pm 1.5\%$  OR  $3/8"$ , WHICHEVER IS GREATER.

DWG TITLE  
**PE3623-XX**

**PE PASTERNAK®**  
 Pasternack Enterprises, Inc.  
 P.O. Box 16759 | Irvine | CA | 92623  
 Phone: (949) 261-1920 | Fax: (949) 261-7451  
 Website: www.pasternack.com | E-Mail: sales@pasternack.com

REV. -	FSCM NO. 53919	CAD FILE 030607	SCALE N/A	SIZE A	127
--------	----------------	-----------------	-----------	--------	-----