



## MMCX Plug to MMCX Plug Cable 12 Inch Length Using RG316-DS Coax

### RF Cable Assemblies Technical Data Sheet


PE38679-12

#### Configuration

- Connector 1: MMCX Plug
- Connector 2: MMCX Plug
- Cable Type: RG316-DS

#### Features

- Max Frequency 3 GHz
- 70% Phase Velocity
- Double Shielded
- FEP Jacket



#### Applications

- General Purpose
- Laboratory Use

#### Description

Pasternack's PE38679-12 MMCX plug to MMCX plug 12 inch cable using RG316-DS coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack MMCX to MMCX cable assembly has a plug to plug gender configuration with 50 ohm flexible RG316-DS coax. The PE38679-12 MMCX plug to MMCX plug cable assembly operates to 3 GHz. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

#### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		3	GHz
VSWR			1.4:1	
Velocity of Propagation	70			%
Capacitance	29.4 [96.46]			pF/ft [pF/m]
Operating Voltage (AC)			250	Vrms

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [MMCX Plug to MMCX Plug Cable 12 Inch Length Using RG316-DS Coax PE38679-12](#)



## MMCX Plug to MMCX Plug Cable 12 Inch Length Using RG316-DS Coax

### RF Cable Assemblies Technical Data Sheet

PE38679-12

#### Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.1	0.25	0.5	1	3	GHz
Insertion Loss (Typ.)	0.28	0.321	0.379	0.461	0.667	dB
VSWR (Max.)	1.4:1	1.4:1	1.4:1	1.4:1	1.4:1	
Return Loss (Max.)	15.56	15.563	15.563	15.563	15.563	dB

#### Mechanical Specifications

##### Cable Assembly

Length*	12 in [304.8 mm]
Diameter	0.18 in [4.57 mm]
Weight	0.022 lbs [9.98 g]

##### Cable

Cable Type	RG316-DS
Impedance	50 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper Clad Steel, Silver PTFE
Dielectric Type	2
Number of Shields	Silver Plated Copper Braid
Shield Layer 1	Silver Plated Copper Braid
Shield Layer 2	FEP, Tan
Jacket Material	0.114 in [2.9 mm]
Jacket Diameter	
One Time Minimum Bend Radius	0.59 in [14.99 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [MMCX Plug to MMCX Plug Cable 12 Inch Length Using RG316-DS Coax PE38679-12](#)



## MMCX Plug to MMCX Plug Cable 12 Inch Length Using RG316-DS Coax

### RF Cable Assemblies Technical Data Sheet

PE38679-12

#### Connectors

Description	Connector 1	Connector 2
Type	MMCX Plug	MMCX Plug
Specification	BS EN 122340	BS EN 122340
Impedance	50 Ohms	50 Ohms
Contact Material and Plating	Brass, Gold	Brass, Gold
Contact Plating Specification	30µ in. minimum	30µ in. minimum
Dielectric Type	Teflon	Teflon
Body Material and Plating	Brass, Gold	Brass, Gold
Body Plating Specification	3µ in. minimum	3µ in. minimum

#### Mechanical Specification Notes:

\*All cable assemblies have a length tolerance of 1.5% or  $\pm 3/8"$ , whichever is greater.

#### Compliance Certifications (see [product page](#) for current document)

#### Plotted and Other Data

##### Notes:

- Values at 25°C, sea level.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [MMCX Plug to MMCX Plug Cable 12 Inch Length Using RG316-DS Coax PE38679-12](#)




## MMCX Plug to MMCX Plug Cable 12 Inch Length Using RG316-DS Coax

### RF Cable Assemblies Technical Data Sheet

PE38679-12

#### How to Order

Part Number Configuration:



Example: PE38679-12 = 12 inches long cable  
PE38679-100cm = 100 cm long cable

MMCX Plug to MMCX Plug Cable 12 Inch Length Using RG316-DS Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [MMCX Plug to MMCX Plug Cable 12 Inch Length Using RG316-DS Coax PE38679-12](#)


URL: <https://www.pasternack.com/mmcx-plug-mmcx-plug-rg316-ds-cable-assembly-pe38679-12-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

# PE38679-12 CAD Drawing

MMCX Plug to MMCX Plug Cable 12 Inch Length Using RG316-DS Coax

Standard Lengths
-12
12"
-24
24"
-36
36"
-48
48"
-60
60"
-XXX
Custom Length in Inches



NOTES:  
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.  
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.  
3. DIMENSIONS ARE IN INCHES [mm].  
4. LENGTH TOLERANCE IS  $\pm 1.5\%$  OR 3/8", WHICHEVER IS GREATER.

DWG TITLE  
**PE38679**

**PE PASTERNACK®**

Pasternack Enterprises, Inc.  
P.O. Box 16759 | Irvine | CA | 92623

Phone: (949) 261-1920 | Fax: (949) 261-7451

Website: [www.pasternack.com](http://www.pasternack.com) | E-Mail: [sales@pasternack.com](mailto:sales@pasternack.com)

REV. -	FSCM NO.	53919	CAD FILE	082411	SCALE N/A	SIZE A	2231