

Reverse Polarity SMA Plug Right Angle to Reverse Polarity SMA Jack Bulkhead Cable Using RG142 Coax

PE39107LF




Configuration

- Connector 1: SMA Plug Reverse Polarity Right Angle
- Connector 2: SMA Jack Reverse Polarity Bulkhead
- Cable Type: RG142
- Coax Flex Type: Flexible

Features

- Shielding Effectivity > 90 dB
- 69.2% Phase Velocity
- Double Shielded
- FEP Jacket



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE39107LF reverse polarity SMA plug right angle to reverse polarity SMA jack bulkhead cable using RG142 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack reverse polarity SMA to reverse polarity SMA cable assembly has a plug to jack gender configuration with 50 ohm flexible RG142 coax. The right angle SMA interface on the RG142 cable allows for easier connections in tight spaces. Our RF cable assembly with SMA bulkhead interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness of better than 90 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Velocity of Propagation		69.2		%
RF Shielding	90			dB
Capacitance		29.4 [96.46]		pF/ft [pF/m]

Mechanical Specifications

Cable Assembly

Weight 0.065 lbs [29.48 g]

Cable

Cable Type RG142

Reverse Polarity SMA Plug Right Angle to Reverse Polarity SMA Jack Bulkhead Cable Using RG142 Coax



PE39107LF

Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper Clad Steel, Silver
Dielectric Type	PTFE
Number of Shields	2
Shield Layer 1	Silver Plated Copper Braid
Shield Layer 2	Silver Plated Copper Braid
Jacket Material	FEP, Tan
Jacket Diameter	0.195 in [4.95 mm]
One Time Minimum Bend Radius	0.984 in [24.99 mm]
Repeated Minimum Bend Radius	2 in [50.8 mm]

Connectors

Description	Connector 1	Connector 2
Type	SMA Plug Reverse Polarity Right Angle	SMA Jack Reverse Polarity Bulkhead
Impedance	50 Ohms	50 Ohms
Configuration	Right Angle	Straight
Contact Material and Plating	Beryllium Copper, Gold	Gold
Contact Plating Specification		MIL-G-45204
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification		QQ-N-290
Coupling Nut Material and Plating	Brass, Nickel	
Hex Size	5/16 in	
Torque	5 in-lbs 0.57 Nm	

Environmental Specifications

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Values at 25°C, sea level.

Reverse Polarity SMA Plug Right Angle to Reverse Polarity SMA Jack Bulkhead Cable Using RG142 Coax



PE39107LF

Typical Performance Data

How to Order

Part Number Configuration:

PE39107LF

- XX

uu

- Unit of Measure:
cm = Centimeters
<blank> = Inches

- Length

- Base Number

Example: PE39107LF-12 = 12 inches long cable
PE39107LF-100cm = 100 cm long cable

Reverse Polarity SMA Plug Right Angle to Reverse Polarity SMA Jack Bulkhead Cable Using RG142 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Reverse Polarity SMA Plug Right Angle to Reverse Polarity SMA Jack Bulkhead Cable Using RG142 Coax PE39107LF](#)

URL: <https://www.pasternack.com/reverse-polarity-sma-plug-right-angle-to-reverse-polarity-sma-jack-bulkhead-cable-using-rg142-pe39107lf-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE39107LF CAD Drawing

Reverse Polarity SMA Plug Right Angle to Reverse Polarity SMA Jack Bulkhead Cable Using RG142 Coax

