



SMA Male to Violet FAKRA Plug Cable
36 Inch Length Using RG174 Coax

RF Cable Assemblies Technical Data Sheet

PE39197H-36

Configuration

- Connector 1: SMA Male
- Connector 2: FAKRA Plug
- Cable Type: RG174

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		1,000	MHz
VSWR			1.4:1	
Velocity of Propagation		66		%
Capacitance		30.8 [101.05]		pF/ft [pF/m]

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	50	100	250	500	1,000	MHz
Insertion Loss (Typ.)	0.326	0.452	0.611	0.835	1.16	dB
VSWR (Max.)	1.4:1	1.4:1	1.4:1	1.4:1	1.4:1	
Return Loss (Max.)	15.56	15.563	15.563	15.563	15.563	dB

Mechanical Specifications

Cable Assembly

Length*	36 in [914.4 mm]
Diameter	0.37 in [9.4 mm]
Weight	0.038 lbs [17.24 g]

Cable

Cable Type	RG174
Impedance	50 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper Clad Steel
Dielectric Type	PE (LD)
Number of Shields	1
Shield Layer 1	Tinned Copper Braid

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male to Violet FAKRA Plug Cable 36 Inch Length Using RG174 Coax PE39197H-36](#)



SMA Male to Violet FAKRA Plug Cable
36 Inch Length Using RG174 Coax

RF Cable Assemblies Technical Data Sheet

PE39197H-36

Jacket Material PVC, Black
Jacket Diameter 0.1 in [2.54 mm]

Connectors

Description	Connector 1	Connector 2
Type	SMA Male	FAKRA Plug
Specification	MIL-STD-348A	
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Contact Material and Plating	Brass, Gold	Phosphor Bronze, Gold
Contact Plating Specification	30µ in. Minimum	
Dielectric Type	PTFE	Teflon
Outer Conductor Material and Plating		Brass, Nickel
Body Material and Plating	Brass, Nickel	Plastic
Body Plating Specification	100µ in. Minimum	
Coupling Nut Material and Plating	Brass, Nickel	
Coupling Nut Plating Specification	100µ in. Minimum	
Hex Size	5/16 in	
Torque	5 in-lbs [0.57 Nm]	

Mechanical Specification Notes:

*All cable assemblies have a length tolerance of 1.5% or $\pm 3/8"$, whichever is greater.

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

- Values at 25°C, sea level.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male to Violet FAKRA Plug Cable 36 Inch Length Using RG174 Coax PE39197H-36](#)



SMA Male to Violet FAKRA Plug Cable
36 Inch Length Using RG174 Coax

RF Cable Assemblies Technical Data Sheet

PE39197H-36

How to Order

Part Number Configuration:

PE39197H

- xx

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE39197H-12 = 12 inches long cable
PE39197H-100cm = 100 cm long cable

SMA Male to Violet FAKRA Plug Cable 36 Inch Length Using RG174 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male to Violet FAKRA Plug Cable 36 Inch Length Using RG174 Coax PE39197H-36](#)

URL: <https://www.pasternack.com/sma-male-fakra-plug-rg174au-cable-assembly-pe39197h-36-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE39197H-36 CAD Drawing

SMA Male to Violet FAKRA Plug Cable 36 Inch Length Using RG174 Coax



How To Order									
Part Number Configuration				Examples		Part # Ext.	Length In Inches	Part # Ext.	Length In Centimeters
PE3 [zzz] [yy] - [xx] [uu]				PE3000LF-100		-12	12"	-25CM	25Cm
				PE3000-100		-24	24"	-50CM	50Cm
				PE3000LF-100CM		-36	36"	-75CM	75Cm
				PE3000-100CM		-48	48"	-100CM	100Cm
						-60	60"	-125CM	125Cm
00 - 99999				CM = Centimeters < Blank > = Inches		-xx	Custom Length	-xxCM	Custom Length
LF = RoHS Compliant < Blank > = Standard				Length					
Note: LF applies only to RF cables									

- NOTES:
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
 3. DIMENSIONS ARE IN INCHES [mm].
 4. LENGTH TOLERANCE IS $\pm 1.5\%$ OR $3/8"$, WHICHEVER IS GREATER.

DWG TITLE
PE39197H

PASTERNAK®
 Pasternack Enterprises, Inc.
 P.O. Box 16759 | Irvine | CA | 92623
Phone: (949) 261-1920 | **Fax:** (949) 261-7451
Website: www.pasternack.com | **E-Mail:** sales@pasternack.com

FSCM NO. 53919

CAD FILE 41613 SCALE N/A SIZE A