

Fire Rated SMA Male Right Angle to SMA Male Right Angle Low Loss Cable Using TCOM-240-FR Coax With Times Microwave Components




PE3C10396

Configuration

- Connector 1: SMA Male Right Angle
- Connector 2: SMA Male Right Angle
- Cable Type: TCOM-240-FR
- Coax Flex Type: Flexible

Features

- Max Frequency 6 GHz
- Shielding Effectivity > 100 dB
- 84% Phase Velocity
- Double Shielded
- PE Jacket
- 500 Mating Cycles



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3C10396 SMA male right angle to SMA male right angle cable using TCOM-240-FR coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack SMA to SMA cable assembly has a male to male gender configuration with 50 ohm flexible TCOM-240-FR coax. The PE3C10396 SMA male to SMA male cable assembly operates to 6 GHz. The right angle SMA interfaces on the TCOM-240-FR cable allow for easier connections in tight spaces. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness of better than 100 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		6	GHz
VSWR			1.4:1	
Velocity of Propagation		84		%
RF Shielding	100			dB
Group Delay		1.21 [3.97]		ns/ft [ns/m]
Capacitance		24.2 [79.4]		pF/ft [pF/m]
Inductance		0.06 [0.2]		uH/ft [uH/m]
DC Resistance Inner Conductor		3.2 [10.5]		Ohms/1000ft [Ohms/Km]
DC Resistance Outer Conductor		2.06 [6.76]		Ohms/1000ft [Ohms/Km]

Fire Rated SMA Male Right Angle to SMA Male
Right Angle Low Loss Cable Using TCOM-240-
FR Coax With Times Microwave Components



PE3C10396

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Jacket Spark			5,000	Vrms

Specifications by Frequency

Part Number	Length	Description	F1	F2	F3	F4	F5	Units	Weight (lbs)
			Frequency					MHz	
PE3C10396	Custom Lengths Available	Insertion Loss (Typ.)	0.037	0.052	0.076	0.123	0.197	dB/ft	
			0.13	0.18	0.25	0.41	0.65	dB/m	
PE3C10396-12	12 inch	Insertion Loss (Typ.)	0.54	0.56	0.58	0.63	0.7	dB	0.081
PE3C10396-24	24 inch	Insertion Loss (Typ.)	0.58	0.61	0.66	0.75	0.9	dB	0.126
PE3C10396-36	36 inch	Insertion Loss (Typ.)	0.62	0.66	0.73	0.87	1.1	dB	0.171
PE3C10396-48	48 inch	Insertion Loss (Typ.)	0.65	0.71	0.81	1	1.29	dB	0.216
PE3C10396-60	60 inch	Insertion Loss (Typ.)	0.69	0.76	0.88	1.12	1.49	dB	0.261

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1:	0.25 dB
Loss due to Connector 2:	0.25 dB
Base Weight:	0.081 pounds
Additional Weight per Inch:	0.00375 pounds

Mechanical Specifications

Cable Assembly

Width/Diameter	0.5 in [12.7 mm]
Weight	0.081 lbs [36.74 g]

Cable

Cable Type	TCOM-240-FR
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper
Dielectric Type	PE (F)
Number of Shields	2
Shield Layer 1	Silver Plated Copper Braid
Shield Layer 2	Tinned Copper Braid
Jacket Material	PE, Black
Jacket Diameter	0.24 in [6.1 mm]
One Time Minimum Bend Radius	0.75 in [19.05 mm]
Repeated Minimum Bend Radius	2.5 in [63.5 mm]
Bending Moment	0.25 lbs-ft [0.34 N-m]
Flat Plate Crush	20 lbs/in [0.36 Kg/mm]
Tensile Strength	80 lbs [36.29 Kg]

Fire Rated SMA Male Right Angle to SMA Male
Right Angle Low Loss Cable Using TCOM-240-
FR Coax With Times Microwave Components



PE3C10396

Connectors

Description	Connector 1	Connector 2
Type	SMA Male Right Angle	SMA Male Right Angle
Impedance	50 Ohms	50 Ohms
Configuration	Right Angle	Right Angle
Mating Cycles	500	500
Contact Material and Plating	Brass, Gold	Brass, Gold
Contact Plating Specification	50 µin	50 µin
Dielectric Type	PTFE	PTFE
Body Material and Plating	Passivated Stainless Steel	Passivated Stainless Steel
Coupling Nut Material and Plating	Passivated Stainless Steel	Passivated Stainless Steel
Torque	7 in-lbs 0.79 Nm	7 in-lbs 0.79 Nm

Environmental Specifications

Operating Range Temperature -40 to +85 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Fire Rated SMA Male Right Angle to SMA Male Right Angle Low Loss Cable Using TCOM-240-FR Coax With Times Microwave Components



PE3C10396

Typical Performance Data

How to Order

Part Number Configuration:

PE3C10396

- xx

uu



Example: PE3C10396-12 = 12 inches long cable
PE3C10396-100cm = 100 cm long cable

Fire Rated SMA Male Right Angle to SMA Male Right Angle Low Loss Cable Using TCOM-240-FR Coax With Times Microwave Components from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Fire Rated SMA Male Right Angle to SMA Male Right Angle Low Loss Cable Using TCOM-240-FR Coax With Times Microwave Components PE3C10396](https://www.pasternack.com/fire-rated-sma-male-right-angle-to-sma-male-right-angle-low-loss-cable-using-tcom-240-fr-pe3c10396-p.aspx)

URL: <https://www.pasternack.com/fire-rated-sma-male-right-angle-to-sma-male-low-loss-cable-using-tcom-240-fr-pe3c10396-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE3C10396 CAD Drawing

Fire Rated SMA Male Right Angle to SMA Male Right Angle Low Loss Cable
Using TCOM-240-FR Coax With Times Microwave Components

