

## 2.92mm Male to 2.4mm Female Cable 24 Inch Length Using PE-SR405FLJ Coax





### PE3C1114-24

#### Configuration

- Connector 1: 2.92mm Male
- Connector 2: 2.4mm Female
- Cable Type: PE-SR405FLJ
- Coax Flex Type: Formable

#### Features

- Shielding Effectivity > 100 dB
- 69.5% Phase Velocity
- FEP Jacket



#### Applications

- General Purpose
- Laboratory Use

#### Description

Pasternack's PE3C1114-24 2.92mm male to 2.4mm female 24 inch cable using PE-SR405FLJ coax is part of our full line of RF components available for same-day shipping. Pasternack's formable RF cable assemblies provide an alternative to costly pre-formed semi-rigid assemblies since they are hand formable. This Pasternack 2.92mm to 2.4mm cable assembly has a male to female gender configuration with 50 ohm formable PE-SR405FLJ coax.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

#### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Velocity of Propagation		69.5		%
RF Shielding	100			dB
Group Delay		1.43 [4.69]		ns/ft [ns/m]
Capacitance		29 [95.14]		pF/ft [pF/m]

#### Mechanical Specifications

##### Cable Assembly

Length	24 in [609.6 mm]
Width/Diameter	0.5 in [12.7 mm]
Weight	0.06 lbs [27.22 g]

##### Cable

Cable Type	PE-SR405FLJ
------------	-------------

## 2.92mm Male to 2.4mm Female Cable 24 Inch Length Using PE-SR405FLJ Coax



### PE3C1114-24

Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper Clad Steel, Silver
Dielectric Type	PTFE
Number of Shields	1
Shield Layer 1	Tinned Copper Braid
Jacket Material	FEP, Black
Jacket Diameter	0.098 in [2.49 mm]
One Time Minimum Bend Radius	0.236 in [5.99 mm]
Repeated Minimum Bend Radius	0.787 in [19.99 mm]

### Connectors

Description	Connector 1	Connector 2
Type	2.92mm Male	2.4mm Female
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Contact Material and Plating	Beryllium Copper, Gold over Nickel	Beryllium Copper, Gold over Nickel
Contact Plating Specification	50 µin minimum	50 µin minimum
Dielectric Type	PCTFE	PEI
Body Material and Plating	Passivated Stainless Steel	Passivated Stainless Steel
Body Plating Specification	SAE-AMS-2700	SAE-AMS-2700
Coupling Nut Material and Plating	Passivated Stainless Steel	
Coupling Nut Plating Specification	SAE-AMS-2700	
Hex Size	5/16 Inch	

### Environmental Specifications

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data

Notes:  
Values at 25°C, sea level.

2.92mm Male to 2.4mm Female Cable 24 Inch Length Using PE-SR405FLJ Coax




**PE3C1114-24**

**Typical Performance Data**

**How to Order**

Part Number Configuration:



Example: PE3C1114-12 = 12 inches long cable  
PE3C1114-100cm = 100 cm long cable

2.92mm Male to 2.4mm Female Cable 24 Inch Length Using PE-SR405FLJ Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.92mm Male to 2.4mm Female Cable 24 Inch Length Using PE-SR405FLJ Coax PE3C1114-24](https://www.pasternack.com/2.92mm-male-to-2.4mm-female-cable-24-inch-length-using-pe-sr405flj-pe3c1114-24-p.aspx)

URL: <https://www.pasternack.com/2.92mm-male-to-2.4mm-female-cable-24-inch-length-using-pe-sr405flj-pe3c1114-24-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

# PE3C1114-24 CAD Drawing

2.92mm Male to 2.4mm Female Cable 24 Inch Length Using PE-SR405FLJ Coax

