

2.92mm Male to 2.92mm Male Cable 12 Inch  
Length Using PE-SR405FL Coax



## RF Cable Assemblies Technical Data Sheet



PE3C1377-12

### Configuration

- Connector 1: 2.92mm Male
- Connector 2: 2.92mm Male
- Cable Type: PE-SR405FL

### Features

- Max Frequency 40 GHz
- 69.5% Phase Velocity



### Applications

- General Purpose
- Laboratory Use

### Description

Pasternack's PE3C1377-12 2.92mm male to 2.92mm male 12 inch cable using PE-SR405FL coax is part of our full line of RF components available for same-day shipping. Pasternack's formable RF cable assemblies provide an alternative to costly pre-formed semi-rigid assemblies since they are hand formable. This Pasternack 2.92mm to 2.92mm cable assembly has a male to male gender configuration with 50 ohm formable PE-SR405FL coax. The PE3C1377-12 2.92mm male to 2.92mm male cable assembly operates to 40 GHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.92mm Male to 2.92mm Male Cable 12 Inch Length Using PE-SR405FL Coax PE3C1377-12](#)

2.92mm Male to 2.92mm Male Cable 12 Inch  
Length Using PE-SR405FL Coax



## RF Cable Assemblies Technical Data Sheet

PE3C1377-12

### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		40	GHz
VSWR		1.4:1		
Return Loss			-15.563	dB
Velocity of Propagation		69.5		%
Capacitance		29 [95.14]		pF/ft [pF/m]

### Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	1	5	10	20		GHz
Insertion Loss (Typ.)	0.43	0.75	1.04	1.54		dB

### Mechanical Specifications

#### Cable Assembly

Length*	12 in [304.8 mm]
Diameter	0.312 in [7.92 mm]
Weight	0.038 lbs [17.24 g]

#### Cable

Cable Type	PE-SR405FL
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper Clad Steel, Silver
Dielectric Type	PTFE
Number of Shields	1
Shield Layer 1	Tinned Copper Braid
Outer Conductor Diameter	0.086 in [2.18 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.92mm Male to 2.92mm Male Cable 12 Inch Length Using PE-SR405FL Coax PE3C1377-12](#)



2.92mm Male to 2.92mm Male Cable 12 Inch  
Length Using PE-SR405FL Coax

## RF Cable Assemblies Technical Data Sheet

PE3C1377-12

### Connectors

Description	Connector 1	Connector 2
Type	2.92mm Male	2.92mm Male
Impedance	50 Ohms	50 Ohms
Contact Material and Plating	Beryllium Copper, Gold	Beryllium Copper
Contact Plating Specification	50 $\mu$ in. minimum	50 $\mu$ in. minimum
Dielectric Type	Ultem 1000	Ultem 1000
Body Material and Plating	Passivated Stainless Steel	Passivated Stainless Steel
Body Plating Specification	SAE-AMS-2700	SAE-AMS-2700
Coupling Nut Material and Plating	Passivated Stainless Steel	Passivated Stainless Steel
Coupling Nut Plating Specification	SAE-AMS-2700	SAE-AMS-2700
Hex Size	5/16 Inch	5/16 Inch

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.92mm Male to 2.92mm Male Cable 12 Inch Length Using PE-SR405FL Coax PE3C1377-12](#)





2.92mm Male to 2.92mm Male Cable 12 Inch Length Using PE-SR405FL Coax

# RF Cable Assemblies Technical Data Sheet

PE3C1377-12

## Typical Performance Data

### PE3C1377-36 VSWR



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.92mm Male to 2.92mm Male Cable 12 Inch Length Using PE-SR405FL Coax PE3C1377-12](#)

2.92mm Male to 2.92mm Male Cable 12 Inch  
Length Using PE-SR405FL Coax



RF Cable Assemblies Technical Data Sheet

PE3C1377-12

**How to Order**

Part Number Configuration:

**PE3C1377**

- **xx**

**uu**

Unit of Measure:  
cm = Centimeters  
<blank> = Inches  
Length  
Base Number

Example: PE3C1377-12 = 12 inches long cable  
PE3C1377-100cm = 100 cm long cable

2.92mm Male to 2.92mm Male Cable 12 Inch Length Using PE-SR405FL Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.92mm Male to 2.92mm Male Cable 12 Inch Length Using PE-SR405FL Coax PE3C1377-12](#)


URL: <https://www.pasternack.com/2.92mm-male-2.92mm-male-pe-sr405fl-cable-assembly-pe3c1377-12-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

# PE3C1377-12 CAD Drawing

2.92mm Male to 2.92mm Male Cable 12 Inch Length Using PE-SR405FL Coax

REVISIONS				
REV.	DESCRIPTION	DATE	APPROVED	
A	PCR PE3C1377	3/16/2021	S.ELLIS	



UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [ ] ARE MILLIMETERS		THIRD-ANGLE PROJECTION
TOLERANCES:		THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF PASTERNAK CORPORATION. ALL RIGHTS RESERVED.
X = $\pm 2$ [5.08] FRACTIONS .XX = $\pm .02$ [.51] $\pm 1/32$ .XXX = $\pm .005$ [.13] ANGLES $\pm 1^\circ$		Pasterнак Enterprises, Inc. P.O. Box 16759, Irvine, CA 92623. Phone: 1.949.261.1920   1.866.727.8376 Fax: 1.949.261.7451 Website: <a href="http://www.pasterнак.com">www.pasterнак.com</a> E-mail: <a href="mailto:sales@pasterнак.com">sales@pasterнак.com</a>
CABLE LENGTH (L) TOLERANCES: L $\leq$ 12 [305] = $\pm 1$ [25] / -0 12 [305] < L $\leq$ 60 [1524] = $\pm 2$ [51] / -0 60 [1524] < L $\leq$ 120 [3048] = $\pm 4$ [102] / -0 120 [3048] < L $\leq$ 300 [7620] = $\pm 6$ [152] / -0 300 [7620] < L = $\pm 5\%$ L / -0		SHEET 1 OF 1 SCALE N/A ITEM NO. PE3C1377 DRAWN BY K.DANG CAGE CODE 53919 SIZE A REV A
ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.		

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.