



75 Ohm F Male Right Angle Connector Crimp/ Solder Attachment for RG6-CATV

RF Connectors Technical Data Sheet

PE44320

Configuration

- F Male Connector
- 75 Ohms
- Right Angle Body Geometry
- RG6-CATV Interface Type
- Crimp/Solder Attachment
- 7/16 inch Hex

Features

- Max. Operating Frequency 2 GHz
- Excellent VSWR of 1.23:1
- Gold Plated Brass Contact

Applications

- General Purpose Test
- Custom Cable Assemblies

Description

Pasternack's PE44320 75 ohm type F male right angle connector crimp/solder attachment for RG6-CATV is part of our full line of RF components available for same-day shipping. Our type F male connector operates up to a maximum frequency of 2 GHz and offers excellent VSWR of 1.23:1. Its right angle body geometry allows for easier connections in tight spaces.

Our 75 ohm type F male right angle connector PE44320 datasheet specifications and drawing with dimensions are shown below in this PDF. Pasternack's broad catalog of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. Whether the need is to provide an I/O for a board design, or simply create a custom cable assembly configuration, Pasternack has the right connector for the job. Pasternack can also expertly build your custom cable connector assemblies for you and ship same-day.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		2	GHz
VSWR			1.23:1	

Mechanical Specifications

Size	
Length	0.87 in [22.1 mm]
Width/Dia.	0.438 in [11.13 mm]
Height	1 in [25.4 mm]
Weight	0.046 lbs [20.87 g]
Mating Torque	12 to 15 in-lbs [1.36 to 1.70 Nm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [75 Ohm F Male Right Angle Connector Crimp/Solder Attachment for RG6-CATV PE44320](#)



75 Ohm F Male Right Angle Connector Crimp/
Solder Attachment for RG6-CATV

RF Connectors Technical Data Sheet

PE44320

Material Specifications

Description	Material	Plating
Contact	Brass	Gold
Insulation	PTFE	
Body	Brass	Nickel
Coupling Nut	Brass	Nickel

Environmental Specifications

Temperature

Operating Range -65 to +165 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

75 Ohm F Male Right Angle Connector Crimp/Solder Attachment for RG6-CATV from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [75 Ohm F Male Right Angle Connector Crimp/Solder Attachment for RG6-CATV PE44320](#)

URL: <https://www.pasternack.com/f-male-standard-rg6-catv-connector-pe44320-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE44320 CAD Drawing

75 Ohm F Male Right Angle Connector Crimp/Solder Attachment for RG6-CATV



CRIMP SIZE REQUIRED

FERRULE: .314" HEX CRIMP TOOL

PE PASTERNAK®
Pasternack Enterprises, Inc.
P.O. Box 16759 | Irvine | CA | 92623
Phone: (949) 261-1920 | Fax: (949) 261-7451
Website: www.pasternack.com | E-Mail: sales@pasternack.com

DWG TITLE
PE44320

NOTES:
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES [mm].
4. FITS MIL-C-17 AND EQUIVALENT CABLES.

FSCM NO. 53919

CAD FILE 040811

SCALE N/A

SIZE A

2233



75 Ohm F Male Connector Crimp/Solder Attachment for RG6-CATV, 3 Pieces Connector

RF Connectors Technical Data Sheet

PE44313

Configuration

- F Male Connector
- 75 Ohms
- Straight Body Geometry
- RG6-CATV Interface Type
- Crimp/Solder Attachment
- 7/16 inch Hex

Features

- Max. Operating Frequency 1,000 MHz
- Good VSWR of 1.3:1
- Gold Plated Brass Contact

Applications

- General Purpose Test
- Custom Cable Assemblies

Description

Pasternack's PE44313 75 ohm type F male connector crimp/solder attachment for RG6-CATV is part of our full line of RF components available for same-day shipping. Our type F male connector operates up to a maximum frequency of 1,000 MHz and offers good VSWR of 1.3:1.

Our 75 ohm type F male connector PE44313 datasheet specifications and drawing with dimensions are shown below in this PDF. Pasternack's broad catalog of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. Whether the need is to provide an I/O for a board design, or simply create a custom cable assembly configuration, Pasternack has the right connector for the job. Pasternack can also expertly build your custom cable connector assemblies for you and ship same-day.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		1,000	MHz
VSWR			1.3:1	
Operating Voltage (AC)			500	Vrms

Mechanical Specifications

Size

Length	1.145 in [29.08 mm]
Width/Dia.	0.433 in [11.00 mm]
Weight	0.027 lbs [12.25 g]
Mating Torque	12 to 15 in-lbs [1.36 to 1.70 Nm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [75 Ohm F Male Connector Crimp/Solder Attachment for RG6-CATV, 3 Pieces Connector PE44313](#)



75 Ohm F Male Connector Crimp/Solder Attachment for RG6-CATV, 3 Pieces Connector

RF Connectors Technical Data Sheet

PE44313

Material Specifications

Description	Material	Plating
Contact	Brass	Gold
Insulation	PTFE	
Body	Brass	Nickel 100 µin minimum
Coupling Nut	Brass	Nickel 100 µin minimum

Environmental Specifications

Temperature

Operating Range

-40 to +85 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

75 Ohm F Male Connector Crimp/Solder Attachment for RG6-CATV, 3 Pieces Connector from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [75 Ohm F Male Connector Crimp/Solder Attachment for RG6-CATV, 3 Pieces Connector PE44313](#)

URL: <https://www.pasternack.com/f-male-standard-rg6-catv-connector-pe44313-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE44313 CAD Drawing

75 Ohm F Male Connector Crimp/Solder Attachment for RG6-CATV, 3 Pieces Connector



CONTACT: SOLDER
FERRULE: .314" HEX CRIMP TOOL

PE PASTERNAK®
Pasternack Enterprises, Inc.
P.O. Box 16759 | Irvine | CA | 92623
Phone: (949) 261-1920 | Fax: (949) 261-7451
Website: www.pasternack.com | E-Mail: sales@pasternack.com

DWG TITLE
PE44313

NOTES:
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES [mm].
4. FITS MIL-C-17 AND EQUIVALENT CABLES.

FSCM NO. 53919

CAD FILE 021610-A
SCALE N/A
SIZE A
2233

75 Ohm Flexible RG6-CATV Coax Cable Triple Shielded with Black PVC (NC) Jacket

TECHNICAL DATA SHEET

RG6-CATV

75 Ohm Flexible RG6-CATV Coax Cable Triple Shielded with Black PVC (NC) Jacket

Configuration

Inner Conductor Material and Plating	Copper
Dielectric Type	PE (F)
Shield Materials	Aluminum Foil, Aluminum Braid
Jacket Material and Color	PVC (NC), Black

Electrical Specifications

Impedance, Ohms	75
Velocity of Propagation, %	85
Maximum Operating Frequency, GHz	3
RF Shielding, dB	70
Capacitance, pF/ft [pF/m]	16.2 [53.15]

Electrical Specifications by Frequency

Frequency 1

Frequency, MHz	5
Attenuation, dB/100ft [dB/100m]	0.58 [1.9]

Frequency 2

Frequency, MHz	250
Attenuation, dB/100ft [dB/100m]	3.3 [10.83]

Frequency 3

Frequency, MHz	550
Attenuation, dB/100ft [dB/100m]	4.9 [16.08]

Frequency 4

Frequency, MHz	1000
Attenuation, dB/100ft [dB/100m]	6.55 [21.49]

Frequency 5

Frequency, GHz	1.45
Attenuation, dB/100ft [dB/100m]	7.9 [25.92]

Frequency 6

Frequency, GHz	1.75
Attenuation, dB/100ft [dB/100m]	8.75 [28.71]

Frequency 7

Frequency, GHz	2.15
----------------	------

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [75 Ohm Flexible RG6-CATV Coax Cable Triple Shielded with Black PVC \(NC\) Jacket RG6-CATV](#)

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.

75 Ohm Flexible RG6-CATV Coax Cable Triple Shielded with Black PVC (NC) Jacket

TECHNICAL DATA SHEET

RG6-CATV

Mechanical Specifications

Temperature

Operating Range, deg C -40 to +80

Inner Conductor

Number of Strands 1
 Material Copper
 Diameter, in [mm] 0.04 [1.02]

Dielectric:

Type PE (F)
 Diameter, in [mm] 0.18 [4.57]

Shield:

Number of 3
 Material 1 Aluminum Foil
 Material 2 Aluminum Braid
 Material 3 Aluminum Foil
 Diameter, in [mm] 0.22 [5.59]

Jacket:

Material PVC (NC)
 Diameter, in [mm] 0.275 [6.99]
 Color Black
 One Time Minimum Bend Radius, in [mm] 1.37 [34.8]
 Weight, lbs/ft [Kg/m] 0.033 [0.05]

Compliance Certifications (visit www.Pasternack.com for current document)

RoHS Compliant Yes

Plotted and Other Data

Notes: Values at 25 °C, sea level

75 Ohm Flexible RG6-CATV Coax Cable Triple Shielded with Black PVC (NC) Jacket from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [75 Ohm Flexible RG6-CATV Coax Cable Triple Shielded with Black PVC \(NC\) Jacket RG6-CATV](#)

URL: <http://www.pasternack.com/flexible-0.275-rg6-catv-75-ohm-coax-cable-pvc-jacket-rg6-catv-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.

RG6-CATV CAD Drawing

75 Ohm Flexible RG6-CATV Coax Cable Triple Shielded with Black PVC (NC) Jacket



NOTES:
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES [mm].

DWG TITLE
RG6-CATV

REV. B FSCM NO. 53919

SIZE A 147

SCALE N/A

CAD FILE 021411-B

PASTERNAK®
Pasternack Enterprises, Inc.
P.O. Box 16759 | Irvine | CA | 92623
Phone: (949) 261-1920 | Fax: (949) 261-7451
Website: www.pasternack.com | E-Mail: sales@pasternack.com