

## Plenum 4.3-10 Male to 7/16 DIN Male Low PIM Cable 36 Inch Length Using SPP-250-LLPL Coax , LF Solder




### PE3C4135-36

#### Configuration

- Connector 1: 4.3-10 Male
- Connector 2: 7/16 DIN Male
- Cable Type: SPP-250-LLPL
- Coax Flex Type: Corrugated

#### Features

- Max Frequency 6 GHz
- Low PIM: -160 dBc Max
- Shielding Effectivity > 100 dB
- 76% Phase Velocity
- FEP Jacket
- PIM < -160 dBc
- 100% Tested with PIM Test Results Marked on Cable
- UL910 Plenum Rated Cable
- Lightweight and Extremely Flexible
- Low Loss with Excellent VSWR
- IP67 (when mated)



#### Applications

- General Purpose
- Laboratory Use
- Low PIM Applications
- Distributed Antenna Systems (DAS)
- Plenum Installations
- Multi-Carrier Communication Systems
- PIM Testing

#### Description

Pasternack's low PIM plenum cable assemblies using SPP-250-LLPL coax and 4.3-10 male to 7/16 DIN male connections are part of our full line of RF components available for same-day shipping. These 4.3-10 male to 7/16 DIN male plenum coax cable assemblies deliver low PIM performance to support Distributed Antenna Systems (DAS) and other complex, multi-carrier communication systems. The SPP-250-LLPL coax cable has been certified in accordance with UL910 for plenum coaxial cable installations. Each 4.3-10 male to 7/16 DIN male cable assembly is 100% tested for Passive Intermodulation (PIM) and the tested value is marked directly on the cable.

Our 4.3-10 male to 7/16 DIN male cable datasheet specifications and drawing with dimensions are shown below in this PDF. Whether the need is to provide a low PIM jumper connection, low PIM test cable or simply create a custom cable assembly configuration, Pasternack has the right cable assemblies for the job.

#### Electrical Specifications

| Description                                | Minimum | Typical | Maximum | Units |
|--|---------|---------|---------|-------|
| Frequency Range                            | DC      |         | 6       | GHz   |
| VSWR                                       |         |         | 1.35:1  |       |
| Velocity of Propagation                    |         | 76      |         | %     |
| RF Shielding                               | 100     |         |         | dB    |
| Passive Intermodulation                    |         | -165    | -160    | dBc   |
| IM3 (2x43dBm Tones) at 850 MHz or 1900 MHz |         |         |         |       |

Plenum 4.3-10 Male to 7/16 DIN Male Low PIM Cable  
36 Inch Length Using SPP-250-LLPL Coax , LF Solder



## PE3C4135-36

### Electrical Specifications

| Description                   | Minimum | Typical      | Maximum | Units                 |
|-------------------------------|---------|--------------|---------|-----------------------|
| Capacitance                   |         | 27 [88.58]   |         | pF/ft [pF/m]          |
| Inductance                    |         | 0.067 [0.22] |         | uH/ft [uH/m]          |
| DC Resistance Inner Conductor |         | 3 [9.84]     |         | Ohms/1000ft [Ohms/Km] |
| Operating Voltage (AC)        |         |              | 750     | Vrms                  |

### Specifications by Frequency

| Description           | F1     | F2     | F3     | F4     | F5     | Units |
|-----------------------|--------|--------|--------|--------|--------|-------|
| Frequency             | 0.0005 | 1      | 2      | 4      | 6      | GHz   |
| Insertion Loss (Max.) | 0.52   | 0.57   | 0.65   | 0.76   | 0.85   | dB    |
| VSWR (Max.)           | 1.25:1 | 1.25:1 | 1.25:1 | 1.35:1 | 1.35:1 |       |

#### Electrical Specification Notes:

PIM test results vary between cables

The Insertion Loss data above is based on the performance specifications of the coax used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.4dB of connector loss.

### Mechanical Specifications

#### Cable Assembly

|                |                     |
|----------------|---------------------|
| Width/Diameter | .28 in [7.11 mm]    |
| Weight         | 0.45 lbs [204.12 g] |

#### Cable

|  |                                  |
|--|----------------------------------|
| Cable Type                             | SPP-250-LLPL                     |
| Impedance                              | 50 Ohms                          |
| Inner Conductor Type                   | Solid                            |
| Inner Conductor Material and Plating   | Copper, Bare                     |
| Dielectric Type                        | PTFE                             |
| Number of Shields                      | 1                                |
| Shield Layer 1                         | Helically Corrugated Copper Tube |
| Outer Conductor 1 Material and Plating | Copper                           |
| Outer Conductor Diameter               | 0.25 in [6.35 mm]                |
| Jacket Material                        | FEP, Blue                        |
| Jacket Diameter                        | 0.28 in [7.11 mm]                |
| One Time Minimum Bend Radius           | 1.25 in [31.75 mm]               |
| Bending Moment                         | 0.8 lbs-ft [1.08 N-m]            |

Plenum 4.3-10 Male to 7/16 DIN Male Low PIM Cable  
36 Inch Length Using SPP-250-LLPL Coax , LF Solder



## PE3C4135-36

### Connectors

| Description                       | Connector 1      | Connector 2      |
|-----------------------------------|------------------|------------------|
| Type                              | 4.3-10 Male      | 7/16 DIN Male    |
| Impedance                         | 50 Ohms          | 50 Ohms          |
| Configuration                     | Straight         | Straight         |
| Contact Material and Plating      | Brass, Silver    | Brass, Silver    |
| Dielectric Type                   | PTFE             | PTFE             |
| Body Material and Plating         | Brass, Tri-Metal | Brass, Tri-Metal |
| Coupling Nut Material and Plating | Brass, Tri-Metal | Brass, Tri-Metal |
| Seal Gasket Material              | Silicone Rubber  | Silicone Rubber  |

### Environmental Specifications

|                             |                   |
|-----------------------------|-------------------|
| Operating Range Temperature | -55 to +200 deg C |
| Storage Range Temperature   | -55 to +200 deg C |
| Plenum Rating               | UL910             |

### Compliance Certifications (see [product page](#) for current document)

### Plotted and Other Data

Notes:  
Values at 25°C, sea level.

Plenum 4.3-10 Male to 7/16 DIN Male Low PIM Cable  
36 Inch Length Using SPP-250-LLPL Coax , LF Solder



**PE3C4135-36**

Typical Performance Data




Plenum 4.3-10 Male to 7/16 DIN Male Low PIM Cable  
36 Inch Length Using SPP-250-LLPL Coax , LF Solder



## PE3C4135-36

### How to Order

Part Number Configuration:



Example: PE3C4135-12 = 12 inches long cable  
PE3C4135-100cm = 100 cm long cable

Plenum 4.3-10 Male to 7/16 DIN Male Low PIM Cable 36 Inch Length Using SPP-250-LLPL Coax , LF Solder from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Plenum 4.3-10 Male to 7/16 DIN Male Low PIM Cable 36 Inch Length Using SPP-250-LLPL Coax , LF Solder PE3C4135-36](#)

URL: <https://www.pasternack.com/4.3-10-male-7-16-din-male-spp250llpl-cable-assembly-pe3c4135-36-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE3C4135-36 CAD Drawing

Plenum 4.3-10 Male to 7/16 DIN Male Low PIM Cable 36 Inch Length Using SPP-250-LLPL Coax , LF Solder



|  |  |    |      |     |       |      |        |
|--|--|----|------|-----|-------|------|--------|
|  <p><b>PASTERNACK</b><br/>THE ENGINEER'S RF SOURCE</p> <p>Pasterнак Enterprises, Inc.<br/>P.O. Box 16759   Irvine   CA   92623</p> <p><b>Phone:</b> (949) 261-1920   <b>Fax:</b> (949) 261-7451<br/><b>Website:</b> <a href="http://www.pasterнак.com">www.pasterнак.com</a>   <b>E-Mail:</b> <a href="mailto:sales@pasternack.com">sales@pasterнак.com</a></p> | <p><b>STANDARD TOLERANCES</b></p> <table border="1" style="margin-left: auto; margin-right: auto;"> <tr> <td style="text-align: center;">.X</td><td style="text-align: center;">±0.2</td></tr> <tr> <td style="text-align: center;">.XX</td><td style="text-align: center;">±0.01</td></tr> <tr> <td style="text-align: center;">.XXX</td><td style="text-align: center;">±0.005</td></tr> </table> <p>*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES</p> | .X | ±0.2 | .XX | ±0.01 | .XXX | ±0.005 |
| .X   | ±0.2   |    |      |     |       |      |        |
| .XX  | ±0.01  |    |      |     |       |      |        |
| .XXX   | ±0.005   |    |      |     |       |      |        |
| <p>DWG TITLE</p> <p>PE3C4135</p>   | <p>NOTES:</p> <p>1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.<br/>2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.<br/>3. DIMENSIONS ARE IN INCHES [mm].</p> <p>CAGE CODE 53919</p> <p>CAD FILE 12/05/18</p> <p>SCALE N/A</p> <p>SIZE A</p> <p>7361</p>  |    |      |     |       |      |        |