

Slide-On BMA Plug Bulkhead to SMP Female Right Angle Cable 60 Inch Length Using PE-SR405FLJ Coax




PE3C4869-60

Configuration

- Connector 1: Slide-On BMA Plug Bulkhead
- Connector 2: SMP Female Right Angle
- Cable Type: PE-SR405FLJ
- Coax Flex Type: Formable

Features

- Max Frequency 20 GHz
- Shielding Effectivity > 100 dB
- 69.5% Phase Velocity
- FEP Jacket
- Good VSWR of 1.5:1
- Gold Plated BMA Contacts
- Low Engagement Force BMA interface
- In stock and ready to ship



Applications

- General Purpose
- Laboratory Use
- BMA Cable RF Backplanes
- Blind Mate BMA Test
- Rack and Panel
- Phased Array Interconnects
- High Speed Switching Networks

Description

Pasternack's BMA cable assemblies using PE-SR405FLJ Coax are part of our full line of RF components available for same-day shipping. These BMA cable assemblies are designed to connect BMA system components, BMA racks, or BMA backplanes, delivering signal frequencies as high as 20 GHz. Our family of BMA cables can also be used to connect switching networks or phase-matched antenna arrays where low loss BMA interconnects are desired. If none of our standard options fit your application, you can specify your own custom BMA cable assembly using Pasternack's online Cable Creator.

Our BMA cable assembly datasheet specifications and drawing with dimensions are shown below in this PDF. Pasternack's broad catalog of RF, microwave and millimeter wave cable assemblies allow designers to configure and customize their signal connections however they like. Whether the need is to provide BMA cabling or blind mate rack connections, Pasternack has the right cable assemblies for the job. Pasternack can also expertly build your custom cable assemblies for you and ship same day.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		20	GHz
VSWR			1.5:1	
Return Loss			15.56	dB
Velocity of Propagation		69.5		%
RF Shielding	100			dB
Group Delay		1.43 [4.69]		ns/ft [ns/m]
Capacitance		29 [95.14]		pF/ft [pF/m]

Slide-On BMA Plug Bulkhead to SMP Female Right Angle Cable 60 Inch Length Using PE-SR405FLJ Coax



PE3C4869-60

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Operating Voltage (AC)			335	Vrms

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	1	2	4.5	9	20	GHz
Insertion Loss (Max.)	1.33	1.73	2.75	4	6.2	dB

Mechanical Specifications

Cable Assembly

Width/Diameter	0.315 in [8 mm]
Weight	0.09 lbs [40.82 g]

Cable

Cable Type	PE-SR405FLJ
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper Clad Steel, Silver
Dielectric Type	PTFE
Number of Shields	1
Outer Conductor 1 Material and Plating	Tinned Copper Composite Braid
Jacket Material	FEP, Black
Jacket Diameter	0.105 in [2.67 mm]
One Time Minimum Bend Radius	0.5 in [12.7 mm]
Repeated Minimum Bend Radius	0.787 in [19.99 mm]

Slide-On BMA Plug Bulkhead to SMP Female Right Angle Cable 60 Inch Length Using PE-SR405FLJ Coax



PE3C4869-60

Connectors

Description	Connector 1	Connector 2
Type	BMA Plug Bulkhead	SMP Female Right Angle
Specification		MIL-STD-348A
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Right Angle
Connection Method	Slide-On	
Contact Material and Plating	Bronze, Gold	Beryllium Copper, Gold
Contact Plating Specification	51.18μ in. minimum	
Dielectric Type	PTFE	PTFE
Outer Conductor Material and Plating	Brass, Tri-Metal	
Outer Conductor Plating Specification	78.74μ in. minimum	
Body Material and Plating	Brass, Tri-Metal	Beryllium Copper, Gold
Body Plating Specification	78.74μ in. minimum	
Hex Size	8 mm	

Environmental Specifications

Operating Range Temperature -55 to +125 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data


Notes:

Slide-On BMA Plug Bulkhead to SMP Female Right Angle
Cable 60 Inch Length Using PE-SR405FLJ Coax



PE3C4869-60

Typical Performance Data



Slide-On BMA Plug Bulkhead to SMP Female Right Angle Cable 60 Inch Length Using PE-SR405FLJ Coax



PE3C4869-60

How to Order

Part Number Configuration:

PE3C4869

- XX

uu

- Unit of Measure:

cm = Centimeters

<blank> = Inches

- Length

- Base Number

Example: PE3C4869-12 = 12 inches long cable
PE3C4869-100cm = 100 cm long cable

Slide-On BMA Plug Bulkhead to SMP Female Right Angle Cable 60 Inch Length Using PE-SR405FLJ Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Slide-On BMA Plug Bulkhead to SMP Female Right Angle Cable 60 Inch Length Using PE-SR405FLJ Coax PE3C4869-60](#)

URL: <https://www.pasternack.com/bma-plug-smp-female-pe-sr405flj-cable-assembly-pe3c4869-60-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE3C4869-60 CAD Drawing

Slide-On BMA Plug Bulkhead to SMP Female Right Angle Cable 60 Inch Length Using PE-SR405FLJ Coax

