

SMA Male Right Angle to Mini SMP Female Cable Using PE-P086 Coax




PE3C3370

Configuration

- Connector 1: SMA Male Right Angle
- Connector 2: Mini SMP Female
- Cable Type: PE-P086
- Coax Flex Type: Flexible

Features

- Max Frequency 10 GHz
- Shielding Effectivity > 110 dB
- 70% Phase Velocity
- Double Shielded
- FEP Jacket



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3C3370 SMA male right angle to Mini SMP female cable using PE-P086 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack SMA to Mini SMP cable assembly has a male to female gender configuration with 50 ohm flexible PE-P086 coax. The PE3C3370 SMA male to Mini SMP female cable assembly operates to 10 GHz. The right angle SMA interface on the PE-P086 cable allows for easier connections in tight spaces. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness of better than 110 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		10	GHz
VSWR			1.4:1	
Velocity of Propagation		70		%
RF Shielding	110			dB
Capacitance		29.4 [96.46]		pF/ft [pF/m]

Specifications by Frequency

SMA Male Right Angle to Mini SMP Female
Cable Using PE-P086 Coax



PE3C3370

Part Number	Length	Description	F1	F2	F3	F4	Units	Weight (lbs)
			Frequency	1000	2500	5000	10000	
PE3C3370	Custom Lengths Available	Insertion Loss (Typ.)	0.211	0.338	0.503	0.743	dB/ft	
			0.7	1.11	1.66	2.44	dB/m	
PE3C3370-6	6 inch	Insertion Loss (Typ.)	0.41	0.47	0.56	0.68	dB	0.021
PE3C3370-12	12 inch	Insertion Loss (Typ.)	0.52	0.64	0.81	1.05	dB	0.027
PE3C3370-24	24 inch	Insertion Loss (Typ.)	0.73	0.98	1.31	1.79	dB	0.041
PE3C3370-36	36 inch	Insertion Loss (Typ.)	0.94	1.32	1.81	2.53	dB	0.054
PE3C3370-48	48 inch	Insertion Loss (Typ.)	1.15	1.66	2.32	3.28	dB	0.067

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1: 0.2 dB
 Loss due to Connector 2: 0.1 dB
 Base Weight: 0.027 pounds
 Additional Weight per Inch: 0.00109 pounds

Mechanical Specifications

Cable Assembly

Width/Diameter 0.5 in [12.7 mm]
 Weight 0.027 lbs [12.25 g]

Cable

Cable Type PE-P086
 Impedance 50 Ohms
 Inner Conductor Type Solid
 Inner Conductor Material and Plating Copper Clad Steel, Silver
 Dielectric Type PTFE
 Number of Shields 2
 Shield Layer 1 Silver Plated Copper Tape
 Shield Layer 2 Silver Plated Copper Braid
 Jacket Material FEP, Blue
 Jacket Diameter 0.104 in [2.64 mm]
 Repeated Minimum Bend Radius 0.52 in [13.21 mm]

SMA Male Right Angle to Mini SMP Female
Cable Using PE-P086 Coax



PE3C3370

Connectors

Description	Connector 1	Connector 2
Type	SMA Male Right Angle	Mini SMP Female
Impedance	50 Ohms	50 Ohms
Configuration	Right Angle	Straight
Contact Material and Plating	Brass, Gold over Nickel	Beryllium Copper, Gold
Contact Plating Specification	8 µin minimum	MIL-G-45204
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Gold over Nickel	Beryllium Copper, Gold
Body Plating Specification	4 µin minimum	MIL-G-45204
Coupling Nut Material and Plating	Passivated Stainless Steel	
Hex Size	5/16 in.	
Torque	8 in-lbs 0.9 Nm	

Environmental Specifications

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

SMA Male Right Angle to Mini SMP Female
Cable Using PE-P086 Coax



PE3C3370

Typical Performance Data


How to Order

Part Number Configuration:

PE3C3370

- xx

uu



Example: PE3C3370-12 = 12 inches long cable
PE3C3370-100cm = 100 cm long cable

SMA Male Right Angle to Mini SMP Female Cable Using PE-P086 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male Right Angle to Mini SMP Female Cable Using PE-P086 Coax PE3C3370](#)

URL: <https://www.pasternack.com/sma-male-right-angle-to-mini-smp-female-cable-using-pe-p086-pe3c3370-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE3C3370 CAD Drawing

SMA Male Right Angle to Mini SMP Female Cable Using PE-P086 Coax

