



HN Male Right Angle to HN Male Cable 36 Inch
Length Using RG217 Coax , LF Solder

RF Cable Assemblies Technical Data Sheet

PE3C3916LF-36

Configuration

- Connector 1: HN Male Right Angle
- Connector 2: HN Male
- Cable Type: RG217

Features

- Max Frequency 1 GHz
- 66% Phase Velocity
- Double Shielded
- PVC Jacket

Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3C3916LF-36 HN male right angle to HN male 36 inch cable using RG217 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack HN to HN cable assembly has a male to male gender configuration with 50 ohm flexible RG217 coax. The PE3C3916LF-36 HN male to HN male cable assembly operates to 1 GHz. The right angle HN interface on the RG217 cable allows for easier connections in tight spaces. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [HN Male Right Angle to HN Male Cable 36 Inch Length Using RG217 Coax , LF Solder PE3C3916LF-36](#)



HN Male Right Angle to HN Male Cable 36 Inch
 Length Using RG217 Coax , LF Solder

RF Cable Assemblies Technical Data Sheet

PE3C3916LF-36

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		1,000	MHz
VSWR			1.45:1	
Velocity of Propagation		66		%
Capacitance		30.8 [101.05]		pF/ft [pF/m]
Operating Voltage (AC)			1,500	Vrms

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	50	100	250	500	1,000	MHz
Insertion Loss (Max.)	0.369	0.453	0.486	0.629	0.93	dB

Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax used in this assembly. Insertion Loss is estimated as 0.2 dB for the HN Male Right Angle connector and 0.1 dB for the HN Male connector.

Mechanical Specifications

Cable Assembly

Length*	36 in [914.4 mm]
Diameter	0.9 in [22.86 mm]

Cable

Cable Type	RG217
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper
Dielectric Type	PE
Number of Shields	2
Shield Layer 1	Copper Braid
Shield Layer 2	Copper Braid
Jacket Material	PVC, Black
Jacket Diameter	0.545 in [13.84 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [HN Male Right Angle to HN Male Cable 36 Inch Length Using RG217 Coax , LF Solder PE3C3916LF-36](#)



HN Male Right Angle to HN Male Cable 36 Inch
Length Using RG217 Coax , LF Solder

RF Cable Assemblies Technical Data Sheet

PE3C3916LF-36

Connectors

Description	Connector 1	Connector 2
Type	HN Male Right Angle	HN Male
Specification	MIL-STD-348A	MIL-STD-348
Impedance	50 Ohms	50 Ohms
Contact Material and Plating	Brass, Gold	Brass, Gold
Contact Plating Specification	MIL-STD-45204	MIL-G-45204
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification	QQ-N-290	QQ-N-290
Coupling Nut Material and Plating	Brass, Nickel	Brass, Nickel
Coupling Nut Plating Specification	QQ-N-290	QQ-N-290

Environmental Specifications

Temperature

Operating Range

-40 to +80 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [HN Male Right Angle to HN Male Cable 36 Inch Length Using RG217 Coax , LF Solder PE3C3916LF-36](#)



HN Male Right Angle to HN Male Cable 36 Inch
Length Using RG217 Coax , LF Solder

RF Cable Assemblies Technical Data Sheet

PE3C3916LF-36

How to Order

Part Number Configuration:

PE3C3916LF

- **xx**

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE3C3916LF-12 = 12 inches long cable
PE3C3916LF-100cm = 100 cm long cable

HN Male Right Angle to HN Male Cable 36 Inch Length Using RG217 Coax , LF Solder from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [HN Male Right Angle to HN Male Cable 36 Inch Length Using RG217 Coax , LF Solder PE3C3916LF-36](#)


URL:

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3C3916LF-36 CAD Drawing

HN Male Right Angle to HN Male Cable 36 Inch Length Using RG217 Coax , LF Solder

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	8/25/2020	S.ELLIS



UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS				THIRD-ANGLE PROJECTION			
TOLERANCES:							
X = ± .2 [.08]		FRACTIONS ± 1/32		THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF PASTERNAK CORPORATION ALL RIGHTS RESERVED.		SHEET 1 OF 1	
.XX = ± .02 [.51]		ANGLES ± 1°		SCALE		N/A	
.XXX = ± .005 [.13]		CABLE LENGTH (L) TOLERANCES:		REV		A	
L ≤ 12 [305] = +1 [25] / -0							
12 [305] < L ≤ 60 [1524] = +2 [51] / -0							
60 [1524] < L ≤ 120 [3048] = +4 [102] / -0							
120 [3048] < L ≤ 300 [7620] = +6 [152] / -0							
300 [7620] < L = +5% / -0							
ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.				SIZE		ITEM NO.	
A		53919		K.DANG		PE3C3916LF	
DRAWN BY				CAGE CODE			
K.DANG				53919			
PASTERNAK® an INFINITE® brand				Website: www.pasternack.com E-mail: sales@pasternack.com Fax: 1.949.261.7451 Phone: 1.949.261.1920 1.866.727.8376 P.O. Box 16759, Irvine, CA 92623. Pasternack Enterprises, Inc.			
							

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.