

## MCX Jack Bulkhead to SMA Female Bulkhead Cable Using RG174 Coax




### PE3C5774

#### Configuration

- Connector 1: MCX Jack Bulkhead
- Connector 2: SMA Female Bulkhead
- Cable Type: RG174
- Coax Flex Type: Flexible

#### Features

- 66% Phase Velocity
- PVC Jacket



#### Applications

- General Purpose
- Laboratory Use

#### Description

Pasternack's PE3C5774 MCX jack bulkhead to SMA female bulkhead cable using RG174 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack MCX to SMA cable assembly has a jack to female gender configuration with 50 ohm flexible RG174 coax. Our RF cable assembly with MCX bulkhead and SMA bulkhead interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

#### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Velocity of Propagation		66		%
Capacitance		31.08 [101.97]		pF/ft [pF/m]

#### Mechanical Specifications

##### Cable Assembly

Width/Diameter	0.5 in [12.7 mm]
Weight	0.023 lbs [10.43 g]

##### Cable

Cable Type	RG174
Impedance	50 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper Clad Steel

## MCX Jack Bulkhead to SMA Female Bulkhead Cable Using RG174 Coax



### PE3C5774

Dielectric Type	PE
Number of Shields	1
Shield Layer 1	Tinned Copper Braid
Jacket Material	PVC, Black
Jacket Diameter	0.11 in [2.79 mm]

### Connectors

Description	Connector 1	Connector 2
Type	MCX Jack Bulkhead	SMA Female Bulkhead
Specification	CECC 22220	MIL-STD-348
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Contact Material and Plating	Beryllium Copper, Gold	Beryllium Copper, Gold
Contact Plating Specification	50 µin minimum	MIL-G-45204
Dielectric Type	PTFE	
Outer Conductor Material and Plating		Brass, Nickel
Body Material and Plating	Brass, Gold	Brass, Nickel
Body Plating Specification	30 µin minimum	

### Environmental Specifications

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data

Notes:

## MCX Jack Bulkhead to SMA Female Bulkhead Cable Using RG174 Coax



### PE3C5774

#### Typical Performance Data

#### How to Order

Part Number Configuration:

**PE3C5774**

**- xx**

**uu**

Unit of Measure:

cm = Centimeters

<blank> = Inches

Length

Base Number

Example: PE3C5774-12 = 12 inches long cable  
PE3C5774-100cm = 100 cm long cable

MCX Jack Bulkhead to SMA Female Bulkhead Cable Using RG174 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [MCX Jack Bulkhead to SMA Female Bulkhead Cable Using RG174 Coax PE3C5774](#)

URL: <https://www.pasternack.com/mcx-jack-bulkhead-to-sma-female-bulkhead-cable-using-rg174-pe3c5774-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

# PE3C5774 CAD Drawing

MCX Jack Bulkhead to SMA Female Bulkhead Cable Using RG174 Coax

