



SMA Male to TNC Male Cable Using LMR-195 Coax In 100 CM Length

RF Cable Assemblies Technical Data Sheet


PE3C4535-100CM

Configuration

- Connector 1: SMA Male
- Connector 2: TNC Male
- Cable Type: LMR-195

Features

- Max Frequency 5.8 GHz
- Shielding Effectivity > 90 dB
- 80% Phase Velocity
- Double Shielded
- PE Jacket



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3C4535-100CM SMA male to TNC male 100 cm cable using LMR-195 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack SMA to TNC cable assembly has a male to male gender configuration with 50 ohm flexible LMR-195 coax. The PE3C4535-100CM SMA male to TNC male cable assembly operates to 5.8 GHz. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness of better than 90 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male to TNC Male Cable Using LMR-195 Coax In 100 CM Length PE3C4535-100CM](#)



SMA Male to TNC Male Cable Using LMR-195 Coax In 100 CM Length

RF Cable Assemblies Technical Data Sheet

PE3C4535-100CM

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		5.8	GHz
VSWR			1.5:1	
Velocity of Propagation		80		%
RF Shielding	90			dB
Group Delay		1.27 [4.17]		ns/ft [ns/m]
Capacitance		25.4 [83.33]		pF/ft [pF/m]
Inductance		0.064 [0.21]		uH/ft [uH/m]
DC Resistance Inner Conductor		7.6 [24.93]		Ω/1000ft [Ω/Km]
DC Resistance Outer Conductor		4.9 [16.08]		Ω/1000ft [Ω/Km]
Operating Voltage (AC)			500	Vrms
Dielectric Withstanding Voltage (AC)			1,000	Vrms
Dielectric Withstanding Voltage (DC)			1,000	Vdc
Jacket Spark			3,000	Vrms
Input Power (Peak)			2.5	KWatts

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.25	0.5	1	2.5	5.8	GHz
Insertion Loss (Typ.)	0.29	0.41	0.59	0.94	1.47	dB

Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1*SQRT(FGHz) dB per connector.

Mechanical Specifications

Cable Assembly

Length*	39.37 in [100 cm]
Weight	0.133 lbs [60.33 g]

Cable

Cable Type	LMR-195
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper
Dielectric Type	PE (F)
Number of Shields	2

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male to TNC Male Cable Using LMR-195 Coax In 100 CM Length PE3C4535-100CM](#)



SMA Male to TNC Male Cable Using LMR-195 Coax In 100 CM Length

RF Cable Assemblies Technical Data Sheet

PE3C4535-100CM

Shield Layer 1	Aluminum Tape
Shield Layer 2	Tinned Copper Braid
Jacket Material	PE, Black
Jacket Diameter	0.195 in [4.95 mm]
One Time Minimum Bend Radius	0.5 in [12.7 mm]
Repeated Minimum Bend Radius	2 in [50.8 mm]
Bending Moment	0.2 lbs-ft [0.27 N-m]
Flat Plate Crush	15 lbs/in [0.27 Kg/mm]
Tensile Strength	40 lbs [18.14 Kg]

Connectors

Description	Connector 1	Connector 2
Type	SMA Male	TNC Male
Specification	MIL-STD-348A	
Impedance	50 Ohms	50 Ohms
Contact Material and Plating	Brass, Gold	Beryllium Copper, Gold
Contact Plating Specification	50 µin minimum	
Dielectric Type	PTFE	Teflon
Body Material and Plating	Brass, Nickel	Brass, Silver
Body Plating Specification	100 µin minimum	
Coupling Nut Material and Plating	Brass, Nickel	Brass, Silver
Coupling Nut Plating Specification	100 µin minimum	
Hex Size	5/16 inch	
Torque	3 in-lbs [0.34 Nm]	

Environmental Specifications

Temperature

Operating Range	-40 to +85 deg C
Storage Range	-70 to +85 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male to TNC Male Cable Using LMR-195 Coax In 100 CM Length PE3C4535-100CM](#)



SMA Male to TNC Male Cable Using LMR-195 Coax In 100 CM Length

RF Cable Assemblies Technical Data Sheet

PE3C4535-100CM

How to Order

Part Number Configuration:

PE3C4535

- **xx**

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE3C4535-12 = 12 inches long cable
PE3C4535-100cm = 100 cm long cable

SMA Male to TNC Male Cable Using LMR-195 Coax In 100 CM Length from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male to TNC Male Cable Using LMR-195 Coax In 100 CM Length PE3C4535-100CM](https://www.pasternack.com/sma-male-to-tnc-male-cable-using-lmr-195-coax-in-100-cm-length-pe3c4535-100cm)

URL: <https://www.pasternack.com/sma-male-to-tnc-male-cable-100-cm-length-using-lmr-195-pe3c4535-100cm-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3C4535-100CM CAD Drawing
SMA Male to TNC Male Cable Using LMR-195 Coax In 100 CM Length

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	11/5/2021	A. GANWANI



UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS TOLERANCES: <table><tr><td>X = ± .2</td><td>[.008]</td><td>FRACTIONS</td><td>± 1/32</td></tr><tr><td>.XX = ± .02</td><td>[.51]</td><td>ANGLES</td><td>± 1°</td></tr><tr><td>.XXX = ± .005</td><td>[.13]</td><td>CABLE LENGTH (L) TOLERANCES:</td><td></td></tr></table> <table><tr><td>L ≤ 12 [305]</td><td>± .1 [25]</td><td>/ -0</td></tr><tr><td>12 [305] < L ≤ 60 [1524]</td><td>± .2 [51]</td><td>/ -0</td></tr><tr><td>60 [1524] < L ≤ 120 [3048]</td><td>± .4 [102]</td><td>/ -0</td></tr><tr><td>120 [3048] < L ≤ 300 [7620]</td><td>± .6 [152]</td><td>/ -0</td></tr><tr><td>300 [7620] < L</td><td>± 5% L</td><td>/ -0</td></tr></table> ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.				X = ± .2	[.008]	FRACTIONS	± 1/32	.XX = ± .02	[.51]	ANGLES	± 1°	.XXX = ± .005	[.13]	CABLE LENGTH (L) TOLERANCES:		L ≤ 12 [305]	± .1 [25]	/ -0	12 [305] < L ≤ 60 [1524]	± .2 [51]	/ -0	60 [1524] < L ≤ 120 [3048]	± .4 [102]	/ -0	120 [3048] < L ≤ 300 [7620]	± .6 [152]	/ -0	300 [7620] < L	± 5% L	/ -0	PASTERNAK® an INFINITE® brand Pasternack Enterprises, Inc. P.O.Box 16759, Irvine, CA 92623. Phone: 1.949.261.1920 1.866.727.8376 Fax: 1.949.261.7451 Website: www.pasternack.com E-mail: sales@pasternack.com THIRD-ANGLE PROJECTION THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF PASTERNAK CORPORATION ALL RIGHTS RESERVED. SHEET 1 OF 1 SCALE N/A			
X = ± .2	[.008]	FRACTIONS	± 1/32																															
.XX = ± .02	[.51]	ANGLES	± 1°																															
.XXX = ± .005	[.13]	CABLE LENGTH (L) TOLERANCES:																																
L ≤ 12 [305]	± .1 [25]	/ -0																																
12 [305] < L ≤ 60 [1524]	± .2 [51]	/ -0																																
60 [1524] < L ≤ 120 [3048]	± .4 [102]	/ -0																																
120 [3048] < L ≤ 300 [7620]	± .6 [152]	/ -0																																
300 [7620] < L	± 5% L	/ -0																																
SIZE A	CAGE CODE 53919	DRAWN BY K.DANG	ITEM NO. PE3C4535	REV A																														

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.