



Slide-On BMA Plug Bulkhead to N Male Cable 24 Inch Length Using RG316 Coax

RF Cable Assemblies Technical Data Sheet

PE3C4945-24

Configuration

- Connector 1: Slide-On BMA Plug Bulkhead
- Connector 2: N Male
- Cable Type: RG316

Features

- Max Frequency 1,000 MHz
- 69% Phase Velocity
- FEP Jacket
- Good VSWR of 1.4:1
- Gold Plated BMA Contacts
- Low Engagement Force BMA interface
- In stock and ready to ship

Applications

- General Purpose
- Laboratory Use BMA Cable RF Backplanes
- Blind Mate BMA Test
- Rack and Panel
- Phased Array Interconnects
- High Speed Switching Networks

Description

Pasternack's BMA cable assemblies using RG316/U Coax are part of our full line of RF components available for same-day shipping. These BMA cable assemblies are designed to connect BMA system components, BMA racks, or BMA backplanes, delivering signal frequencies as high as 22 GHz. Our family of BMA cables can also be used to connect switching networks or phase-matched antenna arrays where low loss BMA interconnects are desired. If none of our standard options fit your application, you can specify your own custom BMA cable assembly using Pasternack's online Cable Creator.

Our BMA cable assembly datasheet specifications and drawing with dimensions are shown below in this PDF. Pasternack's broad catalog of RF, microwave and millimeter wave cable assemblies allow designers to configure and customize their signal connections however they like. Whether the need is to provide BMA cabling or blind mate rack connections, Pasternack has the right cable assemblies for the job. Pasternack can also expertly build your custom cable assemblies for you and ship same day.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		1,000	MHz
VSWR			1.4:1	
Return Loss			15.56	dB
Velocity of Propagation	69			%
Operating Voltage (AC)			250	Vrms
Jacket Spark			2,000	Vrms

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Slide-On BMA Plug Bulkhead to N Male Cable 24 Inch Length Using RG316 Coax PE3C4945-24](#)



Slide-On BMA Plug Bulkhead to N Male Cable 24 Inch Length Using RG316 Coax

RF Cable Assemblies Technical Data Sheet

PE3C4945-24

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	50	100	250	500	1,000	MHz
Insertion Loss (Typ.)	0.35	0.42	0.5	0.74	0.96	dB

Mechanical Specifications

Cable Assembly

Length*

24 in [609.6 mm]

Diameter

0.8 in [20.32 mm]

Cable

Cable Type

RG316

Impedance

50 Ohms

Inner Conductor Type

Stranded

Inner Conductor Material and Plating

Copper Clad Steel, Silver

Dielectric Type

PTFE

Number of Shields

1

Shield Layer 1

Silver Plated Copper Braid

Jacket Material

FEP, Tan

Jacket Diameter

0.098 in [2.49 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Slide-On BMA Plug Bulkhead to N Male Cable 24 Inch Length Using RG316 Coax PE3C4945-24](#)



Slide-On BMA Plug Bulkhead to N Male Cable 24 Inch Length Using RG316 Coax

RF Cable Assemblies Technical Data Sheet

PE3C4945-24

Connectors

Description	Connector 1	Connector 2
Type	BMA Plug Bulkhead	N Male
Specification		MIL-STD-348A
Impedance	50 Ohms	50 Ohms
Connection Method	Slide-On	
Contact Material and Plating	Beryllium Copper, Gold	Brass, Gold
Contact Plating Specification	51.18 μ in. minimum	30 μ in minimum
Dielectric Type	PTFE	PTFE
Outer Conductor Material and Plating	Passivated Stainless Steel	
Body Material and Plating	Passivated Stainless Steel	Brass, Nickel
Body Plating Specification		100 μ in minimum
Coupling Nut Material and Plating		Brass, Nickel
Coupling Nut Plating Specification		100 μ in minimum
Hex Size	8 mm	

Mechanical Specification Notes:

*All cable assemblies have a length tolerance of 1.5% or $\pm 3/8$ ", whichever is greater.

Environmental Specifications

Temperature

Operating Range

-55 to +125 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Slide-On BMA Plug Bulkhead to N Male Cable 24 Inch Length Using RG316 Coax PE3C4945-24](#)




Slide-On BMA Plug Bulkhead to N Male Cable
24 Inch Length Using RG316 Coax

RF Cable Assemblies Technical Data Sheet

PE3C4945-24

Typical Performance Data



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Slide-On BMA Plug Bulkhead to N Male Cable 24 Inch Length Using RG316 Coax PE3C4945-24](#)



Slide-On BMA Plug Bulkhead to N Male Cable 24 Inch Length Using RG316 Coax

RF Cable Assemblies Technical Data Sheet

PE3C4945-24

How to Order

Part Number Configuration:

PE3C4945

- **xx**

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches

Length
Base Number

Example: PE3C4945-12 = 12 inches long cable
PE3C4945-100cm = 100 cm long cable

Slide-On BMA Plug Bulkhead to N Male Cable 24 Inch Length Using RG316 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Slide-On BMA Plug Bulkhead to N Male Cable 24 Inch Length Using RG316 Coax PE3C4945-24](#)

URL: <https://www.pasternack.com/bma-plug-n-male-rg316u-cable-assembly-pe3c4945-24-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3C4945-24 CAD Drawing

Slide-On BMA Plug Bulkhead to N Male Cable 24 Inch Length Using RG316 Coax



STANDARD TOLERANCES

X	± 0.2
.XX	± 0.01
.XXX	± 0.005

*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

PE PASTERNACK®
THE ENGINEER'S RESOURCE

Pasternack Enterprises, Inc.
P.O. Box 16759 | Irvine | CA | 92623

Phone: (949) 261-1920 | Fax: (949) 261-7451

Website: www.pasternack.com | E-Mail: sales@pasternack.com

NOTES:
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES [mm].

DWG TITLE	PE3C4945
CAGE CODE	53919

SCALE N/A	SIZE A
CN2245	