


2.92mm Male to SMP Female Right Angle Cable 24 Inch Length Using PE-SR405FLJ Coax



PE3C6052-24


Configuration

- Connector 1: 2.92mm Male
- Connector 2: SMP Female Right Angle
- Cable Type: PE-SR405FLJ
- Coax Flex Type: Formable



Features

- Max Frequency 12.4 GHz
- Shielding Effectivity > 100 dB
- 69.5% Phase Velocity
- FEP Jacket



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3C6052-24 2.92mm male to SMP female right angle 24 inch cable using PE-SR405FLJ coax is part of our full line of RF components available for same-day shipping. Pasternack's formable RF cable assemblies provide an alternative to costly pre-formed semi-rigid assemblies since they are hand formable. This Pasternack 2.92mm to SMP cable assembly has a male to female gender configuration with 50 ohm formable PE-SR405FLJ coax. The PE3C6052-24 2.92mm male to SMP female cable assembly operates to 12.4 GHz. The right angle SMP interface on the PE-SR405FLJ cable allows for easier connections in tight spaces.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		12.4	GHz
VSWR			1.4:1	
Velocity of Propagation		69.5		%
RF Shielding	100			dB
Group Delay		1.43 [4.69]		ns/ft [ns/m]
Capacitance		29 [95.14]		pF/ft [pF/m]
DC Resistance Inner Conductor		65.7 [215.55]		Ohms/1000ft [Ohms/Km]
DC Resistance Outer Conductor		10.2 [33.46]		Ohms/1000ft [Ohms/Km]
Operating Voltage (AC)			170	Vrms

Specifications by Frequency

2.92mm Male to SMP Female Right Angle Cable 24 Inch Length Using PE-SR405FLJ Coax



PE3C6052-24

Part Number	Length	Description	F1	F2	F3	F4	F5	Units	Weight (lbs)
		Frequency	500	1000	2500	5000	12400	MHz	
PE3C6052	Custom Lengths Available	Insertion Loss (Typ.)	0.15	0.225	0.346	0.549	0.905	dB/ft	
			0.5	0.74	1.14	1.81	2.97	dB/m	
PE3C6052-6	6 inch	Insertion Loss (Typ.)	0.43	0.62	0.97	1.4	2.22	dB	0.023
PE3C6052-9	9 inch	Insertion Loss (Typ.)	0.47	0.67	1.06	1.53	2.44	dB	0.027
PE3C6052-12	12 inch	Insertion Loss (Typ.)	0.51	0.73	1.14	1.67	2.67	dB	0.03
PE3C6052-18	18 inch	Insertion Loss (Typ.)	0.58	0.84	1.31	1.95	3.12	dB	0.038
PE3C6052-24	24 inch	Insertion Loss (Typ.)	0.66	0.95	1.49	2.22	3.58	dB	0.045

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1: 0.01*SQRT(FGHz) dB

Loss due to Connector 2: 0.04*SQRT(FGHz) dB

Base Weight: 0.03 pounds

Additional Weight per Inch: 0.00117 pounds

Mechanical Specifications

Cable Assembly

Length 24 in [609.6 mm]
Width/Diameter 0.5 in [12.7 mm]
Weight 0.045 lbs [20.41 g]

Cable

Cable Type	PE-SR405FLJ
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper Clad Steel, Silver
Dielectric Type	PTFE
Number of Shields	1
Outer Conductor 1 Material and Plating	Tinned Copper Composite Braid
Jacket Material	FEP, Black
Jacket Diameter	0.105 in [2.67 mm]
One Time Minimum Bend Radius	0.5 in [12.7 mm]
Repeated Minimum Bend Radius	0.787 in [19.99 mm]

2.92mm Male to SMP Female Right Angle Cable
24 Inch Length Using PE-SR405FLJ Coax



PE3C6052-24

Connectors

Description	Connector 1	Connector 2
Type	2.92mm Male	SMP Female Right Angle
Specification		MIL-STD-348A
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Right Angle
Mating Cycles	500	
Contact Material and Plating	Beryllium Copper, Gold over Nickel	Beryllium Copper, Gold
Contact Plating Specification	50 μ in minimum	
Dielectric Type	PCTFE	PTFE
Body Material and Plating	Passivated Stainless Steel	Beryllium Copper, Gold
Body Plating Specification	SAE-AMS-2700	
Coupling Nut Material and Plating	Passivated Stainless Steel	
Coupling Nut Plating Specification	SAE-AMS-2700	
Hex Size	5/16 inch	
Torque	8 in-lbs 0.9 Nm	

Environmental Specifications

Operating Range Temperature -55 to +125 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

2.92mm Male to SMP Female Right Angle Cable
24 Inch Length Using PE-SR405FLJ Coax




PE3C6052-24

Typical Performance Data

How to Order

Part Number Configuration:



Example: PE3C6052-12 = 12 inches long cable
PE3C6052-100cm = 100 cm long cable

2.92mm Male to SMP Female Right Angle Cable 24 Inch Length Using PE-SR405FLJ Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.92mm Male to SMP Female Right Angle Cable 24 Inch Length Using PE-SR405FLJ Coax PE3C6052-24](#)

URL: <https://www.pasternack.com/2.92mm-male-to-smp-female-cable-24-inch-length-using-pe-sr405flj-pe3c6052-24-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE3C6052-24 CAD Drawing

2.92mm Male to SMP Female Right Angle Cable 24 Inch Length Using PE-SR405FLJ Coax



PE PASTERNAK® an INFINITE® brand	
INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5 SCALE	
None	Sheet 1 OF 1
Website: www.Pasternack.com	Phone: 1.866.727.8376 1.949.261.1920
DESCRIPTION	2.92mm Male to SMP Female Right Angle Cable Using PE-SR405FLJ Coax
SIZE	ITEM NO.
A	PE3CC052
3	1