

Fire Rated 4.3-10 Female to N Male Low PIM Cable 100 cm  
Length Using SPF-250 Coax Using Times Microwave Parts



## RF Cable Assemblies Technical Data Sheet

**PE3C6351-100CM**

### Configuration

- Connector 1: 4.3-10 Female
- Connector 2: N Male
- Cable Type: SPF-250

### Features

- Max Frequency 5.8 GHz
- Low PIM: -160 dBc Max
- 83% Phase Velocity
- FRPE Jacket
- 100% Tested with PIM Test Results Marked on Cable
- Lightweight and Extremely Flexible
- Low Loss with Excellent VSWR
- IP67 (when mated)
- Using Times Microwave Components

### Applications

• General Purpose	• Distributed Antenna Systems (DAS)	• Multi-Carrier Communication Systems
• Laboratory Use		• PIM Testing
• Low PIM Applications		

### Description

Pasternack's PE3C6351-100CM 4.3-10 female to type N male 100 cm cable using SPF-250 coax is part of our full line of RF components available for same-day shipping. Pasternack's corrugated RF cable assemblies are ideal for applications where durability and high power are needed. This Pasternack 4.3-10 to type N cable assembly has a female to male gender configuration with 50 ohm corrugated SPF-250 coax. The PE3C6351-100CM 4.3-10 female to type N male cable assembly operates to 5.8 GHz. Our low PIM design also offers excellent passive intermodulation performance with PIM levels better than -160 dBc. Times Microwave cable is used in each assembly and TMS components are used to form connections with the super flexible low PIM cable. These cable assemblies are expertly built to satisfy your specific need with high quality Times Microwave Systems manufactured parts.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Fire Rated 4.3-10 Female to N Male Low PIM Cable 100 cm Length Using SPF-250 Coax Using Times Microwave Parts PE3C6351-100CM](#)



## Fire Rated 4.3-10 Female to N Male Low PIM Cable 100 cm Length Using SPF-250 Coax Using Times Microwave Parts

### RF Cable Assemblies Technical Data Sheet

**PE3C6351-100CM**

#### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		5.8	GHz
VSWR			1.4:1	
Velocity of Propagation		83		%
Passive Intermodulation		-165	-160	dBc
Capacitance		24 [78.74]		pF/ft [pF/m]
Inductance		0.054 [0.18]		uH/ft [uH/m]

#### Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.45	0.7	1	2.5	5.8	GHz
Insertion Loss (Max.)	0.27	0.34	0.41	0.66	1.03	dB

#### Electrical Specification Notes:

PIM test results vary between cables

The Insertion Loss data above is based on the performance specifications of the coax used in this assembly. The Insertion Loss includes an estimated insertion loss of  $0.1 * \text{SQRT}(F\text{GHz})$  dB per connector.

#### Mechanical Specifications

##### Cable Assembly

Weight 0.37 lbs [167.83 g]

##### Cable

Cable Type SPF-250  
 Impedance 50 Ohms  
 Inner Conductor Type Solid  
 Inner Conductor Material and Plating Copper Clad Aluminum  
 Dielectric Type Foam PE  
 Number of Shields 1  
 Shield Layer 1 Helically Corrugated Copper Tube  
 Outer Conductor Material and Plating Copper  
 Jacket Material FRPE, Black  
 Jacket Diameter 0.303 in [7.7 mm]

One Time Minimum Bend Radius 1.25 in [31.75 mm]  
 Bending Moment 0.5 lbs-ft [0.68 N-m]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Fire Rated 4.3-10 Female to N Male Low PIM Cable 100 cm Length Using SPF-250 Coax Using Times Microwave Parts PE3C6351-100CM](#)



Fire Rated 4.3-10 Female to N Male Low PIM Cable 100 cm Length Using SPF-250 Coax Using Times Microwave Parts

## RF Cable Assemblies Technical Data Sheet

**PE3C6351-100CM**

### Connectors

Description	Connector 1	Connector 2
Type	4.3-10 Female	N Male
Impedance	50 Ohms	50 Ohms
Mating Cycles		500
Contact Material and Plating	Phosphor Bronze, Silver	Brass, Silver
Contact Plating Specification	200 $\mu$ in	200 $\mu$ in
Dielectric Type	PTFE	PTFE
Outer Conductor Material and Plating	Brass, Tri-Metal	
Outer Conductor Plating Specification	80 $\mu$ in	
Body Material and Plating	Brass, Tri-Metal	Brass, Tri-Metal
Body Plating Specification	80 $\mu$ in	80 $\mu$ in
Coupling Nut Material and Plating		Brass, Tri-Metal
Coupling Nut Plating Specification		80 $\mu$ in
Torque		9.74 in-lbs [1.1 Nm]

### Environmental Specifications

#### Temperature

Operating Range

-55 to +200 deg C

Storage Range

-55 to +200 deg C

Environmental Specification Notes:

CMR (Riser) Fire Rated

### Compliance Certifications (see [product page](#) for current document)

### Plotted and Other Data

Notes:

- Values at 25°C, sea level.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Fire Rated 4.3-10 Female to N Male Low PIM Cable 100 cm Length Using SPF-250 Coax Using Times Microwave Parts PE3C6351-100CM](#)



Fire Rated 4.3-10 Female to N Male Low PIM Cable 100 cm  
Length Using SPF-250 Coax Using Times Microwave Parts

## RF Cable Assemblies Technical Data Sheet

**PE3C6351-100CM**

### How to Order

Part Number Configuration:

**PE3C6351**

- **xx**

**uu**

Unit of Measure:  
cm = Centimeters  
<blank> = Inches  
Length  
Base Number

Example: PE3C6351-12 = 12 inches long cable  
PE3C6351-100cm = 100 cm long cable

Fire Rated 4.3-10 Female to N Male Low PIM Cable 100 cm Length Using SPF-250 Coax Using Times Microwave Parts from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Fire Rated 4.3-10 Female to N Male Low PIM Cable 100 cm Length Using SPF-250 Coax Using Times Microwave Parts PE3C6351-100CM](#)

URL: <https://www.pasternack.com/4.3-10-female-n-male-spf250-cable-assembly-pe3c6351-100cm-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

# PE3C6351-100CM CAD Drawing

Fire Rated 4.3-10 Female to N Male Low PIM Cable 100 cm Length  
Using SPF-250 Coax Using Times Microwave Parts

