

Plenum 4.3-10 Male Right Angle to 4.3-10 Male  
Right Angle Low PIM Cable 50 cm Length Using SPP-250-  
LLPL Coax Using Times Microwave Parts

## RF Cable Assemblies Technical Data Sheet

**PE3C6177-50CM**

### Configuration

- Connector 1: 4.3-10 Male Right Angle
- Connector 2: 4.3-10 Male Right Angle
- Cable Type: SPP-250-LLPL

### Features

- Max Frequency 5.8 GHz
- Low PIM: -160 dBc Max
- Shielding Effectivity > 100 dB
- 76% Phase Velocity
- FEP Jacket
- 100% Tested with PIM Test Results Marked on Cable
- UL910 Plenum Rated Cable
- Lightweight and Extremely Flexible
- Low Loss with Excellent VSWR
- IP67 (when mated)
- Using Times Microwave Components

### Applications


- General Purpose
- Laboratory Use
- Low PIM Applications
- Distributed Antenna Systems (DAS)
- Plenum Installations
- Multi-Carrier Communication Systems
- PIM Testing

### Description

Pasternack's PE3C6177-50CM 4.3-10 male right angle to 4.3-10 male right angle 50 cm cable using SPP-250-LLPL coax is part of our full line of RF components available for same-day shipping. Pasternack's corrugated RF cable assemblies are ideal for applications where durability and high power are needed. This Pasternack 4.3-10 to 4.3-10 cable assembly has a male to male gender configuration with 50 ohm corrugated SPP-250-LLPL coax. The PE3C6177-50CM 4.3-10 male to 4.3-10 male cable assembly operates to 5.8 GHz. Our low PIM design also offers excellent passive intermodulation performance with PIM levels better than -160 dBc. The right angle 4.3-10 interfaces on the SPP-250-LLPL cable allow for easier connections in tight spaces. Times Microwave cable is used in each assembly and TMS components are used to form connections with the super flexible low PIM cable. These cable assemblies are expertly built to satisfy your specific need with high quality Times Microwave Systems manufactured parts.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Plenum 4.3-10 Male Right Angle to 4.3-10 Male Right Angle Low PIM Cable 50 cm Length Using SPP-250-LLPL Coax Using Times Microwave Parts PE3C6177-50CM](#)



Plenum 4.3-10 Male Right Angle to 4.3-10 Male  
 Right Angle Low PIM Cable 50 cm Length Using SPP-250-  
 LLPL Coax Using Times Microwave Parts

## RF Cable Assemblies Technical Data Sheet

**PE3C6177-50CM**

### Electrical Specifications

| Description                   | Minimum | Typical      | Maximum | Units           |
|-------------------------------|---------|--------------|---------|-----------------|
| Frequency Range               | DC      |              | 5.8     | GHz             |
| VSWR                          |         |              | 1.4:1   |                 |
| Velocity of Propagation       |         | 76           |         | %               |
| RF Shielding                  | 100     |              |         | dB              |
| Passive Intermodulation       |         | -165         | -160    | dBc             |
| Capacitance                   |         | 27 [88.58]   |         | pF/ft [pF/m]    |
| Inductance                    |         | 0.067 [0.22] |         | uH/ft [uH/m]    |
| DC Resistance Inner Conductor |         | 3 [9.84]     |         | Ω/1000ft [Ω/Km] |

### Specifications by Frequency

| Description           | F1   | F2   | F3  | F4   | F5   | Units |
|-----------------------|------|------|-----|------|------|-------|
| Frequency             | 0.45 | 0.7  | 1   | 2.5  | 5.8  | GHz   |
| Insertion Loss (Max.) | 0.21 | 0.26 | 0.3 | 0.48 | 0.75 | dB    |

#### Electrical Specification Notes:

PIM test results vary between cables

The Insertion Loss data above is based on the performance specifications of the coax used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1\*SQRT(FGHz) dB per connector.

### Mechanical Specifications

#### Cable Assembly

##### Cable

|                                      |                                  |
|--------------------------------------|----------------------------------|
| Cable Type                           | SPP-250-LLPL                     |
| Impedance                            | 50 Ohms                          |
| Inner Conductor Type                 | Solid                            |
| Inner Conductor Material and Plating | Copper                           |
| Dielectric Type                      | PTFE                             |
| Number of Shields                    | 1                                |
| Shield Layer 1                       | Helically Corrugated Copper Tube |
| Outer Conductor Material and Plating | Copper                           |
| Outer Conductor Diameter             | 0.25 in [6.35 mm]                |
| Jacket Material                      | FEP, Blue                        |
| Jacket Diameter                      | 0.28 in [7.11 mm]                |
| One Time Minimum Bend Radius         | 1.25 in [31.75 mm]               |

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Plenum 4.3-10 Male Right Angle to 4.3-10 Male Right Angle Low PIM Cable 50 cm Length Using SPP-250-LLPL Coax Using Times Microwave Parts PE3C6177-50CM](#)



Plenum 4.3-10 Male Right Angle to 4.3-10 Male  
Right Angle Low PIM Cable 50 cm Length Using SPP-250-  
LLPL Coax Using Times Microwave Parts

## RF Cable Assemblies Technical Data Sheet

**PE3C6177-50CM**

Bending Moment

0.8 lbs-ft [1.08 N-m]

### Connectors

| Description                        | Connector 1             | Connector 2             |
|------------------------------------|-------------------------|-------------------------|
| Type                               | 4.3-10 Male Right Angle | 4.3-10 Male Right Angle |
| Impedance                          | 50 Ohms                 | 50 Ohms                 |
| Contact Material and Plating       | Brass, Silver           | Brass, Silver           |
| Contact Plating Specification      | 200μ in                 | 200μ in                 |
| Dielectric Type                    | PTFE                    | PTFE                    |
| Body Material and Plating          | Brass, Tri-Metal        | Brass, Tri-Metal        |
| Body Plating Specification         | 80μ in                  | 80μ in                  |
| Coupling Nut Material and Plating  | Brass, Nickel           | Brass, Nickel           |
| Coupling Nut Plating Specification | 200μ in                 | 200μ in                 |
| Torque                             | 15.05 in-lbs [1.7 Nm]   | 15.05 in-lbs [1.7 Nm]   |

### Environmental Specifications

#### Temperature

Operating Range

-55 to +200 deg C

Storage Range

-55 to +200 deg C

Plenum Rating

UL910

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data

Notes:

- Values at 25°C, sea level.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Plenum 4.3-10 Male Right Angle to 4.3-10 Male Right Angle Low PIM Cable 50 cm Length Using SPP-250-LLPL Coax Using Times Microwave Parts PE3C6177-50CM](#)



Plenum 4.3-10 Male Right Angle to 4.3-10 Male  
Right Angle Low PIM Cable 50 cm Length Using SPP-250-  
LLPL Coax Using Times Microwave Parts

## RF Cable Assemblies Technical Data Sheet

**PE3C6177-50CM**

### How to Order

Part Number Configuration:

**PE3C6177**

- **xx**

**uu**

Unit of Measure:  
cm = Centimeters  
<blank> = Inches  
Length  
Base Number

Example: PE3C6177-12 = 12 inches long cable  
PE3C6177-100cm = 100 cm long cable

Plenum 4.3-10 Male Right Angle to 4.3-10 Male Right Angle Low PIM Cable 50 cm Length Using SPP-250-LLPL Coax Using Times Microwave Parts from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Plenum 4.3-10 Male Right Angle to 4.3-10 Male Right Angle Low PIM Cable 50 cm Length Using SPP-250-LLPL Coax Using Times Microwave Parts PE3C6177-50CM](https://www.pasternack.com/4.3-10-male-4.3-10-male-spp250llpl-cable-assembly-pe3c6177-50cm-p.aspx)


URL: <https://www.pasternack.com/4.3-10-male-4.3-10-male-spp250llpl-cable-assembly-pe3c6177-50cm-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

# PE3C6177-50CM CAD Drawing

Plenum 4.3-10 Male Right Angle to 4.3-10 Male Right Angle Low PIM Cable  
50 cm Length Using SPP-250-LLPL Coax Using Times Microwave Parts

| REVISIONS |                 |          |          |
|-----------|-----------------|----------|----------|
| REV.      | DESCRIPTION     | DATE     | APPROVED |
| A         | INITIAL RELEASE | 04/09/19 | SELLIS   |



|                                                                                                  |  |  |                                                                                     |  |                                                                                                                        |  |
|--------------------------------------------------------------------------------------------------|--|--|-------------------------------------------------------------------------------------|--|------------------------------------------------------------------------------------------------------------------------|--|
| UNLESS OTHERWISE SPECIFIED<br>LEADING DIMENSIONS ARE INCHES<br>DIMENSIONS IN [ ] ARE MILLIMETERS |  |  |  |  | THE INFORMATION AND<br>DESIGN IN THIS DOCUMENT<br>IS THE PROPERTY OF<br>PASTERNAK CORPORATION.<br>ALL RIGHTS RESERVED. |  |
| TOLERANCES:                                                                                      |  |  |                                                                                     |  | SHEET 1 OF 1                                                                                                           |  |
| X±.2 [5.08] FRACTIONS                                                                            |  |  | Pasternack Enterprises, Inc.                                                        |  | SCALE N/A                                                                                                              |  |
| .XX±.01 [.25] ±.132                                                                              |  |  | P.O.Box 16759, Irvine, CA 92623.                                                    |  |                                                                                                                        |  |
| XXX±.005 [.13] ANGLES ± 1°                                                                       |  |  | Phone: 1.949.261.1920   1.866.727.8376                                              |  |                                                                                                                        |  |
| ALL DIMENSIONS SHOWN<br>ARE FOR REFERENCE ONLY.                                                  |  |  | Fax: 1.949.261.7451                                                                 |  |                                                                                                                        |  |
| THIRD-ANGLE PROJECTION                                                                           |  |  | www.pasternack.com   e-mail: sales@pasternack.com                                   |  |                                                                                                                        |  |
|               |  |  | SIZE [CAGE DRAWN BY PART NUMBER REV                                                 |  | A 53919 K.DANG PE3C6177 A                                                                                              |  |

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.