



3.5mm Female to Straight Cut Lead Cable 12 Inch Length Using RG402 Coax

RF Cable Assemblies Technical Data Sheet

PE3C7590-12

Configuration

- Connector 1: 3.5mm Female
- Connector 2: Straight Cut Lead
- Cable Type: RG402

Features

- 69.5% Phase Velocity

Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3C7590-12 50 ohm 3.5mm female to straight cut lead 12 inch cable using RG402 coax is part of our full line of RF components available for same-day shipping. Pasternack's semi-rigid RF cable assemblies are ideal for high performance applications and can be formed, using proper tooling, to the routing pattern required.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Velocity of Propagation		69.5		%

Mechanical Specifications

Cable Assembly				
Length*		12 in [304.8 mm]		
Cable				
Cable Type		RG402		
Impedance		50 Ohms		
Inner Conductor Type		Solid		
Inner Conductor Material and Plating		Copper Clad Steel, Silver		
Dielectric Type		PTFE		
Number of Shields		1		
Outer Conductor Material and Plating		Copper		
Repeated Minimum Bend Radius		0.25 in [6.35 mm]		

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [3.5mm Female to Straight Cut Lead Cable 12 Inch Length Using RG402 Coax PE3C7590-12](#)



3.5mm Female to Straight Cut Lead Cable
12 Inch Length Using RG402 Coax

RF Cable Assemblies Technical Data Sheet

PE3C7590-12

Connectors

Description	Connector 1	Connector 2
Type	3.5mm Female	Straight Cut Lead
Impedance	50 Ohms	0 Ohms
Contact Material and Plating	Beryllium Copper, Gold over Nickel	
Contact Plating Specification	50 µin minimum	
Dielectric Type	PCTFE	
Body Material and Plating	Passivated Stainless Steel	
Body Plating Specification	SAE-AMS-2700	

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [3.5mm Female to Straight Cut Lead Cable 12 Inch Length Using RG402 Coax PE3C7590-12](#)



3.5mm Female to Straight Cut Lead Cable
12 Inch Length Using RG402 Coax

RF Cable Assemblies Technical Data Sheet

PE3C7590-12

How to Order

Part Number Configuration:

PE3C7590

- **xx**

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE3C7590-12 = 12 inches long cable
PE3C7590-100cm = 100 cm long cable

3.5mm Female to Straight Cut Lead Cable 12 Inch Length Using RG402 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [3.5mm Female to Straight Cut Lead Cable 12 Inch Length Using RG402 Coax PE3C7590-12](https://www.pasternack.com/3.5mm-female-straight-cut-sexless-rg402u-cable-assembly-pe3c7590-12-p.aspx)


URL: <https://www.pasternack.com/3.5mm-female-straight-cut-sexless-rg402u-cable-assembly-pe3c7590-12-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3C7590-12 CAD Drawing

3.5mm Female to Straight Cut Lead Cable 12 Inch Length Using RG402 Coax

REVISIONS		
REV.	DESCRIPTION	DATE
A	INITIAL RELEASE	10/21/2020
		APPROVED
		S. ELLIS



3.5mm FEMALE

UNLESS OTHERWISE SPECIFIED
LEADING DIMENSIONS ARE INCHES
DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:
 .X = ±.2 [.008] FRACTIONS ± 1/32
 .XX = ±.02 [.51] ANGLES ± 1°
 .XXX = ±.005 [.13]

CABLE LENGTH (L), TOLERANCES:
 L ≤ 12 [305] = +1 [25] / -0
 12 [305] < L ≤ 60 [1524] = +2 [51] / -0
 60 [1524] < L ≤ 120 [3048] = +4 [102] / -0
 120 [3048] < L ≤ 300 [7620] = +6 [152] / -0
 300 [7620] < L = +5% / -0

ALL DIMENSIONS SHOWN
ARE FOR REFERENCE ONLY.

PE PASTERNAK
an INFINITE brand

Pasternack Enterprises, Inc.
 P. O. Box 16759, Irvine, CA 92623.
 Phone: 1.949.261.1920 | 1.866.727.8376
 Fax: 1.949.261.7451
 Website: www.pasternack.com
 E-mail: sales@pasternack.com

SIZE: A CAGE CODE: 53919 DRAWN BY: K.DANG ITEM NO.: PE3C7590

THIRD-ANGLE PROJECTION

THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF PASTERNAK CORPORATION. ALL RIGHTS RESERVED.

SHEET 1 OF 1

SCALE: N/A

REV: A